


Plug-In

Power Splitter/Combiner

NON-CATALOG

PSC-8A-4+

8 Way-0° 50Ω 5 to 500 MHz



CASE STYLE: E10
PRICE: CONTACT SALES DPT.

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.62W max.
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

SUM PORT	29
PORT 1	7
PORT 2	16
PORT 3	31
PORT 4	24
PORT 5	9
PORT 6	2
PORT 7	26
PORT 8	17
GROUND	all other pins
CASE GROUND	all other pins
NOT USED	15

Features

- wideband, 5 to 500 MHz
- good isolation, 23 dB typ.
- rugged welded construction
- excellent amplitude unbalance. 0.3 dB typ.

Applications

- VHF/UHF
- defense and federal communications

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION (dB)						INSERTION LOSS (dB) ABOVE 9.0 dB						PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)		
	L		M		U		L		M		U		L		M		U	
	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.	Max.	Max.	Max.
f _L -f _U																		
5-500	25	20	23	18	20	15	0.7	1.2	1.0	1.8	1.4	2.5	3.0	8.0	16.0	0.2	0.3	0.5

L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U]

Typical Performance Data

Freq. (MHz)	Total Loss ¹ (dB)						Amplitude Unbalance (dB)	Isolation (dB)				VSWR		
	S-1		S-2	S-3	S-4	S-6	S-8	1-2	1-8	3-4	6-7	S	1	8
5.00	9.51	9.50	9.48	9.48	9.47	9.47	0.04	25.99	38.34	26.38	26.57	1.39	1.13	1.14
10.00	9.49	9.49	9.47	9.48	9.47	9.46	0.04	26.07	38.65	26.30	26.38	1.38	1.10	1.10
20.00	9.49	9.49	9.47	9.49	9.47	9.47	0.04	25.95	38.62	26.13	26.21	1.38	1.10	1.10
35.00	9.48	9.48	9.46	9.47	9.45	9.46	0.03	26.80	38.29	27.02	27.09	1.38	1.12	1.12
50.00	9.55	9.56	9.52	9.54	9.52	9.52	0.04	29.71	38.01	30.08	29.99	1.40	1.14	1.13
80.00	9.64	9.65	9.62	9.63	9.61	9.61	0.04	37.01	37.49	37.92	36.72	1.44	1.16	1.15
110.00	9.80	9.81	9.76	9.80	9.77	9.77	0.05	41.82	37.01	40.79	38.66	1.50	1.18	1.17
140.00	9.80	9.84	9.78	9.81	9.78	9.78	0.07	36.27	36.66	35.02	34.25	1.56	1.19	1.18
170.00	9.83	9.85	9.81	9.83	9.80	9.81	0.06	32.78	35.91	31.84	31.29	1.61	1.22	1.21
200.00	10.06	10.10	10.04	10.10	10.05	10.05	0.07	31.00	35.56	30.12	29.67	1.67	1.24	1.24
240.00	9.87	9.91	9.87	9.90	9.86	9.87	0.06	29.58	34.89	28.71	28.26	1.71	1.24	1.23
325.00	9.96	10.00	9.97	10.02	9.96	9.96	0.08	29.68	33.91	28.57	27.90	1.70	1.26	1.26
400.00	10.02	10.08	10.04	10.11	10.04	10.03	0.12	33.51	33.16	31.54	30.06	1.56	1.25	1.26
450.00	10.07	10.14	10.12	10.16	10.10	10.08	0.14	42.38	32.81	37.15	33.57	1.41	1.24	1.25
500.00	10.05	10.14	10.07	10.18	10.09	10.07	0.18	37.15	32.52	38.45	37.11	1.25	1.21	1.24


1. Total Loss = Insertion Loss + 9dB splitter loss.



electrical schematic



Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	
1.580	1.620	.380	.410	.770	.810	.030	
40.13	41.15	9.65	10.41	19.56	20.57	0.76	
H	J	K	L				wt
.200	.10	.20	.14				grams
5.08	2.54	5.08	3.56				23.0

Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com
IF/RF MICROWAVE COMPONENTS

For detailed performance specs & shopping online see web site

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.

REV. C
M141218
PSC-8A-4+
HY/TD/CP/AM
130422

8 Way-0° Power Splitter/Combiner

PSC-8A-4+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹						AMP. UNBAL. (dB)	ISOLATION				PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR		
	S-1	S-2	S-3	S-4	S-6	S-8		1-2	1-8	3-4	6-7			S	1	8
5.0	9.51	9.50	9.48	9.48	9.47	9.47	0.04	25.99	38.34	26.38	26.57	0.09	5.0	1.39	1.13	1.14
7.5	9.49	9.49	9.48	9.48	9.46	9.46	0.03	26.08	38.60	26.35	26.44	0.15	7.5	1.38	1.11	1.11
10.0	9.49	9.49	9.47	9.48	9.47	9.46	0.04	26.07	38.65	26.30	26.38	0.17	10.0	1.38	1.10	1.10
15.0	9.49	9.48	9.46	9.47	9.45	9.45	0.04	26.00	38.69	26.19	26.27	0.18	15.0	1.38	1.10	1.10
20.0	9.49	9.49	9.47	9.49	9.47	9.47	0.04	25.95	38.62	26.13	26.21	0.22	20.0	1.38	1.10	1.10
25.0	9.50	9.49	9.47	9.48	9.47	9.46	0.04	25.99	38.52	26.18	26.27	0.32	25.0	1.38	1.11	1.11
30.0	9.48	9.48	9.46	9.47	9.45	9.45	0.04	26.23	38.44	26.44	26.50	0.31	30.0	1.38	1.12	1.12
35.0	9.48	9.48	9.46	9.47	9.45	9.46	0.03	26.80	38.29	27.02	27.09	0.27	35.0	1.38	1.12	1.12
40.0	9.50	9.49	9.47	9.49	9.47	9.47	0.03	27.66	38.22	27.92	27.94	0.32	40.0	1.39	1.13	1.13
45.0	9.53	9.53	9.50	9.51	9.50	9.49	0.04	28.66	38.12	28.96	28.92	0.41	45.0	1.39	1.13	1.13
50.0	9.55	9.56	9.52	9.54	9.52	9.52	0.04	29.71	38.01	30.08	29.99	0.52	50.0	1.40	1.14	1.13
60.0	9.57	9.58	9.55	9.57	9.54	9.55	0.03	31.86	37.85	32.38	32.09	0.53	60.0	1.41	1.14	1.14
70.0	9.59	9.59	9.57	9.59	9.56	9.56	0.03	34.30	37.62	34.97	34.36	0.59	70.0	1.42	1.15	1.15
80.0	9.64	9.65	9.62	9.63	9.61	9.61	0.04	37.01	37.49	37.92	36.72	0.70	80.0	1.44	1.16	1.15
90.0	9.70	9.72	9.68	9.71	9.68	9.68	0.04	39.92	37.35	40.84	38.72	0.79	90.0	1.46	1.17	1.16
100.0	9.77	9.78	9.74	9.78	9.74	9.74	0.05	42.01	37.19	42.08	39.49	0.82	100.0	1.48	1.17	1.17
110.0	9.80	9.81	9.76	9.80	9.77	9.77	0.05	41.82	37.01	40.79	38.66	0.87	110.0	1.50	1.18	1.17
120.0	9.79	9.81	9.77	9.80	9.77	9.77	0.04	39.86	36.83	38.62	37.13	0.94	120.0	1.52	1.18	1.18
130.0	9.80	9.83	9.78	9.81	9.78	9.78	0.05	37.94	36.69	36.60	35.59	1.00	130.0	1.54	1.18	1.18
140.0	9.80	9.84	9.78	9.81	9.78	9.78	0.07	36.27	36.66	35.02	34.25	1.14	140.0	1.56	1.19	1.18
150.0	9.79	9.82	9.78	9.80	9.77	9.77	0.06	34.77	36.24	33.70	33.07	1.22	150.0	1.58	1.19	1.19
160.0	9.77	9.80	9.75	9.78	9.74	9.76	0.06	33.65	36.05	32.66	32.08	1.27	160.0	1.59	1.21	1.20
170.0	9.83	9.85	9.81	9.83	9.80	9.81	0.06	32.78	35.91	31.84	31.29	1.43	170.0	1.61	1.22	1.21
180.0	9.97	10.00	9.95	10.00	9.95	9.96	0.06	32.12	35.83	31.21	30.70	1.53	180.0	1.63	1.23	1.23
190.0	10.07	10.12	10.05	10.10	10.06	10.06	0.08	31.54	35.72	30.67	30.20	1.52	190.0	1.65	1.24	1.23
200.0	10.06	10.10	10.04	10.10	10.05	10.05	0.07	31.00	35.56	30.12	29.67	1.54	200.0	1.67	1.24	1.24
210.0	10.01	10.05	9.99	10.05	10.01	10.01	0.06	30.52	35.36	29.66	29.23	1.61	210.0	1.68	1.24	1.24
220.0	9.95	9.99	9.94	9.99	9.94	9.95	0.05	30.14	35.20	29.28	28.84	1.71	220.0	1.69	1.24	1.23
230.0	9.90	9.94	9.90	9.93	9.89	9.90	0.06	29.84	35.04	28.96	28.51	1.79	230.0	1.70	1.23	1.23
240.0	9.87	9.91	9.87	9.90	9.86	9.87	0.06	29.58	34.89	28.71	28.26	1.92	240.0	1.71	1.24	1.23
250.0	9.88	9.90	9.88	9.89	9.85	9.85	0.07	29.38	34.73	28.49	28.03	2.03	250.0	1.71	1.25	1.24
275.0	10.20	10.24	10.20	10.25	10.21	10.19	0.08	29.36	34.60	28.43	27.93	2.34	275.0	1.71	1.27	1.27
300.0	10.09	10.15	10.10	10.16	10.11	10.10	0.09	29.36	34.23	28.35	27.78	2.50	300.0	1.72	1.27	1.27
325.0	9.96	10.00	9.97	10.02	9.96	9.96	0.08	29.68	33.91	28.57	27.90	2.68	325.0	1.70	1.26	1.26
350.0	10.04	10.09	10.07	10.09	10.04	10.04	0.09	30.42	33.63	29.15	28.32	2.98	350.0	1.66	1.27	1.27
375.0	10.22	10.28	10.25	10.30	10.23	10.22	0.11	31.81	33.52	30.25	29.15	3.24	375.0	1.61	1.27	1.27
400.0	10.02	10.08	10.04	10.11	10.04	10.03	0.12	33.51	33.16	31.54	30.06	3.54	400.0	1.56	1.25	1.26
425.0	10.01	10.06	10.03	10.09	10.01	10.02	0.13	36.56	32.92	33.74	31.51	3.77	425.0	1.50	1.25	1.26
450.0	10.07	10.14	10.12	10.16	10.10	10.08	0.14	42.38	32.81	37.15	33.57	4.24	450.0	1.41	1.24	1.25
475.0	10.01	10.09	10.04	10.12	10.04	10.02	0.17	46.14	32.61	41.22	35.93	4.49	475.0	1.33	1.23	1.24
500.0	10.05	10.14	10.07	10.18	10.09	10.07	0.18	37.15	32.52	38.45	37.11	4.90	500.0	1.25	1.21	1.24

¹Total Loss = Insertion Loss + 9dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS








REV. X2
PSC-8A-4+
6/21/2010
Page 1 of 1

8 Way-0° Power Splitter/Combiner

PSC-8A-4+

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 • Fax (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. X2
PSC-8A-4+
6/21/2010
Page 1 of 1

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
E10	1.580 (40.13)	1.620 (41.15)	.380 (9.65)	.410 (10.41)	.770 (19.56)	.810 (20.57)	.030 (.76)	.200 (5.08)	.10 (2.54)	.20 (5.08)	.14 (3.56)	23.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead Pins 4 & 5. Pin numbers do not appear on unit, for reference only.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Gross Leak	125°C Bubble Test	MIL-STD-202, Method 112, Condition D
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D