

Bandpass Filter

50Ω 624 to 680 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W at 25°C

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

RF IN	2
RF OUT	6
GROUND	1,3,4,5,7,8

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J
.350	.350	.100	.175	.075	.100	.110	.040	.080
8.89	8.89	2.54	4.45	1.91	2.54	2.79	1.02	2.03
K	L	M	N	P	Q	R		wt
.050	.040	.195	.390	.120	.390	.070		grams
1.27	1.02	4.95	9.91	3.05	9.91	1.78		0.25

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-332 Suggested PCB Layout (PL-176)



NOTES:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- good VSWR, 1.5:1 typ. @ passband
- small size 0.35" x 0.35"
- shielded case
- aqueous washable

Applications

- harmonic rejection
- transmitters / receivers
- navigation



Generic photo used for illustration purposes only

CASE STYLE: GP731

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500, 1000


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 7dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss > 35dB		Passband		Stopband
F _c	F ₁ - F ₂	F ₃	F ₄	F ₅	F ₆	Typ.	Max.	Typ.
652	624 - 680	550	760	520	810 - 1000	1.5	-	18

Typical Frequency Response





Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1	113.30	269.77
200	74.50	266.10
500	42.61	46.62
520	38.59	37.21
550	31.13	23.35
580	20.57	10.30
590	16.05	6.51
610	7.39	1.63
624	5.10	1.27
650	4.09	1.26
652	4.06	1.25
680	4.21	1.43
710	7.72	3.19
730	15.04	8.55
760	25.93	19.29
770	29.21	22.80
810	43.00	35.35
1000	41.53	64.23



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp









Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	87.99	96.86	109.10	0.05	0.05	0.05	0.05	0.05	0.05
10	103.13	106.03	103.34	0.04	0.04	0.04	0.05	0.05	0.05
50	114.68	107.52	110.28	0.03	0.03	0.03	0.05	0.06	0.06
105	112.07	107.74	103.48	0.02	0.04	0.04	0.05	0.07	0.07
110	97.11	100.91	107.18	0.02	0.04	0.04	0.05	0.07	0.07
140	99.12	98.33	92.40	0.02	0.05	0.05	0.05	0.07	0.08
200	90.89	90.37	88.39	0.03	0.06	0.07	0.06	0.09	0.10
260	85.02	86.77	86.55	0.05	0.09	0.10	0.07	0.11	0.13
305	82.84	86.41	86.26	0.06	0.11	0.12	0.08	0.13	0.14
340	83.56	87.61	86.91	0.08	0.13	0.14	0.09	0.14	0.16
370	86.33	98.41	95.26	0.10	0.15	0.17	0.11	0.16	0.18
400	90.67	82.07	82.61	0.11	0.17	0.19	0.12	0.18	0.20
410	82.93	78.20	78.18	0.12	0.18	0.20	0.13	0.19	0.21
426	75.18	72.54	72.54	0.14	0.20	0.22	0.14	0.21	0.23
446	68.08	66.73	66.75	0.17	0.24	0.26	0.16	0.23	0.25
470	60.50	59.72	59.82	0.21	0.29	0.31	0.20	0.27	0.30
492	53.63	53.13	53.14	0.27	0.36	0.39	0.25	0.33	0.36
500	51.04	50.62	50.59	0.30	0.39	0.43	0.27	0.36	0.40
520	44.11	43.79	43.70	0.42	0.53	0.58	0.36	0.47	0.51
530	40.31	40.01	39.87	0.51	0.63	0.69	0.43	0.55	0.60
536	37.89	37.58	37.42	0.57	0.71	0.78	0.49	0.61	0.68
550	31.70	31.38	31.15	0.80	0.99	1.09	0.68	0.84	0.93
552	30.74	30.42	30.17	0.85	1.04	1.15	0.72	0.89	0.99
560	26.73	26.38	26.10	1.10	1.34	1.50	0.93	1.15	1.28
570	21.20	20.83	20.52	1.64	2.01	2.27	1.41	1.74	1.97
572	20.02	19.66	19.35	1.80	2.22	2.50	1.56	1.93	2.19
588	10.35	10.30	10.23	5.07	6.22	7.07	4.98	6.14	7.03
595	7.05	7.37	7.54	9.07	10.65	11.74	10.18	12.06	13.26
603	5.04	5.62	5.97	15.27	16.53	17.45	22.92	19.04	17.01
618	3.99	4.62	5.00	18.48	19.54	19.82	12.15	11.63	11.28
624	3.88	4.50	4.87	15.19	15.29	15.04	10.84	10.58	10.39
630	3.83	4.43	4.80	12.40	12.38	12.17	10.10	10.05	10.01
650	3.66	4.22	4.57	9.32	9.43	9.42	12.15	13.09	13.86
652	3.64	4.20	4.55	9.31	9.42	9.41	12.84	13.98	14.92
660	3.58	4.16	4.52	9.41	9.47	9.44	16.23	18.36	20.25
667	3.60	4.20	4.58	9.41	9.44	9.40	16.87	18.11	18.63
680	3.79	4.44	4.87	9.64	9.90	10.03	12.41	12.66	12.66
693	4.15	4.99	5.57	14.26	14.74	14.57	11.74	11.64	11.35
700	4.80	5.88	6.63	16.80	14.05	12.44	10.64	9.82	9.21
715	9.13	10.55	11.52	4.62	4.42	4.23	4.07	3.99	3.88
727	14.26	15.57	16.47	2.11	2.23	2.25	2.03	2.18	2.22
740	19.59	20.73	21.54	1.21	1.37	1.43	1.22	1.41	1.47
742	20.36	21.48	22.27	1.13	1.30	1.35	1.15	1.34	1.40
743	20.74	21.85	22.64	1.10	1.26	1.32	1.12	1.30	1.37
750	23.32	24.37	25.12	0.90	1.06	1.12	0.93	1.11	1.17
760	26.79	27.78	28.50	0.72	0.88	0.94	0.75	0.92	0.98
770	30.12	31.05	31.75	0.61	0.75	0.81	0.63	0.79	0.85
777	32.41	33.32	34.01	0.55	0.69	0.74	0.57	0.72	0.78
798	39.57	40.42	41.16	0.44	0.57	0.61	0.44	0.58	0.63
800	40.30	41.15	41.90	0.43	0.56	0.60	0.43	0.57	0.62
810	44.33	45.16	45.95	0.40	0.52	0.56	0.40	0.53	0.58
826	52.84	53.26	53.79	0.36	0.47	0.52	0.35	0.48	0.52
836	57.02	56.35	55.59	0.34	0.45	0.49	0.33	0.45	0.50
850	51.97	51.75	51.33	0.32	0.43	0.47	0.31	0.42	0.46
856	50.03	50.06	49.83	0.31	0.42	0.46	0.30	0.41	0.45
862	48.55	48.73	48.61	0.31	0.42	0.45	0.29	0.40	0.44
870	47.11	47.43	47.38	0.30	0.40	0.44	0.28	0.39	0.43
924	42.47	42.96	43.09	0.27	0.36	0.40	0.23	0.34	0.37
994	40.00	40.51	40.65	0.24	0.33	0.36	0.20	0.30	0.33
1000	39.89	40.44	40.57	0.24	0.33	0.36	0.20	0.30	0.33


Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
624	9.81	9.63	9.51
625	9.69	9.52	9.41
626	9.58	9.42	9.31
627	9.47	9.31	9.21
628	9.36	9.22	9.12
629	9.26	9.12	9.03
630	9.16	9.03	8.95
631	9.06	8.95	8.87
632	8.97	8.87	8.79
633	8.89	8.79	8.72
634	8.81	8.72	8.66
635	8.74	8.65	8.60
636	8.67	8.59	8.54
637	8.60	8.53	8.49
638	8.54	8.48	8.45
639	8.49	8.44	8.40
640	8.44	8.39	8.37
641	8.39	8.36	8.34
642	8.35	8.32	8.31
643	8.32	8.30	8.29
644	8.29	8.27	8.27
645	8.26	8.25	8.25
646	8.24	8.24	8.24
647	8.22	8.22	8.23
648	8.21	8.21	8.22
649	8.20	8.21	8.22
650	8.19	8.20	8.22
651	8.19	8.20	8.21
652	8.18	8.20	8.22
653	8.18	8.20	8.22
654	8.19	8.20	8.22
655	8.19	8.21	8.23
656	8.19	8.21	8.23
657	8.20	8.22	8.24
658	8.20	8.22	8.24
659	8.21	8.23	8.25
660	8.21	8.23	8.25
661	8.22	8.24	8.26
662	8.22	8.24	8.26
663	8.23	8.24	8.26
664	8.23	8.25	8.27
665	8.23	8.25	8.28
666	8.24	8.26	8.28
667	8.24	8.26	8.29
668	8.24	8.27	8.30
669	8.25	8.27	8.31
670	8.25	8.28	8.32
671	8.26	8.30	8.34
672	8.27	8.31	8.36
673	8.28	8.33	8.38
674	8.29	8.35	8.41
675	8.31	8.38	8.44
676	8.33	8.41	8.48
677	8.36	8.45	8.52
678	8.39	8.49	8.57
679	8.44	8.54	8.63
680	8.48	8.60	8.69

Typical Performance Curves



Typical Performance Curves



Outline Dimensions

GP731



CASE #	A	B	C	D	E	F	G	H	J	K	L	M
GP731	.350 (8.89)	.350 (8.89)	.100 (2.54)	.175 (4.45)	.075 (1.91)	.100 (2.54)	.110 (2.79)	.040 (1.02)	.080 (2.03)	.050 (1.27)	.040 (1.02)	.195 (4.95)

CASE #	N	P	Q	R	WT. GRAM
GP731	.390 (9.91)	.120 (3.05)	.390 (9.91)	.070 (1.78)	.4 +0.3 -0.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:

For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F78



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
16	12	7	10
			20
			50
			100
			200
		13	500, 1000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	R59289	NEW RELEASE (FROM RAVON)	02/05	DK	HH
A	M101151	ADDED "RBP" & CORRECTED PIN	10/10/05	MMG	DJ
		CONNECTION TO DESCRIPTION OF PL-DWG.			
B	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/20/06	GT	IL

SUGGESTED MOUNTING CONFIGURATION

FOR GP731 CASE STYLE, "qf" PIN CONNECTION.



- NOTES:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS ±

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±

INITIALS

DATE

DRAWN DK (RAVON) 10 FEB 05

CHECKED RZ (RAVON) 10 FEB 05

APPROVED HH (RAVON) 10 FEB 05

Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, qf, GP731, RBP, TB-332

SIZE A

CODE IDENT 15542

DRAWING NO: 98-PL-176

REV: B

FILE: 98PL176

SCALE: 5:1

SHEET: 1 OF 1

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit



TB-332



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215