

2 Way-90° 50Ω 1200 to 2200 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	17.5W* max.

* Derate linearly to 3.5W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.


Pin Connections

SUM PORT	2
PORT 1 (0°)	8
PORT 2 (+90°)	4
GROUND	1,3,5,7
50 OHM TERM EXTERNAL	6

Outline Drawing




PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	
.150	.150	.032	.008	.036	.018	.062	.028	.022	
3.81	3.81	0.81	0.20	0.91	0.46	1.57	0.71	0.56	
K	L	M	N	P	Q	R	S	T	wt
.017	.014	.036	.018	.062	.028	.037	.017	.014	grams
0.43	0.36	0.91	0.46	1.57	0.71	0.94	0.43	0.36	0.05

Demo Board MCL P/N: TB-302+
Suggested PCB Layout (PL-128)

NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
4. DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- low insertion loss, 0.4 dB typ.
- high isolation, 25 dB typ.
- LTCC construction
- excellent temperature stability
- small size, 0.15" X 0.15"
- aqueous washable
- protected by U.S. Patent 7,030,713

Applications

- WCDMA • defense
- PCS
- DECT
- PHS
- radar




Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) Avg. of Coupled Outputs ABOVE 3 dB		PHASE UNBALANCE (Degrees)		AMPLITUDE UNBALANCE (dB)	
f_L - f_U	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.
1200-2200								
1200-1400	32	24	0.4	0.6	1	3	0.4	1.0
1400-1800	35	20	0.4	0.7	1	3	0.5	0.85
1800-2200	23	16	0.6	0.9	1	5	0.5	0.9


Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
1200.00	3.06	3.64	0.58	30.83	90.74	1.03	1.16	1.19
1300.00	3.28	3.43	0.16	33.49	91.05	1.01	1.18	1.20
1350.00	3.37	3.35	0.03	34.64	91.20	1.02	1.19	1.20
1400.00	3.47	3.27	0.20	35.21	91.33	1.04	1.19	1.20
1500.00	3.63	3.16	0.47	33.11	91.51	1.08	1.21	1.21
1550.00	3.70	3.12	0.58	31.38	91.57	1.10	1.22	1.21
1600.00	3.76	3.09	0.67	29.70	91.60	1.12	1.24	1.22
1700.00	3.84	3.07	0.77	27.04	91.58	1.15	1.27	1.23
1750.00	3.87	3.08	0.79	25.86	91.55	1.17	1.28	1.24
1800.00	3.89	3.10	0.79	24.69	91.48	1.18	1.29	1.25
1900.00	3.89	3.18	0.71	22.58	91.25	1.23	1.31	1.28
1950.00	3.87	3.24	0.63	21.66	91.11	1.25	1.32	1.30
2000.00	3.83	3.32	0.52	20.85	90.94	1.27	1.33	1.32
2100.00	3.73	3.52	0.21	19.49	90.53	1.31	1.35	1.35
2200.00	3.56	3.78	0.22	18.38	90.13	1.33	1.37	1.40

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



2 Way-90° Power Splitter/Combiner

QCC-20+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. From 90° (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2				S	1	2
400	9.72	0.68	9.05	0.98	26.45	1.06	1.12	1.06
500	8.16	0.94	7.22	0.91	25.43	1.07	1.14	1.07
600	6.99	1.22	5.76	0.77	24.92	1.07	1.15	1.07
700	6.08	1.52	4.57	0.64	24.82	1.08	1.16	1.07
800	5.38	1.81	3.56	0.46	25.02	1.08	1.16	1.07
900	4.80	2.10	2.71	0.33	25.47	1.08	1.15	1.06
1000	4.35	2.37	1.97	0.21	26.03	1.08	1.14	1.05
1050	4.17	2.50	1.66	0.18	26.36	1.08	1.14	1.05
1100	3.99	2.63	1.37	0.13	26.75	1.08	1.13	1.04
1150	3.84	2.74	1.10	0.12	27.06	1.09	1.13	1.04
1200	3.71	2.86	0.85	0.09	27.32	1.09	1.13	1.03
1250	3.59	2.97	0.62	0.10	27.53	1.09	1.12	1.03
1300	3.48	3.06	0.42	0.09	27.68	1.10	1.12	1.03
1350	3.39	3.16	0.23	0.13	27.72	1.11	1.12	1.04
1400	3.31	3.24	0.07	0.15	27.59	1.11	1.12	1.04
1450	3.25	3.32	0.08	0.18	27.32	1.12	1.12	1.05
1500	3.19	3.39	0.20	0.26	27.01	1.13	1.12	1.05
1550	3.15	3.45	0.30	0.31	26.51	1.14	1.12	1.06
1600	3.12	3.51	0.39	0.43	25.94	1.15	1.13	1.07
1700	3.09	3.58	0.49	0.64	24.79	1.17	1.14	1.09
1800	3.10	3.62	0.52	0.92	23.51	1.20	1.16	1.11
1850	3.12	3.63	0.51	1.09	22.91	1.22	1.17	1.13
1900	3.15	3.62	0.47	1.24	22.28	1.23	1.18	1.14
2000	3.26	3.58	0.32	1.67	21.13	1.26	1.20	1.17
2050	3.32	3.55	0.22	1.87	20.57	1.28	1.21	1.19
2100	3.41	3.50	0.10	2.10	20.03	1.30	1.23	1.21
2150	3.50	3.45	0.05	2.37	19.49	1.32	1.24	1.24
2200	3.62	3.39	0.23	2.57	19.00	1.34	1.26	1.26
2250	3.76	3.32	0.44	2.83	18.54	1.36	1.28	1.28
2300	3.91	3.24	0.67	3.12	18.07	1.39	1.30	1.31
2350	4.07	3.15	0.92	3.39	17.62	1.42	1.32	1.34
2400	4.27	3.06	1.21	3.73	17.23	1.45	1.35	1.38
2450	4.50	2.96	1.53	4.03	16.85	1.48	1.38	1.41
2500	4.75	2.86	1.89	4.32	16.48	1.52	1.41	1.45
2550	5.02	2.76	2.26	4.64	16.16	1.56	1.45	1.49
2600	5.34	2.66	2.68	4.99	15.88	1.60	1.50	1.54

¹ Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2

QCC-20+

110130

Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



2 Way-90° Power Splitter/Combiner

QCC-20+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -55°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. From 90° (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2				S	1	2
400	9.68	0.60	9.08	1.53	26.75	1.05	1.12	1.05
500	8.10	0.85	7.25	1.65	25.67	1.06	1.13	1.06
600	6.90	1.12	5.78	1.72	25.10	1.07	1.14	1.06
700	5.98	1.41	4.58	1.79	24.92	1.08	1.15	1.06
800	5.26	1.69	3.56	1.82	25.13	1.08	1.15	1.06
900	4.67	1.97	2.71	1.88	25.55	1.08	1.14	1.05
1000	4.21	2.23	1.97	1.98	26.05	1.09	1.14	1.05
1050	4.01	2.36	1.65	2.03	26.45	1.08	1.13	1.04
1100	3.83	2.48	1.35	2.12	26.96	1.08	1.13	1.04
1150	3.67	2.60	1.07	2.20	27.37	1.09	1.12	1.03
1200	3.53	2.71	0.83	2.26	27.66	1.09	1.12	1.03
1250	3.41	2.81	0.61	2.37	27.85	1.09	1.12	1.03
1300	3.30	2.90	0.40	2.47	28.07	1.10	1.11	1.03
1350	3.19	3.00	0.20	2.60	28.20	1.10	1.11	1.03
1400	3.11	3.08	0.03	2.74	27.91	1.11	1.12	1.03
1450	3.05	3.16	0.11	2.87	27.44	1.12	1.12	1.04
1500	2.98	3.23	0.25	3.06	27.00	1.13	1.12	1.04
1550	2.94	3.28	0.34	3.22	26.32	1.15	1.12	1.05
1600	2.90	3.34	0.44	3.42	25.62	1.16	1.13	1.06
1700	2.86	3.41	0.55	3.85	24.35	1.18	1.14	1.08
1800	2.86	3.45	0.59	4.33	22.85	1.22	1.16	1.11
1850	2.87	3.45	0.58	4.61	22.20	1.23	1.17	1.13
1900	2.90	3.45	0.55	4.85	21.55	1.25	1.18	1.14
2000	2.99	3.41	0.42	5.47	20.35	1.29	1.19	1.18
2050	3.04	3.37	0.33	5.78	19.90	1.30	1.20	1.19
2100	3.12	3.33	0.22	6.10	19.46	1.31	1.22	1.21
2150	3.21	3.28	0.07	6.47	18.90	1.34	1.23	1.24
2200	3.31	3.22	0.09	6.76	18.45	1.35	1.24	1.26
2250	3.43	3.14	0.29	7.13	18.09	1.37	1.25	1.28
2300	3.57	3.07	0.50	7.54	17.68	1.40	1.28	1.31
2350	3.72	2.97	0.75	7.93	17.27	1.43	1.31	1.34
2400	3.91	2.88	1.03	8.35	16.91	1.45	1.34	1.37
2450	4.12	2.77	1.34	8.70	16.58	1.48	1.37	1.40
2500	4.34	2.68	1.66	9.07	16.29	1.52	1.39	1.44
2550	4.59	2.57	2.03	9.61	15.99	1.56	1.44	1.48
2600	4.89	2.45	2.44	9.97	15.76	1.58	1.51	1.51

¹ Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2
QCC-20+
110130
Page 2 of 3



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits®



2 Way-90° Power Splitter/Combiner

QCC-20+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +100°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. From 90° (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2				S	1	2
400	9.72	0.74	8.99	0.96	26.28	1.07	1.13	1.08
500	8.17	1.00	7.17	0.85	25.32	1.07	1.15	1.08
600	7.01	1.29	5.72	0.67	24.94	1.07	1.16	1.08
700	6.12	1.59	4.53	0.49	24.90	1.07	1.17	1.08
800	5.42	1.89	3.53	0.23	25.15	1.07	1.16	1.07
900	4.86	2.18	2.69	0.04	25.59	1.07	1.16	1.06
1000	4.43	2.46	1.96	0.11	26.06	1.08	1.15	1.05
1050	4.24	2.59	1.65	0.19	26.31	1.08	1.15	1.04
1100	4.07	2.72	1.35	0.26	26.55	1.09	1.14	1.04
1150	3.92	2.84	1.08	0.30	26.75	1.09	1.14	1.04
1200	3.80	2.96	0.83	0.36	26.90	1.10	1.13	1.04
1250	3.68	3.07	0.62	0.38	27.02	1.10	1.13	1.04
1300	3.59	3.17	0.42	0.40	27.05	1.11	1.12	1.04
1350	3.49	3.27	0.23	0.39	27.03	1.12	1.12	1.05
1400	3.43	3.36	0.07	0.40	26.94	1.12	1.12	1.05
1450	3.37	3.43	0.07	0.38	26.75	1.13	1.11	1.06
1500	3.31	3.50	0.19	0.33	26.54	1.14	1.11	1.06
1550	3.28	3.56	0.28	0.31	26.20	1.14	1.12	1.07
1600	3.25	3.62	0.37	0.23	25.82	1.15	1.12	1.08
1700	3.23	3.69	0.46	0.06	24.97	1.16	1.13	1.09
1800	3.25	3.73	0.48	0.18	23.91	1.18	1.15	1.11
1850	3.28	3.74	0.46	0.30	23.37	1.20	1.17	1.13
1900	3.31	3.73	0.42	0.43	22.78	1.21	1.18	1.14
2000	3.43	3.69	0.26	0.80	21.61	1.24	1.21	1.17
2050	3.50	3.66	0.15	0.97	21.01	1.26	1.22	1.19
2100	3.59	3.61	0.02	1.16	20.44	1.28	1.23	1.21
2150	3.70	3.56	0.14	1.42	19.88	1.30	1.25	1.23
2200	3.83	3.51	0.32	1.58	19.34	1.33	1.27	1.26
2250	3.97	3.43	0.54	1.84	18.82	1.35	1.29	1.29
2300	4.14	3.36	0.78	2.07	18.31	1.38	1.31	1.32
2350	4.32	3.28	1.05	2.33	17.80	1.42	1.32	1.35
2400	4.53	3.19	1.34	2.63	17.37	1.45	1.35	1.38
2450	4.77	3.09	1.67	2.93	16.96	1.49	1.38	1.42
2500	5.04	3.00	2.04	3.18	16.55	1.53	1.41	1.47
2550	5.33	2.90	2.43	3.48	16.22	1.57	1.45	1.51
2600	5.67	2.80	2.86	3.82	15.92	1.62	1.49	1.56

¹ Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2

QCC-20+

110130

Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




2 Way-90° Power Splitter/Combiner


QCC-20+

Typical Performance Curves


Total Loss




Total Loss S-1 vs. TEMPERATURE




Amplitude Unbalance vs. TEMPERATURE



Phase Unbalance vs. TEMPERATURE



Isolation 1-2 vs. TEMPERATURE



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see






REV. X2
QCC-20+
110130
Page 1 of 2

2 Way-90° Power Splitter/Combiner


QCC-20+

Typical Performance Curves




GF981
GF995

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K
GF981	.150 (3.81)	.150 (3.81)	.032 (0.81)	.008 (0.20)	.036 (0.91)	.018 (0.46)	.062 (1.57)	.028 (0.71)	.022 (0.56)	.017 (0.43)
GF995			.065 MAX (1.65)							

CASE #	L	M	N	P	Q	R	S	T	WT. GRAM
GF981	.014 (0.36)	.036 (0.91)	.018 (0.46)	.062 (1.57)	.028 (0.71)	.037 (0.94)	.017 (0.43)	.014 (0.36)	.05
GF995									.06

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Open style, Ceramic Base.
- Termination finish: Palladium Silver.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F68



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
12	8	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000
		13	Standard	2000
				3000
				4000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M86087	NEW RELEASE	04/14/03	GF	ABD
A	M86801	CHG. NAME OF MODEL FROM TCQ TO QCC	05/23/03	MMG	ABD
B	M93045	TB-302 WAS TB-250	07/06/04	MMG	ABD
C	M102713	ADDED"...WITH SMOBC"	01/16/06	GF	IL

SUGGESTED MOUNTING CONFIGURATION
FOR GF981 CASE STYLE, "nz" PIN CONNECTION



NOTES: 1.COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" $\pm$ 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2.BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
 2 PL DECIMALS $\pm$
 3 PL DECIMALS $\pm$.005
 ANGLES $\pm$
 FRACTIONS $\pm$

INITIALS

DATE

DRAWN

GF

03/19/03

CHECKED

IL

04/12/03

APPROVED

ABD

04/14/03



Mini-Circuits®

13 Neptune Avenue
 Brooklyn NY 11235

PL, nz, GF981, QCC, TB-302

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-128

REV:

C

FILE: 98PL128


SCALE:

8:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-302+



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215