



Mini-Circuits®

ULTRA-SMALL CERAMIC


## Power Splitter/Combiner

QCN-3+

2 Way-90° 50Ω 220 to 470 MHz

## FEATURES

- Low insertion loss, 0.4 dB typ.
- High isolation, 25 dB typ.
- Wrap-around terminal for excellent solderability
- Ultra small, 0.12"X0.06"X0.035"



Generic photo used for illustration purposes only

CASE STYLE: FV1206-1

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## APPLICATIONS

- Balanced amplifiers
- Modulators
- VHF
- Defense communication

## ELECTRICAL SPECIFICATIONS AT 25°C


| Parameter                    | Frequency (MHz) | Min. | Typ. | Max. | Unit   |
|------------------------------|-----------------|------|------|------|--------|
| Frequency Range              |                 | 220  |      | 470  | MHz    |
| Insertion Loss, above 3.0 dB | 220-470         |      | 0.6  | 0.8  | dB     |
|                              | 270-350         |      | 0.4  | 0.7  |        |
|                              | 350-450         |      | 0.6  | 0.8  |        |
| Isolation                    | 220-470         | 18   | 24   |      | dB     |
|                              | 270-350         | 18   | 25   |      |        |
|                              | 350-450         | 20   | 30   |      |        |
| Phase Unbalance              | 220-470         |      | 1    | 8    | Degree |
|                              | 270-350         |      | 3    | 5    |        |
|                              | 350-450         |      | 5    | 8    |        |
| Amplitude Unbalance          | 220-470         |      | 0.5  | 1.7  | dB     |
|                              | 270-350         |      | 0.7  | 1.0  |        |
|                              | 350-450         |      | 0.5  | 1.0  |        |
| VSWR                         | 220-470         |      | 1.2  |      | (:1)   |
|                              | 270-350         |      | 1.2  |      |        |
|                              | 350-450         |      | 1.2  |      |        |

## MAXIMUM RATINGS

| Parameter                   | Ratings        |
|-----------------------------|----------------|
| Operating Temperature       | -55°C to 100°C |
| Storage Temperature         | -55°C to 100°C |
| Power Input (as a splitter) | 15W* max.      |

\* Derate linearly to 7W at 100°C ambient.  
Permanent damage may occur if any of these limits are exceeded.

## ELECTRICAL SCHEMATIC



Mini-Circuits®

[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)

REV. F  
ECO-010256  
QCN-3+  
AD/TD/CP/AM  
220929

PAGE 1 OF 3



Mini-Circuits®

ULTRA-SMALL CERAMIC

## Power Splitter/Combiner

QCN-3+


2 Way-90° 50Ω 220 to 470 MHz

## PIN CONNECTIONS

|                      |     |
|----------------------|-----|
| SUM PORT             | 1   |
| PORT 1 (0°)          | 4   |
| PORT 2 (+90°)        | 6   |
| GROUND               | 2,5 |
| 50 OHM TERM EXTERNAL | 3   |

PRODUCT MARKING: SB

DEMO BOARD MCL P/N: TB-255  
SUGGESTED PCB LAYOUT (PL-131)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS  $0.020" \pm 0.0015"$ ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.


2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## OUTLINE DRAWING



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm 0.002$

## OUTLINE DIMENSIONS (Inches/mm)

| A    | B    | C    | D    | E     | F    |
|------|------|------|------|-------|------|
| .126 | .063 | .035 | .024 | .022  | .011 |
| 3.20 | 1.60 | 0.89 | 0.61 | 0.56  | 0.28 |
| G    | H    | J    | K    | wt    |      |
| .039 | .024 | .042 | .123 | grams |      |
| 0.99 | 0.61 | 1.07 | 3.12 | .020  |      |

## TAPE &amp; REEL INFORMATION: F75





Mini-Circuits

ULTRA-SMALL CERAMIC

## Power Splitter/Combiner




QCN-3+

2 Way-90° 50Ω 220 to 470 MHz

## TYPICAL PERFORMANCE DATA

| Frequency<br>(MHz) | Total Loss <sup>1</sup><br>(dB) |      | Amplitude<br>Unbalance<br>(dB) | Isolation<br>(dB) | Phase<br>Unbalance<br>(deg.) | VSWR<br>(:1) |      |      |
|--------------------|---------------------------------|------|--------------------------------|-------------------|------------------------------|--------------|------|------|
|                    | S-1                             | S-2  |                                |                   |                              | S            | 1    | 2    |
| 220.00             | 3.91                            | 3.00 | 0.91                           | 23.23             | 90.40                        | 1.07         | 1.12 | 1.07 |
| 230.00             | 3.77                            | 3.11 | 0.67                           | 23.41             | 90.55                        | 1.06         | 1.12 | 1.06 |
| 250.00             | 3.55                            | 3.31 | 0.23                           | 23.85             | 90.86                        | 1.05         | 1.11 | 1.06 |
| 260.00             | 3.45                            | 3.41 | 0.05                           | 24.11             | 91.02                        | 1.05         | 1.11 | 1.05 |
| 270.00             | 3.37                            | 3.49 | 0.12                           | 24.37             | 91.18                        | 1.04         | 1.10 | 1.05 |
| 290.00             | 3.24                            | 3.64 | 0.39                           | 24.96             | 91.53                        | 1.04         | 1.10 | 1.04 |
| 310.00             | 3.16                            | 3.76 | 0.60                           | 25.67             | 91.88                        | 1.03         | 1.09 | 1.03 |
| 330.00             | 3.12                            | 3.83 | 0.72                           | 26.46             | 92.26                        | 1.03         | 1.08 | 1.03 |
| 350.00             | 3.11                            | 3.88 | 0.77                           | 27.38             | 92.67                        | 1.04         | 1.08 | 1.02 |
| 370.00             | 3.14                            | 3.88 | 0.74                           | 28.47             | 93.12                        | 1.05         | 1.07 | 1.02 |
| 390.00             | 3.22                            | 3.85 | 0.63                           | 29.82             | 93.63                        | 1.07         | 1.07 | 1.02 |
| 410.00             | 3.35                            | 3.78 | 0.42                           | 31.55             | 94.16                        | 1.09         | 1.07 | 1.01 |
| 430.00             | 3.55                            | 3.66 | 0.11                           | 33.99             | 94.80                        | 1.11         | 1.07 | 1.01 |
| 450.00             | 3.82                            | 3.50 | 0.32                           | 37.16             | 95.56                        | 1.14         | 1.07 | 1.02 |
| 470.00             | 4.19                            | 3.29 | 0.90                           | 38.74             | 96.48                        | 1.17         | 1.08 | 1.02 |

1. Total Loss = Insertion Loss + 3 dB splitter loss.



## NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



# 2 Way-90° Power Splitter/Combiner

QCN-3+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

| FREQ.<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |      | AMP.<br>UNBAL.<br>(dB) | PHASE UNBAL.<br>From 90°<br>(deg.) | ISOLATION<br>(dB)<br>1-2 | VSWR<br>(:1) |      |      |
|----------------|---------------------------------|------|------------------------|------------------------------------|--------------------------|--------------|------|------|
|                | S-1                             | S-2  |                        |                                    |                          | S            | 1    | 2    |
| 100            | 1.12                            | 7.76 | 6.64                   | 0.86                               | 23.48                    | 1.09         | 1.09 | 1.12 |
| 125            | 1.52                            | 6.41 | 4.89                   | 0.68                               | 22.51                    | 1.10         | 1.10 | 1.13 |
| 150            | 1.91                            | 5.43 | 3.52                   | 0.46                               | 22.02                    | 1.10         | 1.11 | 1.14 |
| 175            | 2.30                            | 4.72 | 2.42                   | 0.19                               | 21.86                    | 1.10         | 1.10 | 1.14 |
| 200            | 2.64                            | 4.19 | 1.54                   | 0.11                               | 21.92                    | 1.09         | 1.10 | 1.14 |
| 210            | 2.78                            | 4.01 | 1.24                   | 0.23                               | 22.01                    | 1.08         | 1.09 | 1.14 |
| 220            | 2.91                            | 3.86 | 0.95                   | 0.38                               | 22.12                    | 1.08         | 1.09 | 1.13 |
| 230            | 3.02                            | 3.72 | 0.70                   | 0.52                               | 22.25                    | 1.07         | 1.09 | 1.13 |
| 240            | 3.13                            | 3.60 | 0.47                   | 0.70                               | 22.40                    | 1.07         | 1.08 | 1.13 |
| 250            | 3.23                            | 3.50 | 0.26                   | 0.84                               | 22.57                    | 1.06         | 1.08 | 1.12 |
| 260            | 3.34                            | 3.41 | 0.07                   | 0.98                               | 22.77                    | 1.06         | 1.08 | 1.12 |
| 270            | 3.42                            | 3.33 | 0.09                   | 1.16                               | 22.98                    | 1.05         | 1.07 | 1.12 |
| 280            | 3.50                            | 3.26 | 0.24                   | 1.33                               | 23.21                    | 1.05         | 1.07 | 1.12 |
| 290            | 3.58                            | 3.20 | 0.37                   | 1.51                               | 23.46                    | 1.04         | 1.07 | 1.11 |
| 300            | 3.64                            | 3.16 | 0.49                   | 1.69                               | 23.72                    | 1.03         | 1.06 | 1.11 |
| 310            | 3.70                            | 3.12 | 0.58                   | 1.87                               | 24.03                    | 1.03         | 1.06 | 1.11 |
| 320            | 3.75                            | 3.09 | 0.65                   | 2.09                               | 24.35                    | 1.02         | 1.05 | 1.10 |
| 330            | 3.78                            | 3.07 | 0.71                   | 2.28                               | 24.71                    | 1.02         | 1.05 | 1.10 |
| 340            | 3.81                            | 3.06 | 0.75                   | 2.51                               | 25.10                    | 1.02         | 1.05 | 1.10 |
| 350            | 3.83                            | 3.06 | 0.77                   | 2.72                               | 25.48                    | 1.02         | 1.04 | 1.10 |
| 360            | 3.84                            | 3.07 | 0.77                   | 2.97                               | 25.94                    | 1.03         | 1.04 | 1.09 |
| 370            | 3.83                            | 3.09 | 0.74                   | 3.19                               | 26.45                    | 1.03         | 1.04 | 1.09 |
| 380            | 3.82                            | 3.12 | 0.70                   | 3.45                               | 27.04                    | 1.04         | 1.04 | 1.09 |
| 390            | 3.80                            | 3.17 | 0.63                   | 3.73                               | 27.69                    | 1.05         | 1.04 | 1.09 |
| 400            | 3.77                            | 3.22 | 0.54                   | 4.01                               | 28.42                    | 1.06         | 1.03 | 1.09 |
| 410            | 3.73                            | 3.29 | 0.44                   | 4.31                               | 29.26                    | 1.07         | 1.03 | 1.09 |
| 420            | 3.68                            | 3.38 | 0.30                   | 4.64                               | 30.36                    | 1.08         | 1.03 | 1.09 |
| 430            | 3.61                            | 3.48 | 0.14                   | 4.97                               | 31.64                    | 1.10         | 1.03 | 1.10 |
| 440            | 3.54                            | 3.60 | 0.06                   | 5.38                               | 33.32                    | 1.11         | 1.04 | 1.10 |
| 450            | 3.46                            | 3.74 | 0.28                   | 5.81                               | 35.56                    | 1.13         | 1.04 | 1.10 |
| 460            | 3.37                            | 3.90 | 0.54                   | 6.26                               | 38.86                    | 1.14         | 1.04 | 1.11 |
| 470            | 3.26                            | 4.10 | 0.84                   | 6.79                               | 44.48                    | 1.16         | 1.05 | 1.11 |
| 480            | 3.15                            | 4.33 | 1.18                   | 7.40                               | 47.25                    | 1.18         | 1.05 | 1.12 |
| 490            | 3.02                            | 4.58 | 1.56                   | 8.11                               | 39.53                    | 1.20         | 1.06 | 1.13 |
| 500            | 2.89                            | 4.90 | 2.01                   | 8.91                               | 34.52                    | 1.23         | 1.07 | 1.14 |
| 525            | 2.56                            | 5.98 | 3.41                   | 11.77                              | 26.93                    | 1.30         | 1.11 | 1.18 |
| 550            | 2.25                            | 7.64 | 5.39                   | 16.98                              | 21.93                    | 1.40         | 1.17 | 1.24 |

<sup>1</sup> Total Loss = Insertion Loss+ 3dB Splitter Loss

REV. X2

QCN-3+

100627

Page 1 of 3



**Mini-Circuits®**

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



# 2 Way-90° Power Splitter/Combiner

QCN-3+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -55°C

| FREQ.<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |      | AMP.<br>UNBAL.<br>(dB) | PHASE UNBAL.<br>From 90°<br>(deg.) | ISOLATION<br>(dB)<br>1-2 | VSWR<br>(:1) |      |      |
|----------------|---------------------------------|------|------------------------|------------------------------------|--------------------------|--------------|------|------|
|                | S-1                             | S-2  |                        |                                    |                          | S            | 1    | 2    |
| 100            | 1.04                            | 7.74 | 6.70                   | 0.86                               | 23.81                    | 1.09         | 1.09 | 1.12 |
| 125            | 1.43                            | 6.38 | 4.95                   | 0.75                               | 22.87                    | 1.10         | 1.11 | 1.14 |
| 150            | 1.82                            | 5.39 | 3.57                   | 0.54                               | 22.40                    | 1.10         | 1.11 | 1.14 |
| 175            | 2.19                            | 4.66 | 2.47                   | 0.29                               | 22.25                    | 1.09         | 1.10 | 1.14 |
| 200            | 2.54                            | 4.12 | 1.57                   | 0.04                               | 22.31                    | 1.09         | 1.10 | 1.14 |
| 210            | 2.67                            | 3.94 | 1.28                   | 0.05                               | 22.40                    | 1.08         | 1.10 | 1.14 |
| 220            | 2.80                            | 3.79 | 0.99                   | 0.19                               | 22.51                    | 1.08         | 1.09 | 1.14 |
| 230            | 2.92                            | 3.65 | 0.74                   | 0.30                               | 22.63                    | 1.08         | 1.09 | 1.14 |
| 240            | 3.03                            | 3.52 | 0.49                   | 0.44                               | 22.78                    | 1.07         | 1.09 | 1.13 |
| 250            | 3.13                            | 3.42 | 0.29                   | 0.56                               | 22.95                    | 1.07         | 1.09 | 1.13 |
| 260            | 3.23                            | 3.32 | 0.09                   | 0.71                               | 23.14                    | 1.06         | 1.08 | 1.13 |
| 270            | 3.32                            | 3.24 | 0.08                   | 0.87                               | 23.36                    | 1.06         | 1.08 | 1.12 |
| 280            | 3.40                            | 3.16 | 0.24                   | 1.00                               | 23.60                    | 1.05         | 1.07 | 1.12 |
| 290            | 3.47                            | 3.09 | 0.37                   | 1.15                               | 23.84                    | 1.05         | 1.07 | 1.12 |
| 300            | 3.53                            | 3.05 | 0.48                   | 1.31                               | 24.11                    | 1.04         | 1.06 | 1.11 |
| 310            | 3.59                            | 3.01 | 0.58                   | 1.47                               | 24.43                    | 1.04         | 1.06 | 1.11 |
| 320            | 3.64                            | 2.97 | 0.66                   | 1.65                               | 24.77                    | 1.03         | 1.06 | 1.11 |
| 330            | 3.67                            | 2.96 | 0.72                   | 1.81                               | 25.14                    | 1.03         | 1.06 | 1.11 |
| 340            | 3.70                            | 2.94 | 0.76                   | 1.99                               | 25.55                    | 1.02         | 1.06 | 1.11 |
| 350            | 3.72                            | 2.93 | 0.79                   | 2.18                               | 25.96                    | 1.02         | 1.05 | 1.10 |
| 360            | 3.73                            | 2.94 | 0.79                   | 2.39                               | 26.46                    | 1.02         | 1.05 | 1.10 |
| 370            | 3.73                            | 2.95 | 0.77                   | 2.58                               | 27.02                    | 1.03         | 1.05 | 1.10 |
| 380            | 3.72                            | 2.98 | 0.74                   | 2.81                               | 27.66                    | 1.03         | 1.05 | 1.10 |
| 390            | 3.69                            | 3.02 | 0.68                   | 3.02                               | 28.37                    | 1.04         | 1.05 | 1.10 |
| 400            | 3.66                            | 3.06 | 0.60                   | 3.27                               | 29.18                    | 1.05         | 1.05 | 1.10 |
| 410            | 3.62                            | 3.12 | 0.50                   | 3.52                               | 30.14                    | 1.06         | 1.05 | 1.10 |
| 420            | 3.57                            | 3.20 | 0.37                   | 3.81                               | 31.40                    | 1.07         | 1.05 | 1.10 |
| 430            | 3.50                            | 3.29 | 0.21                   | 4.07                               | 32.91                    | 1.08         | 1.05 | 1.10 |
| 440            | 3.43                            | 3.40 | 0.04                   | 4.41                               | 34.91                    | 1.09         | 1.05 | 1.11 |
| 450            | 3.35                            | 3.53 | 0.18                   | 4.76                               | 37.61                    | 1.11         | 1.05 | 1.11 |
| 460            | 3.26                            | 3.68 | 0.43                   | 5.15                               | 41.49                    | 1.12         | 1.06 | 1.12 |
| 470            | 3.15                            | 3.85 | 0.70                   | 5.58                               | 44.93                    | 1.14         | 1.06 | 1.12 |
| 480            | 3.04                            | 4.07 | 1.03                   | 6.09                               | 40.83                    | 1.16         | 1.07 | 1.13 |
| 490            | 2.90                            | 4.31 | 1.41                   | 6.67                               | 35.86                    | 1.18         | 1.08 | 1.14 |
| 500            | 2.77                            | 4.60 | 1.83                   | 7.35                               | 32.21                    | 1.21         | 1.09 | 1.16 |
| 525            | 2.42                            | 5.59 | 3.16                   | 9.71                               | 25.77                    | 1.28         | 1.13 | 1.20 |
| 550            | 2.10                            | 7.15 | 5.05                   | 14.02                              | 21.15                    | 1.38         | 1.20 | 1.26 |

<sup>1</sup> Total Loss = Insertion Loss+ 3dB Splitter Loss

REV. X2  
QCN-3+  
100627  
Page 2 of 3

# 2 Way-90° Power Splitter/Combiner

QCN-3+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +100°C

| FREQ.<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |      | AMP.<br>UNBAL.<br>(dB) | PHASE UNBAL.<br>From 90°<br>(deg.) | ISOLATION<br>(dB)<br>1-2 | VSWR<br>(:1) |      |      |
|----------------|---------------------------------|------|------------------------|------------------------------------|--------------------------|--------------|------|------|
|                | S-1                             | S-2  |                        |                                    |                          | S            | 1    | 2    |
| 100            | 1.16                            | 7.77 | 6.61                   | 0.86                               | 23.29                    | 1.10         | 1.10 | 1.13 |
| 125            | 1.56                            | 6.42 | 4.86                   | 0.63                               | 22.28                    | 1.10         | 1.10 | 1.13 |
| 150            | 1.96                            | 5.45 | 3.49                   | 0.38                               | 21.79                    | 1.10         | 1.10 | 1.14 |
| 175            | 2.35                            | 4.75 | 2.40                   | 0.09                               | 21.62                    | 1.10         | 1.10 | 1.14 |
| 200            | 2.70                            | 4.22 | 1.52                   | 0.23                               | 21.67                    | 1.09         | 1.10 | 1.14 |
| 210            | 2.84                            | 4.05 | 1.22                   | 0.40                               | 21.77                    | 1.08         | 1.10 | 1.14 |
| 220            | 2.96                            | 3.90 | 0.94                   | 0.56                               | 21.88                    | 1.08         | 1.09 | 1.13 |
| 230            | 3.09                            | 3.77 | 0.69                   | 0.72                               | 22.00                    | 1.07         | 1.09 | 1.13 |
| 240            | 3.19                            | 3.65 | 0.46                   | 0.89                               | 22.15                    | 1.06         | 1.08 | 1.12 |
| 250            | 3.30                            | 3.55 | 0.25                   | 1.06                               | 22.32                    | 1.06         | 1.08 | 1.12 |
| 260            | 3.40                            | 3.46 | 0.06                   | 1.23                               | 22.52                    | 1.05         | 1.07 | 1.11 |
| 270            | 3.49                            | 3.39 | 0.11                   | 1.42                               | 22.74                    | 1.05         | 1.07 | 1.11 |
| 280            | 3.57                            | 3.31 | 0.26                   | 1.60                               | 22.97                    | 1.04         | 1.07 | 1.11 |
| 290            | 3.64                            | 3.25 | 0.38                   | 1.78                               | 23.21                    | 1.03         | 1.06 | 1.11 |
| 300            | 3.70                            | 3.22 | 0.49                   | 1.98                               | 23.46                    | 1.03         | 1.06 | 1.10 |
| 310            | 3.76                            | 3.19 | 0.57                   | 2.17                               | 23.76                    | 1.02         | 1.06 | 1.10 |
| 320            | 3.81                            | 3.16 | 0.64                   | 2.43                               | 24.08                    | 1.02         | 1.05 | 1.10 |
| 330            | 3.84                            | 3.15 | 0.70                   | 2.65                               | 24.43                    | 1.02         | 1.05 | 1.10 |
| 340            | 3.87                            | 3.14 | 0.73                   | 2.88                               | 24.80                    | 1.02         | 1.04 | 1.09 |
| 350            | 3.89                            | 3.14 | 0.75                   | 3.13                               | 25.17                    | 1.03         | 1.03 | 1.09 |
| 360            | 3.90                            | 3.16 | 0.74                   | 3.40                               | 25.61                    | 1.04         | 1.03 | 1.09 |
| 370            | 3.90                            | 3.18 | 0.72                   | 3.67                               | 26.09                    | 1.04         | 1.03 | 1.09 |
| 380            | 3.89                            | 3.22 | 0.67                   | 3.94                               | 26.65                    | 1.05         | 1.02 | 1.09 |
| 390            | 3.86                            | 3.27 | 0.60                   | 4.24                               | 27.24                    | 1.06         | 1.02 | 1.09 |
| 400            | 3.84                            | 3.32 | 0.51                   | 4.56                               | 27.92                    | 1.08         | 1.02 | 1.09 |
| 410            | 3.79                            | 3.40 | 0.39                   | 4.88                               | 28.70                    | 1.09         | 1.02 | 1.09 |
| 420            | 3.74                            | 3.50 | 0.24                   | 5.26                               | 29.71                    | 1.10         | 1.02 | 1.09 |
| 430            | 3.67                            | 3.60 | 0.07                   | 5.62                               | 30.88                    | 1.11         | 1.02 | 1.09 |
| 440            | 3.61                            | 3.73 | 0.12                   | 6.07                               | 32.35                    | 1.13         | 1.02 | 1.10 |
| 450            | 3.52                            | 3.88 | 0.36                   | 6.55                               | 34.30                    | 1.15         | 1.02 | 1.10 |
| 460            | 3.43                            | 4.05 | 0.63                   | 7.08                               | 37.09                    | 1.16         | 1.03 | 1.10 |
| 470            | 3.33                            | 4.26 | 0.93                   | 7.67                               | 41.87                    | 1.18         | 1.03 | 1.11 |
| 480            | 3.21                            | 4.50 | 1.29                   | 8.39                               | 54.13                    | 1.20         | 1.03 | 1.11 |
| 490            | 3.09                            | 4.78 | 1.69                   | 9.18                               | 43.87                    | 1.23         | 1.04 | 1.12 |
| 500            | 2.96                            | 5.12 | 2.16                   | 10.12                              | 36.74                    | 1.25         | 1.05 | 1.13 |
| 525            | 2.64                            | 6.26 | 3.61                   | 13.41                              | 27.87                    | 1.33         | 1.08 | 1.16 |
| 550            | 2.36                            | 8.01 | 5.66                   | 19.42                              | 22.54                    | 1.42         | 1.15 | 1.22 |

<sup>1</sup> Total Loss = Insertion Loss+ 3dB Splitter Loss

REV. X2

QCN-3+

100627

Page 3 of 3



**Mini-Circuits®**

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




# 2 Way-90° Power Splitter/Combiner


QCN-3+

## Typical Performance Curves


Total Loss




Total Loss S-1 vs. TEMPERATURE




Amplitude Unbalance vs. TEMPERATURE



Phase Unbalance vs. TEMPERATURE



Isolation 1-2 vs. TEMPERATURE






REV. X2  
QCN-3+  
100627  
Page 1 of 2

# 2 Way-90° Power Splitter/Combiner

QCN-3+

## Typical Performance Curves



REV. X2

QCN-3+

100627

Page 2 of 2



**Mini-Circuits®**


IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE #   | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L  | M  | N  | P  | WT. GRAM |
|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----|----|----|----|----------|
| FV1206-1 | .126<br>(3.20) | .063<br>(1.60) | .035<br>(0.89) | .024<br>(0.61) | .022<br>(0.56) | .011<br>(0.28) | .039<br>(0.99) | .024<br>(0.61) | .042<br>(1.07) | .123<br>(3.12) | -- | -- | -- | -- | .020     |

Dimensions are in inches (mm). Tolerances: 2 PL.  $\pm .01$ ; 3 PL.  $\pm .005$

#### Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**  
 For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
 For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



ISO 9001 ISO 14001 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



# Tape & Reel Packaging

# TR-F75

## DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

| Applicable Case Styles |
|------------------------|
| FV1206-1               |
| FV1206-3               |

| Applicable Case Styles |
|------------------------|
| FV1206-4               |
| FV1206-5               |
| FV1206-6               |
| FV1206-7               |
| FV1206-9               |
| JC0603C-1              |

| Applicable Case Styles |
|------------------------|
| NL1008C-6              |
| FV1206-12              |
| NL1008C-9              |
| NL1008C-10             |

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         |                   | Standard                            | 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)

Mini-Circuits ISO 9001 & ISO 14001 Certified

**Mini-Circuits®**


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION               | DATE     | DR  | AUTH |
|-----|---------|---------------------------|----------|-----|------|
| OR  | M87001  | NEW RELEASE               | 05/20/03 | MMG | ABD  |
| A   | M87231  | CORRECTED DWG.            | 05/28/03 | MMG | ABD  |
| B   | M91636  | ADDED "pn" PIN CONNECTION | 04/07/04 | AV  | ABD  |
| C   | M102713 | ADDED "...WITH SMOBC"     | 01/16/06 | GF  | IL   |

SUGGESTED MOUNTING CONFIGURATION  
FOR FV1206-1 CASE STYLE, "pb/pn" PIN CONNECTIONS



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020"  $\pm$  0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS  $\pm$ 3 PL DECIMALS  $\pm$  .005ANGLES  $\pm$ FRACTIONS  $\pm$ 

DRAWN

MMG

05/14/03

CHECKED

AV

05/19/03

APPROVED

ABD

05/20/03



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, pb/pn, FV1206-1, QCN/BDCN, TB-255

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-131

REV:

C

FILE:

98PL131

SCALE:

10:1

SHEET:

1 OF 1


Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

# Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                           | Reference/Spec                                                                                       |
|----------------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment                                                | Individual Model Data Sheet                                                                          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                               | Individual Model Data Sheet                                                                          |
| Humidity                   | 90 to 95% RH, 240 hours, 50°C                                                       | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat         | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak              | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability              | 10X Magnification                                                                   | J-STD-002, Para 4.2.5, Test S, 95% Coverage                                                          |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                   | MIL-STD-202, Method 213, Condition A                                                                 |