

50Ω 410 to 470 MHz

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5 W at 25°C

Permanent damage may occur if any of these limits are exceeded.

RF IN	2
RF OUT	6
GROUND	1,3,4,5,7,8


PCB Land Pattern

Suggested Layout,
Tolerance to be within $\pm.002$

Legend:
 METALLIZATION
 SOLDER RESIST

A	B	C	D	E	F	G	H	J
350	.350	.100	.175	.075	.100	.110	.040	.080
3.89	8.89	2.54	4.45	1.91	2.54	2.79	1.02	2.03
K	L	M	N	P	Q	R	wt	
500	.040	.195	.390	120	.390	.070	grams	
1.27	1.02	4.95	9.91	3.05	9.91	1.78	0.25	

Demo Board MCL P/N: TB-332
Suggested PCB Layout (PL-176)




1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025" ± .002"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK



Notes:



- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instruments.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusions, warranties and remedies thereunder, please visit [Mini-Circuits' website at www.minicircuits.com/MCQ_StandardTerms.aspx](http://www.minicircuits.com/MCQ_StandardTerms.aspx)

- linear phase, up to $\pm 3\text{deg}$ typ. @ $F_c \pm 30\text{MHz}$
- good VSWR, 1.3:1 typ. @ passband
- small size 0.35" x 0.35"
- shielded case
- aqueous washable

- harmonic rejection
- transmitters / receivers
- personal & home communication

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 3dB) Fc	STOPBANDS (MHz)				MAXIMUM DEVIATION FROM LINEAR PHASE (deg.) Fc ± 30MHz	VSWR (:1)		
		Loss > 20dB		Loss > 30dB			Passband		Stopband
		F3	F4	F5	F6		Typ.	Max.	Typ.
440	410 - 470	320	650	200	850 - 1500	±6	1.3	2.0	20

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Deviation from Linear Phase (deg)
0.5	101.96	4669.18	410.0	2.69
50.0	62.44	4976.10	413.0	1.43
150.0	42.32	390.29	416.0	0.56
320.0	30.36	28.41	420.5	-0.37
355.0	18.05	10.40	425.0	-0.84
370.0	8.73	4.79	428.0	-0.96
380.0	4.74	2.55	434.0	-0.86
395.0	2.23	1.30	437.0	-0.73
410.0	1.67	1.20	438.5	-0.62
440.0	1.43	1.17	440.0	-0.53
470.0	1.79	1.34	441.5	-0.42
490.0	3.67	2.66	443.0	-0.30
500.0	5.97	4.37	446.0	-0.07
510.0	9.60	7.47	452.0	0.34
530.0	21.82	16.89	455.0	0.49
650.0	26.91	56.67	463.0	0.45
850.0	35.76	89.73	466.5	0.19
1500.0	36.15	58.75	470.0	-0.24



CASE STYLE: GP731

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Metal Shield Band Pass Filter

RBP-440+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
1	89.18	97.70	95.24	0.00	0.01	0.00	0.01	0.03	0.03
10	88.91	89.41	91.28	0.00	0.00	0.00	0.02	0.03	0.06
50	62.62	62.83	62.79	0.01	0.02	0.02	0.07	0.11	0.13
100	50.33	50.34	50.24	0.01	0.03	0.06	0.11	0.15	0.18
150	42.58	42.56	42.57	0.01	0.05	0.09	0.13	0.18	0.22
200	36.55	36.55	36.54	0.04	0.10	0.15	0.17	0.23	0.28
250	31.59	31.62	31.62	0.11	0.18	0.24	0.22	0.31	0.36
300	29.01	29.08	29.17	0.30	0.40	0.47	0.36	0.48	0.56
320	31.68	31.85	32.10	0.43	0.56	0.65	0.49	0.63	0.72
350	20.86	20.39	19.87	1.06	1.29	1.47	1.04	1.31	1.51
355	17.00	16.64	16.21	1.32	1.59	1.81	1.29	1.61	1.87
370	7.86	7.80	7.64	3.33	3.85	4.30	3.45	4.08	4.64
380	4.01	4.17	4.23	7.02	7.70	8.35	7.79	8.80	9.76
400	1.62	1.90	2.09	16.91	16.93	17.07	25.01	24.66	23.98
410	1.42	1.68	1.86	16.44	16.80	17.09	17.87	18.15	18.30
420	1.31	1.56	1.72	16.26	16.92	17.48	16.33	16.90	17.29
430	1.23	1.47	1.64	16.96	17.92	18.69	16.61	17.40	17.95
440	1.18	1.42	1.59	18.74	20.11	21.21	18.18	19.22	19.95
470	1.31	1.64	1.89	21.87	20.30	19.21	20.67	19.70	18.91
490	2.59	3.12	3.56	8.48	8.18	7.92	9.67	9.61	9.52
500	4.48	5.21	5.81	4.79	4.72	4.63	6.05	6.16	6.19
510	7.78	8.73	9.49	2.54	2.63	2.66	3.64	3.87	3.98
530	19.13	20.44	21.63	0.91	1.11	1.24	1.55	1.82	1.97
600	25.21	25.41	25.56	0.31	0.47	0.59	0.42	0.56	0.65
650	27.30	27.54	27.73	0.20	0.36	0.47	0.26	0.38	0.45
700	29.81	30.04	30.24	0.14	0.31	0.42	0.19	0.30	0.36
800	33.96	34.21	34.42	0.10	0.27	0.38	0.13	0.24	0.31
850	35.90	36.20	36.35	0.09	0.26	0.37	0.12	0.24	0.30
900	37.40	37.56	37.75	0.10	0.24	0.36	0.11	0.23	0.30
1000	38.67	38.79	39.04	0.09	0.26	0.36	0.09	0.22	0.29
1200	38.87	38.96	39.10	0.10	0.26	0.37	0.07	0.22	0.30
1300	37.98	38.05	38.21	0.10	0.26	0.37	0.08	0.24	0.34
1400	37.15	37.34	37.42	0.09	0.26	0.36	0.07	0.24	0.35
1500	35.95	36.01	36.18	0.10	0.26	0.37	0.05	0.24	0.36
1600	34.99	35.22	35.37	0.09	0.26	0.37	0.06	0.26	0.39
1700	33.52	33.85	33.92	0.08	0.26	0.37	0.05	0.28	0.40
1800	32.47	32.89	33.07	0.06	0.25	0.36	0.06	0.28	0.43
2000	30.10	30.34	30.50	0.08	0.28	0.39	0.07	0.34	0.51
2200	28.99	29.05	29.04	0.05	0.26	0.40	0.07	0.37	0.55
2300	28.15	28.20	28.06	0.07	0.29	0.44	0.04	0.37	0.58
2400	27.72	27.76	27.84	0.10	0.33	0.49	0.06	0.40	0.60
2500	26.71	27.05	27.10	0.03	0.29	0.44	0.06	0.39	0.63
2600	27.49	27.48	27.53	0.06	0.35	0.53	0.06	0.42	0.65
2700	25.23	25.53	25.44	0.10	0.37	0.55	0.06	0.42	0.67
2800	26.32	26.41	26.46	0.06	0.38	0.59	0.06	0.42	0.70
3000	25.58	25.97	26.02	0.07	0.41	0.64	0.09	0.48	0.77
3200	24.25	24.49	24.62	0.09	0.46	0.73	0.11	0.51	0.79
3300	23.59	23.90	23.98	0.12	0.48	0.75	0.13	0.53	0.84
3400	23.49	23.85	23.92	0.12	0.51	0.80	0.14	0.54	0.87
3500	22.76	23.31	23.43	0.12	0.52	0.84	0.16	0.56	0.90
3600	23.29	23.55	23.61	0.16	0.56	0.87	0.17	0.56	0.89
3700	22.13	22.56	22.67	0.15	0.54	0.88	0.20	0.61	0.96
3800	22.47	22.55	22.66	0.17	0.59	0.91	0.21	0.61	0.97
4000	21.93	22.21	22.30	0.18	0.62	0.95	0.26	0.67	1.03

REV. X2

RBP-440+

101012

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Metal Shield Band Pass Filter

RBP-440+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
410	6.42	6.33	6.26
412	6.26	6.18	6.13
414	6.13	6.06	6.01
416	6.00	5.94	5.93
418	5.93	5.88	5.86
420	5.81	5.80	5.77
422	5.75	5.72	5.71
424	5.69	5.67	5.65
426	5.63	5.61	5.60
428	5.55	5.54	5.54
430	5.55	5.51	5.51
432	5.51	5.49	5.50
434	5.49	5.46	5.49
436	5.45	5.45	5.46
438	5.45	5.45	5.47
440	5.44	5.46	5.48
442	5.44	5.47	5.49
444	5.47	5.49	5.51
446	5.50	5.50	5.52
448	5.52	5.53	5.58
450	5.55	5.56	5.60
452	5.58	5.60	5.65
454	5.62	5.66	5.68
456	5.69	5.73	5.79
458	5.76	5.79	5.82
460	5.83	5.87	5.91
462	5.92	5.96	5.99
464	6.01	6.04	6.10
466	6.09	6.14	6.19
468	6.23	6.26	6.33
470	6.33	6.39	6.47
472	6.46	6.53	6.60
474	6.60	6.68	6.74
476	6.77	6.83	6.90
478	6.93	6.99	7.07
480	7.12	7.17	7.25
482	7.30	7.34	7.43
484	7.48	7.53	7.60
486	7.67	7.71	7.76
488	7.84	7.90	7.92
490	7.99	8.01	8.02
492	8.15	8.13	8.13
494	8.27	8.23	8.20
496	8.34	8.28	8.22
498	8.39	8.27	8.18
500	8.37	8.20	8.05
505	8.20	7.97	7.76
510	7.85	7.54	7.29
515	7.28	6.89	6.56
520	6.41	5.92	5.49
525	5.27	4.56	3.95
530	3.47	2.27	1.06

REV. X2

RBP-440+

101012

Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



Typical Performance Curves



REV. X2

RBP-440+

101012

Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661





The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Outline Dimensions

GP731



CASE #	A	B	C	D	E	F	G	H	J	K	L	M
GP731	.350 (8.89)	.350 (8.89)	.100 (2.54)	.175 (4.45)	.075 (1.91)	.100 (2.54)	.110 (2.79)	.040 (1.02)	.080 (2.03)	.050 (1.27)	.040 (1.02)	.195 (4.95)

CASE #	N	P	Q	R	WT. GRAM
GP731	.390 (9.91)	.120 (3.05)	.390 (9.91)	.070 (1.78)	.4 +0.3 -0.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:

For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F78



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
16	12	7	10
			20
			50
			100
			200
		13	500, 1000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	R59289	NEW RELEASE (FROM RAVON)	02/05	DK	HH
A	M101151	ADDED "RBP" & CORRECTED PIN	10/10/05	MMG	DJ
		CONNECTION TO DESCRIPTION OF PL-DWG.			
B	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/20/06	GT	IL

SUGGESTED MOUNTING CONFIGURATION
 FOR GP731 CASE STYLE, "qf" PIN CONNECTION.



- NOTES: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025" ± .002"; COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	DK (RAVON)	10 FEB 05
	CHECKED	RZ (RAVON)	10 FEB 05
	APPROVED	HH (RAVON)	10 FEB 05

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits®

13 Neptune Avenue
 Brooklyn NY 11235


PL, qf, GP731, RBP, TB-332

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-176	REV: B
FILE: 98PL176	SCALE: 5:1	SHEET: 1 OF 1	

Evaluation Board and Circuit



TB-332



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215