

Non-Catalog Model

Frequency Mixer

SCM-5

Level 7 (LO Power +7 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : YY109


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	1250		1800	MHz
	RF (fL to fU)	1250		1800	MHz
	IF	0		500	MHz
Conversion Loss			5.8	8.0	dB
LO-RF Isolation		17	28		dB
LO-IF Isolation		8	18		dB
1 dB Comp. Input Power			+1		dBm

Note: Non-hermetic

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	1
RF	8
IF	3
GROUND	2, 4, 5, 6, 7

Electrical Schematics



Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)			LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
		@LO (dBm)				@LO (dBm)			@LO (dBm)		
		+4	+7	+10		+4	+7	+10	+4	+7	+10
1250.0	1280.0	7.07	6.32	5.90	1250.0	24.7	24.8	25.0	17.3	18.9	20.0
1298.5	1328.5	6.96	6.19	5.82	1298.5	24.5	24.6	24.8	16.7	18.3	19.2
1330.9	1300.9	6.34	5.58	5.17	1330.9	25.1	25.1	25.2	15.8	17.5	18.5
1347.1	1317.1	6.36	5.60	5.14	1347.1	25.3	25.5	25.5	15.4	17.1	18.1
1379.4	1349.4	6.12	5.45	5.33	1379.4	25.4	25.8	25.9	14.9	16.6	17.7
1411.8	1381.8	5.91	5.33	5.36	1411.8	25.1	25.6	25.9	14.5	16.0	16.9
1444.1	1414.1	5.86	5.31	5.67	1444.1	25.6	26.2	26.4	14.2	15.4	16.2
1460.3	1430.3	5.81	5.31	5.86	1460.3	26.2	26.7	27.1	14.0	15.2	15.9
1500.0	1470.0	5.87	5.26	5.76	1500.0	26.8	27.1	26.9	13.2	14.0	14.7
1541.2	1511.2	5.85	5.26	5.77	1541.2	27.1	27.6	27.2	13.6	13.8	14.1
1557.4	1527.4	6.01	5.31	5.73	1557.4	27.2	27.6	26.8	13.4	13.2	13.5
1589.7	1559.7	6.04	5.36	5.92	1589.7	27.6	28.2	27.3	13.7	13.1	13.0
1622.1	1592.1	6.23	5.54	5.94	1622.1	27.6	28.0	26.0	13.3	12.4	12.0
1654.4	1624.4	6.32	5.70	6.08	1654.4	27.2	27.4	26.2	13.1	12.2	11.6
1670.5	1640.6	6.37	5.76	6.05	1670.5	27.0	27.1	26.2	13.4	12.4	11.7
1702.9	1672.9	6.59	5.96	6.01	1702.9	26.0	25.8	25.0	12.8	11.5	10.8
1751.5	1721.5	6.61	6.00	5.96	1751.5	26.0	25.7	24.8	12.8	11.3	10.2
1767.6	1737.6	6.55	5.95	5.91	1767.6	26.1	25.8	24.5	12.9	11.3	10.1
1783.8	1753.8	6.61	5.97	5.87	1783.8	25.5	25.1	24.0	12.4	10.7	9.7
1800.0	1770.0	6.63	5.94	5.84	1800.0	25.2	24.8	23.8	12.4	10.7	9.7

REV. X1

SCM-5

060613

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Data


RF/LO (MHz)	RF VSWR (:1)			LO VSWR (:1)			IF (MHz)	IF VSWR (:1)			LO/RF (MHz)	max. DC output (mV)	DC Offset (mV)
	@LO (dBm)			@LO (dBm)				@LO (dBm)			@LO (dBm)		
	+4	+7	+10	+4	+7	+10		+4	+7	+10	+7		
1250.0	3.60	2.97	2.47	8.72	10.89	12.80	5.0	2.29	1.92	1.68	1250.0	-106.1	10.73
1298.5	3.14	2.57	2.16	8.95	10.62	12.09	10.0	2.32	1.94	1.69	1298.5	-96.8	10.24
1330.9	2.80	2.31	1.93	9.23	10.69	12.09	20.0	2.34	1.95	1.70	1330.9	-90.3	10.32
1347.1	2.71	2.24	1.86	9.63	11.03	12.52	50.0	2.35	1.95	1.70	1347.1	-89.3	10.73
1379.4	2.47	2.00	1.67	10.69	11.77	13.09	52.9	2.36	1.95	1.70	1379.4	-80.0	10.62
1411.8	2.25	1.84	1.51	11.24	11.85	13.09	100.0	2.39	1.97	1.71	1411.8	-72.9	11.49
1444.1	2.09	1.69	1.38	11.24	11.69	12.52	100.8	2.39	1.97	1.71	1444.1	-65.6	12.83
1460.3	2.02	1.61	1.31	11.53	11.77	12.52	148.7	2.43	1.99	1.73	1460.3	-65.1	14.16
1500.0	1.88	1.51	1.21	12.44	12.44	12.80	196.6	2.43	1.98	1.72	1500.0	-59.7	16.09
1541.2	1.74	1.43	1.16	12.61	12.71	12.61	200.0	2.43	1.98	1.72	1541.2	-45.0	17.30
1557.4	1.72	1.42	1.16	12.61	12.52	12.44	244.5	2.41	1.97	1.71	1557.4	-41.4	17.69
1589.7	1.67	1.43	1.22	12.35	12.52	12.18	250.0	2.41	1.96	1.71	1589.7	-38.2	18.47
1622.1	1.67	1.47	1.30	12.35	12.52	12.09	260.5	2.39	1.96	1.71	1622.1	-33.3	18.99
1654.4	1.68	1.52	1.39	12.26	12.44	11.85	292.4	2.36	1.95	1.70	1622.1	-29.7	18.70
1670.6	1.70	1.56	1.44	12.18	12.26	11.77	324.4	2.32	1.92	1.68	1670.6	-32.2	19.75
1702.9	1.74	1.64	1.54	11.93	11.85	11.53	372.3	2.23	1.88	1.66	1702.9	-35.6	20.08
1751.5	1.85	1.78	1.71	11.61	11.31	11.09	404.2	2.18	1.87	1.64	1751.5	-34.0	17.75
1767.6	1.88	1.85	1.77	11.53	11.31	10.89	452.1	2.12	1.85	1.63	1767.6	-33.4	16.69
1783.8	1.93	1.90	1.82	11.46	11.17	10.19	484.0	2.08	1.83	1.63	1783.8	-34.5	16.04
1800.0	1.97	1.97	1.90	11.61	11.03	10.50	500.0	2.08	1.83	1.63	1800.0	-38.1	15.67

Typical Performance Curves


Conversion Loss




LO-RF Isolation




LO-IF Isolation




RF VSWR




LO VSWR



IF VSWR



Max. DC Output



REV. X1

SCM-5

060613

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Outline Dimensions

YY101
YY109
YY161



PCB Land Pattern



Suggested Layout
Tolerance to be within $\pm.002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	WT. GRAM S
YY101*			.20 (5.08)							.450 (11.43)	--	.470 (11.94)				1.6
YY109*	.75 (19.05)	.38 (9.65)	.20 (5.08)	.010 (0.25)	.050 (1.27)	.020 (0.51)	.200 (5.08)	.075 (1.91)	.600 (15.24)	.720 (18.29)	--	.740 (18.80)	.100 (2.54)	.150 (3.81)	.148 (3.76)	1.6
YY161			.28 (7.11)							.450 (11.43)	--	.470 (11.94)				1.6

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.
- Special Tolerances: Termination thickness $\pm .003$ inch.
- * Denotes: For SCM mixers, long termination version (case YY109) is available upon request, consult factory. To order short termination version (case YY101) add -NL suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Evaluation Board and Circuit



TB-171



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215