

Surface Mount, Micro-Miniature Power Splitter/Combiner

SBTCJ-1W+

2 Way-180° 50Ω 1 to 750 MHz

Features

- low insertion loss, 0.7 dB typ.
- good isolation, 23 dB typ.
- good VSWR, 1.25 typ. all ports
- small size, 0.15X0.15"X0.15"
- temperature stable, LTCC base
- low cost
- protected by US Patent, 6,806,790

Applications

- cellular
- UHF/VHF receivers/transmitters



Generic photo used for illustration purposes only

CASE STYLE: AT790

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost	
Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000, 2000

Electrical Specifications

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		1		750	MHz
Insertion Loss Above 3.0 dB	1 - 100	—	0.6	1.7	dB
	100 - 375	—	0.6	1.2	
	375 - 750	—	0.9	1.8	
Isolation ¹	1 - 100	20	23	—	dB
	100 - 375	20	22	—	
	375 - 750	20	24	—	
Phase Unbalance	1 - 100	—	—	3	Degree
	100 - 375	—	—	7	
	375 - 750	—	—	10	
Amplitude Unbalance	1 - 100	—	—	0.2	dB
	100 - 375	—	—	0.4	
	375 - 750	—	—	0.9	

1. Isolation, 17 dB min. at 1 - 3 MHz

Maximum Ratings

Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	0.5W max.
Internal Dissipation	0.125W max

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

Function	Pin Number
SUM PORT	6
PORT 1	1
PORT 2	3
GROUND	2,4
NOT USED	5

Electrical Schematic



2 Way-180° Power Splitter/Combiner

SBTCJ-1W+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB) 1-2	PHASE UNBAL. from 180° (Deg)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1.0	3.96	4.00	0.04	22.87	0.16	1.0	1.33	1.18	1.19
2.0	3.88	3.92	0.04	22.92	0.17	2.0	1.27	1.14	1.15
3.0	3.81	3.84	0.03	22.97	0.18	3.0	1.22	1.12	1.12
5.0	3.66	3.68	0.02	23.07	0.19	5.0	1.15	1.08	1.08
7.0	3.58	3.60	0.02	23.01	0.20	7.0	1.12	1.06	1.06
9.0	3.57	3.59	0.01	22.78	0.20	9.0	1.12	1.05	1.05
10.0	3.57	3.58	0.01	22.67	0.20	10.0	1.11	1.05	1.05
12.0	3.57	3.58	0.01	22.53	0.21	12.0	1.11	1.04	1.04
14.0	3.58	3.58	0.00	22.46	0.22	14.0	1.11	1.04	1.04
16.0	3.58	3.58	0.00	22.40	0.23	16.0	1.10	1.04	1.04
18.0	3.58	3.58	0.00	22.38	0.23	18.0	1.10	1.04	1.04
20.0	3.58	3.59	0.01	22.37	0.23	20.0	1.10	1.03	1.04
30.0	3.60	3.60	0.00	22.34	0.28	30.0	1.10	1.03	1.03
40.0	3.61	3.61	0.00	22.36	0.36	40.0	1.10	1.03	1.03
50.0	3.61	3.61	0.00	22.39	0.41	50.0	1.10	1.03	1.03
100.0	3.64	3.65	0.01	22.51	0.75	100.0	1.10	1.04	1.05
150.0	3.65	3.67	0.02	22.69	1.08	150.0	1.10	1.05	1.06
200.0	3.66	3.70	0.04	22.93	1.42	200.0	1.11	1.06	1.07
250.0	3.66	3.73	0.07	23.22	1.75	250.0	1.12	1.07	1.09
300.0	3.66	3.76	0.10	23.59	2.08	300.0	1.13	1.09	1.11
350.0	3.67	3.80	0.13	23.99	2.41	350.0	1.14	1.10	1.13
400.0	3.66	3.84	0.18	24.49	2.69	400.0	1.16	1.12	1.16
450.0	3.66	3.89	0.23	25.08	3.05	450.0	1.17	1.14	1.18
500.0	3.66	3.94	0.28	25.75	3.35	500.0	1.18	1.17	1.21
550.0	3.67	3.99	0.32	26.52	3.67	550.0	1.20	1.19	1.24
600.0	3.67	4.06	0.39	27.35	3.96	600.0	1.21	1.23	1.28
650.0	3.68	4.13	0.45	28.11	4.27	650.0	1.23	1.26	1.32
700.0	3.70	4.22	0.52	28.78	4.53	700.0	1.24	1.30	1.36
750.0	3.71	4.29	0.58	29.02	4.76	750.0	1.26	1.35	1.41
800.0	3.74	4.39	0.65	28.79	5.02	800.0	1.28	1.39	1.46
850.0	3.77	4.49	0.72	28.16	5.24	850.0	1.30	1.44	1.51
900.0	3.80	4.59	0.79	27.08	5.46	900.0	1.32	1.50	1.57
950.0	3.85	4.70	0.85	25.81	5.59	950.0	1.34	1.56	1.63
1000.0	3.91	4.82	0.91	24.53	5.71	1000.0	1.36	1.62	1.70
1050.0	3.96	4.95	0.99	23.30	5.78	1050.0	1.38	1.68	1.77
1100.0	4.04	5.08	1.04	22.14	5.83	1100.0	1.40	1.74	1.85
1150.0	4.13	5.22	1.09	21.06	5.77	1150.0	1.42	1.81	1.93
1200.0	4.22	5.38	1.16	20.06	5.66	1200.0	1.44	1.88	2.02
1250.0	4.31	5.54	1.23	19.18	5.47	1250.0	1.46	1.95	2.12
1300.0	4.42	5.71	1.29	18.34	5.24	1300.0	1.49	2.02	2.22
1350.0	4.54	5.89	1.35	17.60	4.86	1350.0	1.51	2.09	2.32
1400.0	4.67	6.08	1.41	16.91	4.40	1400.0	1.54	2.17	2.44
1450.0	4.81	6.29	1.48	16.30	3.83	1450.0	1.57	2.24	2.56
1500.0	4.95	6.50	1.55	15.72	3.15	1500.0	1.59	2.32	2.68
1550.0	5.10	6.74	1.64	15.19	2.45	1550.0	1.63	2.40	2.82
1600.0	5.25	6.96	1.71	14.69	1.60	1600.0	1.66	2.48	2.97
1650.0	5.42	7.22	1.80	14.25	0.64	1650.0	1.69	2.55	3.12
1700.0	5.57	7.46	1.89	13.82	0.47	1700.0	1.72	2.63	3.29
1750.0	5.74	7.74	2.00	13.43	1.70	1750.0	1.75	2.71	3.46
1800.0	5.91	8.04	2.13	13.07	3.05	1800.0	1.78	2.79	3.65
1850.0	6.09	8.34	2.25	12.74	4.50	1850.0	1.82	2.86	3.84
1900.0	6.26	8.67	2.41	12.42	6.01	1900.0	1.85	2.94	4.03
1950.0	6.44	9.02	2.58	12.15	7.76	1950.0	1.88	3.01	4.24
2000.0	6.62	9.37	2.75	11.86	9.46	2000.0	1.92	3.09	4.46

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
SBTCJ-1W+
2/18/2013
Page 1 of 3

2 Way-180° Power Splitter/Combiner

SBTCJ-1W+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB) 1-2	PHASE UNBAL. from 180° (Deg)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1.0	4.38	4.40	0.02	20.12	0.16	1.0	1.52	1.26	1.27
2.0	4.23	4.24	0.01	21.11	0.15	2.0	1.41	1.23	1.23
3.0	4.08	4.08	0.00	22.11	0.14	3.0	1.33	1.19	1.20
5.0	3.77	3.76	0.01	24.10	0.13	5.0	1.22	1.15	1.15
7.0	3.60	3.58	0.02	24.81	0.12	7.0	1.17	1.12	1.12
9.0	3.55	3.53	0.02	24.25	0.12	9.0	1.14	1.11	1.11
10.0	3.52	3.50	0.02	23.98	0.12	10.0	1.13	1.10	1.11
12.0	3.50	3.48	0.02	23.49	0.12	12.0	1.11	1.10	1.10
14.0	3.49	3.47	0.02	23.07	0.13	14.0	1.11	1.09	1.09
16.0	3.48	3.46	0.02	22.66	0.14	16.0	1.10	1.09	1.09
18.0	3.48	3.46	0.02	22.48	0.14	18.0	1.09	1.08	1.08
20.0	3.47	3.46	0.01	22.29	0.14	20.0	1.09	1.08	1.08
30.0	3.47	3.45	0.02	21.85	0.21	30.0	1.08	1.08	1.07
40.0	3.47	3.46	0.01	21.67	0.29	40.0	1.08	1.08	1.07
50.0	3.47	3.46	0.01	21.61	0.35	50.0	1.08	1.08	1.07
100.0	3.49	3.49	0.00	21.56	0.73	100.0	1.08	1.08	1.09
150.0	3.49	3.52	0.03	21.80	1.12	150.0	1.09	1.09	1.10
200.0	3.50	3.55	0.05	22.08	1.51	200.0	1.10	1.09	1.12
250.0	3.50	3.58	0.08	22.31	1.91	250.0	1.11	1.10	1.13
300.0	3.50	3.61	0.11	22.67	2.28	300.0	1.13	1.11	1.14
350.0	3.50	3.64	0.14	23.11	2.67	350.0	1.14	1.12	1.16
400.0	3.49	3.68	0.19	23.61	3.06	400.0	1.15	1.13	1.19
450.0	3.48	3.73	0.25	24.15	3.46	450.0	1.17	1.15	1.21
500.0	3.48	3.77	0.29	24.84	3.83	500.0	1.19	1.17	1.24
550.0	3.48	3.82	0.34	25.63	4.21	550.0	1.20	1.20	1.27
600.0	3.48	3.88	0.40	26.51	4.55	600.0	1.22	1.23	1.31
650.0	3.49	3.95	0.46	27.45	4.93	650.0	1.23	1.27	1.35
700.0	3.50	4.03	0.53	28.41	5.25	700.0	1.25	1.30	1.39
750.0	3.50	4.10	0.60	29.14	5.57	750.0	1.26	1.35	1.44
800.0	3.53	4.20	0.67	29.45	5.92	800.0	1.28	1.39	1.49
850.0	3.55	4.28	0.73	29.31	6.18	850.0	1.30	1.44	1.54
900.0	3.58	4.38	0.80	28.47	6.48	900.0	1.32	1.50	1.60
950.0	3.62	4.49	0.87	27.21	6.71	950.0	1.34	1.55	1.66
1000.0	3.67	4.61	0.94	25.82	6.92	1000.0	1.36	1.61	1.74
1050.0	3.72	4.73	1.01	24.49	7.07	1050.0	1.38	1.68	1.81
1100.0	3.79	4.86	1.07	23.24	7.24	1100.0	1.40	1.75	1.89
1150.0	3.86	5.00	1.14	22.02	7.31	1150.0	1.43	1.82	1.98
1200.0	3.94	5.15	1.21	20.91	7.37	1200.0	1.46	1.89	2.07
1250.0	4.04	5.31	1.27	19.96	7.34	1250.0	1.48	1.97	2.17
1300.0	4.14	5.46	1.32	19.07	7.26	1300.0	1.50	2.05	2.27
1350.0	4.27	5.64	1.37	18.23	7.03	1350.0	1.54	2.14	2.38
1400.0	4.39	5.83	1.44	17.45	6.76	1400.0	1.57	2.22	2.51
1450.0	4.53	6.02	1.49	16.77	6.44	1450.0	1.60	2.31	2.63
1500.0	4.68	6.25	1.57	16.21	5.80	1500.0	1.63	2.41	2.75
1550.0	4.82	6.45	1.63	15.57	5.38	1550.0	1.67	2.50	2.92
1600.0	4.98	6.68	1.70	15.04	4.72	1600.0	1.70	2.59	3.08
1650.0	5.15	6.91	1.76	14.56	3.92	1650.0	1.73	2.70	3.25
1700.0	5.32	7.17	1.85	14.14	2.93	1700.0	1.77	2.80	3.42
1750.0	5.49	7.42	1.93	13.70	1.87	1750.0	1.81	2.89	3.62
1800.0	5.67	7.70	2.03	13.31	0.72	1800.0	1.85	3.00	3.82
1850.0	5.86	7.99	2.13	12.96	0.56	1850.0	1.89	3.11	4.06
1900.0	6.03	8.31	2.28	12.62	1.91	1900.0	1.93	3.20	4.27
1950.0	6.22	8.62	2.40	12.29	3.41	1950.0	1.97	3.30	4.53
2000.0	6.39	8.95	2.56	11.99	5.20	2000.0	2.01	3.39	4.77

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR
SBTCJ-1W+
2/18/2013
Page 2 of 3

2 Way-180° Power Splitter/Combiner

SBTCJ-1W+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +85°C

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB) 1-2	PHASE UNBAL. from 180° (Deg)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1.0	4.13	4.14	0.01	21.87	0.01	1.0	1.35	1.19	1.19
2.0	4.06	4.07	0.01	22.03	0.03	2.0	1.30	1.15	1.15
3.0	3.99	4.00	0.01	22.19	0.05	3.0	1.26	1.12	1.12
5.0	3.85	3.86	0.01	22.52	0.08	5.0	1.19	1.07	1.07
7.0	3.78	3.79	0.01	22.65	0.11	7.0	1.16	1.05	1.06
9.0	3.77	3.78	0.01	22.59	0.12	9.0	1.16	1.05	1.05
10.0	3.77	3.78	0.01	22.56	0.13	10.0	1.15	1.04	1.04
12.0	3.77	3.78	0.01	22.52	0.15	12.0	1.15	1.04	1.04
14.0	3.78	3.78	0.00	22.51	0.17	14.0	1.15	1.04	1.04
16.0	3.78	3.78	0.00	22.50	0.19	16.0	1.15	1.04	1.04
18.0	3.78	3.78	0.00	22.50	0.19	18.0	1.15	1.04	1.03
20.0	3.78	3.79	0.01	22.51	0.20	20.0	1.15	1.04	1.03
30.0	3.80	3.80	0.00	22.54	0.29	30.0	1.15	1.04	1.03
40.0	3.81	3.81	0.00	22.58	0.37	40.0	1.15	1.04	1.03
50.0	3.82	3.83	0.01	22.64	0.45	50.0	1.14	1.04	1.03
100.0	3.85	3.85	0.00	22.82	0.84	100.0	1.15	1.03	1.03
150.0	3.86	3.88	0.02	22.89	1.18	150.0	1.14	1.05	1.03
200.0	3.87	3.91	0.04	23.08	1.56	200.0	1.14	1.06	1.04
250.0	3.87	3.94	0.07	23.38	1.89	250.0	1.15	1.07	1.06
300.0	3.88	3.98	0.10	23.71	2.25	300.0	1.16	1.09	1.08
350.0	3.88	4.01	0.13	24.02	2.59	350.0	1.17	1.10	1.10
400.0	3.88	4.06	0.18	24.38	2.93	400.0	1.18	1.12	1.12
450.0	3.88	4.11	0.23	24.81	3.29	450.0	1.20	1.14	1.14
500.0	3.88	4.17	0.29	25.29	3.63	500.0	1.21	1.17	1.17
550.0	3.89	4.23	0.34	25.82	3.97	550.0	1.23	1.20	1.21
600.0	3.89	4.30	0.41	26.30	4.31	600.0	1.24	1.23	1.24
650.0	3.90	4.37	0.47	26.59	4.68	650.0	1.26	1.27	1.28
700.0	3.92	4.45	0.53	26.67	5.00	700.0	1.28	1.31	1.32
750.0	3.93	4.53	0.60	26.50	5.31	750.0	1.30	1.35	1.36
800.0	3.97	4.64	0.67	26.05	5.62	800.0	1.31	1.40	1.41
850.0	4.00	4.73	0.73	25.39	5.92	850.0	1.33	1.44	1.46
900.0	4.04	4.84	0.80	24.52	6.21	900.0	1.35	1.50	1.51
950.0	4.09	4.95	0.86	23.56	6.43	950.0	1.37	1.55	1.57
1000.0	4.15	5.07	0.92	22.58	6.59	1000.0	1.39	1.61	1.63
1050.0	4.22	5.19	0.97	21.63	6.71	1050.0	1.41	1.66	1.70
1100.0	4.30	5.32	1.02	20.70	6.79	1100.0	1.43	1.73	1.76
1150.0	4.39	5.45	1.06	19.80	6.75	1150.0	1.45	1.78	1.84
1200.0	4.48	5.60	1.12	18.97	6.62	1200.0	1.47	1.85	1.92
1250.0	4.59	5.75	1.16	18.24	6.47	1250.0	1.49	1.91	2.00
1300.0	4.70	5.91	1.21	17.53	6.20	1300.0	1.51	1.97	2.09
1350.0	4.82	6.08	1.26	16.88	5.75	1350.0	1.53	2.03	2.18
1400.0	4.95	6.26	1.31	16.29	5.23	1400.0	1.55	2.10	2.28
1450.0	5.09	6.46	1.37	15.75	4.61	1450.0	1.58	2.16	2.38
1500.0	5.24	6.69	1.45	15.27	3.81	1500.0	1.60	2.22	2.49
1550.0	5.37	6.88	1.51	14.76	3.06	1550.0	1.63	2.28	2.62
1600.0	5.53	7.11	1.58	14.32	2.07	1600.0	1.65	2.33	2.75
1650.0	5.69	7.35	1.66	13.91	0.98	1650.0	1.68	2.39	2.89
1700.0	5.84	7.61	1.77	13.56	0.28	1700.0	1.71	2.45	3.02
1750.0	6.01	7.88	1.87	13.19	1.59	1750.0	1.74	2.51	3.19
1800.0	6.18	8.17	1.99	12.89	3.07	1800.0	1.76	2.56	3.35
1850.0	6.35	8.48	2.13	12.59	4.59	1850.0	1.80	2.62	3.53
1900.0	6.51	8.80	2.29	12.29	6.19	1900.0	1.82	2.67	3.71
1950.0	6.69	9.14	2.45	12.03	7.99	1950.0	1.86	2.73	3.92
2000.0	6.86	9.50	2.64	11.79	9.93	2000.0	1.89	2.79	4.11

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


IF/RF MICROWAVE COMPONENTS

REV. OR
SBTCJ-1W+
2/18/2013
Page 3 of 3

2 Way-180° Power Splitter/Combiner

SBTCJ-1W+

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


IF/RF MICROWAVE COMPONENTS

REV. OR
SBTCJ-1W+
2/18/2013
Page 1 of 2

2 Way-180° Power Splitter/Combiner

SBTCJ-1W+

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS




REV. OR
SBTCJ-1W+
2/18/2013
Page 2 of 2

Outline Dimensions

AT790



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
AT790	.150 (3.81)	.150 (3.81)	.150 (3.81)	.050 (1.27)	.030 (0.76)	.025 (0.64)	.028 (0.71)	.050 (1.27)	.160 (4.06)	.030 (0.76)	-- --	.10

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Open style, Ceramic base.
2. Termination finish: Palladium Silver.



P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F15

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
12	8	7	20
			50
			100
			200
		13	500
			1000
			2000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82767	NEW RELEASE	12/26/02	MMG	HY
A	M102713	ADDED "...WITH SMOBC"	10/27/06	MMG	HY


SUGGESTED MOUNTING CONFIGURATION FOR
AT790 CASE STYLE, "nk" PIN CONNECTION



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005 ANGLES $\pm$ FRACTIONS $\pm$	DRAWN	MMG	12/26/02
	CHECKED	AV	12/26/02
	APPROVED	HY	12/26/02



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235



PL, nk, AT790, SBT CJ-1W, TB-227

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Mini-Circuits®

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-117	A
FILE:	98PL117	SCALE:	10:1
SHEET:		1 OF 1	

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215