

# Bandpass Filter

50Ω 460 to 560 MHz


## Maximum Ratings

|                                                                 |                |
|-----------------------------------------------------------------|----------------|
| Operating Temperature                                           | -40°C to 85°C  |
| Storage Temperature                                             | -55°C to 100°C |
| RF Power Input                                                  | 0.5W Max.      |
| Permanent damage may occur if any of these limits are exceeded. |                |

## Pin Connections

|        |                  |
|--------|------------------|
| INPUT  | 1                |
| OUTPUT | 8                |
| GROUND | 2, 3, 4, 5, 6, 7 |

## Outline Drawing




## Outline Dimensions (inch/mm)


| A     | B     | C    | D     | E    | F    |       |
|-------|-------|------|-------|------|------|-------|
| .44   | .74   | .27  | .200  | .07  | .060 |       |
| 11.18 | 18.80 | 6.86 | 5.08  | 1.78 | 1.52 |       |
| G     | H     | J    | K     | L    | M    | wt.   |
| .040  | .660  | .200 | .470  | .055 | .060 | grams |
| 1.02  | 16.76 | 5.08 | 11.94 | 1.40 | 1.52 | 3.0   |

Note: Please refer to case style drawing for details

## Demo Board MCL P/N: TB-368 Suggested PCB Layout (PL-230)



- NOTE:
- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025"±.002". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK




## Features

- high rejection
- flat group delay @ passband
- shielded case
- aqueous washable

## Applications

- mobile TV
- receivers / transmitters
- harmonic rejection

# SXBP-507+



Generic photo used for illustration purposes only

CASE STYLE: HF1139


## +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


## Bandpass Filter Electrical Specifications (T<sub>AMB</sub> = 25°C)

| CENTER FREQ. (MHz) | PASSBAND (MHz)<br>(Loss < 3.5dB) | STOPBANDS (MHz) |                |                |                | VSWR (:1) |      |          |
|--------------------|----------------------------------|-----------------|----------------|----------------|----------------|-----------|------|----------|
|                    |                                  | Loss > 20dB     |                | Loss > 40dB    |                | Passband  |      | Stopband |
| F <sub>c</sub>     | F <sub>1</sub> - F <sub>2</sub>  | F <sub>3</sub>  | F <sub>4</sub> | F <sub>5</sub> | F <sub>6</sub> | Typ.      | Max. | Typ.     |
| 507                | 460 - 560                        | 300             | 615            | 220            | 635 - 2250     | 1.6       | 2.0  | 20       |

## Typical Frequency Response





## Functional Schematic



## Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) |          | Return Loss (dB) | Frequency (MHz) | Group Delay (nSec) |
|-----------------|---------------------|----------|------------------|-----------------|--------------------|
|                 | $\bar{x}$           | $\sigma$ |                  |                 |                    |
| 1.0             | 93.82               | 5.84     | 0.00             | 460.0           | 5.78               |
| 220.0           | 48.63               | 0.24     | 0.07             | 465.0           | 5.80               |
| 300.0           | 31.19               | 0.27     | 0.20             | 470.0           | 5.80               |
| 345.0           | 18.59               | 0.38     | 0.64             | 475.0           | 5.78               |
| 372.0           | 9.38                | 0.47     | 2.44             | 480.0           | 5.79               |
| 390.0           | 4.39                | 0.30     | 9.47             | 485.0           | 5.83               |
| 400.0           | 2.24                | 0.13     | 15.57            | 495.0           | 5.90               |
| 460.0           | 1.41                | 0.06     | 12.80            | 500.0           | 5.91               |
| 485.0           | 1.40                | 0.03     | 14.67            | 505.0           | 6.02               |
| 507.0           | 1.57                | 0.05     | 13.05            | 510.0           | 6.05               |
| 545.0           | 1.75                | 0.03     | 21.96            | 515.0           | 6.23               |
| 560.0           | 2.24                | 0.04     | 13.37            | 520.0           | 6.37               |
| 580.0           | 4.33                | 0.77     | 22.73            | 530.0           | 6.84               |
| 590.0           | 10.81               | 1.85     | 5.86             | 535.0           | 7.21               |
| 600.0           | 19.67               | 1.84     | 2.25             | 540.0           | 7.66               |
| 615.0           | 32.88               | 1.92     | 1.17             | 550.0           | 8.52               |
| 635.0           | 53.72               | 1.69     | 0.72             | 555.0           | 8.93               |
| 2250.0          | 56.17               | 0.13     | 0.32             | 560.0           | 9.34               |



## Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

# Surface Mount Band Pass Filter

**SXBP-507+**

## Typical Performance Data

| FREQ.<br>(MHz) | INSERTION LOSS<br>(dB) |          |          | INPUT RETURN LOSS<br>(dB) |          |          | OUTPUT RETURN LOSS<br>(dB) |          |          |
|----------------|------------------------|----------|----------|---------------------------|----------|----------|----------------------------|----------|----------|
|                | @ -40° C               | @ +25° C | @ +85° C | @ -40° C                  | @ +25° C | @ +85° C | @ -40° C                   | @ +25° C | @ +85° C |
| 1              | 109.05                 | 91.01    | 92.79    | 0.00                      | 0.00     | 0.00     | 0.00                       | 0.00     | 0.00     |
| 10             | 93.34                  | 94.90    | 87.05    | 0.00                      | 0.00     | 0.01     | 0.01                       | 0.00     | 0.01     |
| 50             | 97.76                  | 91.75    | 84.71    | 0.01                      | 0.01     | 0.02     | 0.01                       | 0.00     | 0.02     |
| 100            | 75.12                  | 74.04    | 75.73    | 0.02                      | 0.01     | 0.03     | 0.02                       | 0.00     | 0.03     |
| 200            | 53.06                  | 52.88    | 52.88    | 0.01                      | 0.05     | 0.08     | 0.02                       | 0.06     | 0.09     |
| 220            | 48.87                  | 48.80    | 48.68    | 0.02                      | 0.06     | 0.10     | 0.03                       | 0.08     | 0.12     |
| 300            | 31.41                  | 31.35    | 31.21    | 0.13                      | 0.20     | 0.25     | 0.15                       | 0.24     | 0.29     |
| 345            | 18.61                  | 18.49    | 18.33    | 0.38                      | 0.52     | 0.60     | 0.49                       | 0.65     | 0.77     |
| 390            | 3.13                   | 3.31     | 3.40     | 6.03                      | 6.42     | 6.72     | 8.30                       | 9.27     | 10.12    |
| 400            | 1.81                   | 2.07     | 2.23     | 11.00                     | 11.04    | 11.08    | 18.86                      | 20.09    | 20.73    |
| 460            | 1.14                   | 1.41     | 1.58     | 16.43                     | 16.09    | 15.78    | 15.11                      | 14.91    | 14.74    |
| 485            | 1.10                   | 1.40     | 1.60     | 17.43                     | 16.26    | 15.40    | 17.13                      | 16.05    | 15.16    |
| 500            | 1.22                   | 1.54     | 1.74     | 15.63                     | 14.69    | 14.02    | 15.18                      | 14.29    | 13.60    |
| 507            | 1.27                   | 1.59     | 1.79     | 14.88                     | 14.20    | 13.70    | 14.42                      | 13.74    | 13.25    |
| 545            | 1.57                   | 1.99     | 2.29     | 20.39                     | 18.23    | 16.72    | 26.67                      | 21.92    | 19.04    |
| 560            | 2.12                   | 2.65     | 3.03     | 14.15                     | 13.41    | 12.93    | 13.72                      | 12.77    | 12.02    |
| 580            | 6.17                   | 7.75     | 9.06     | 5.93                      | 5.32     | 4.79     | 6.83                       | 6.11     | 5.51     |
| 590            | 14.46                  | 16.23    | 17.69    | 1.88                      | 1.98     | 1.99     | 2.25                       | 2.35     | 2.34     |
| 600            | 23.29                  | 24.97    | 26.31    | 1.02                      | 1.19     | 1.26     | 1.23                       | 1.42     | 1.49     |
| 615            | 36.56                  | 38.11    | 39.48    | 0.64                      | 0.79     | 0.89     | 0.74                       | 0.91     | 0.99     |
| 635            | 62.69                  | 64.36    | 65.26    | 0.40                      | 0.54     | 0.63     | 0.47                       | 0.63     | 0.70     |
| 700            | 68.58                  | 68.23    | 69.90    | 0.17                      | 0.30     | 0.36     | 0.18                       | 0.32     | 0.38     |
| 800            | 64.40                  | 65.51    | 65.83    | 0.07                      | 0.20     | 0.27     | 0.09                       | 0.21     | 0.27     |
| 900            | 64.88                  | 66.48    | 66.08    | 0.03                      | 0.15     | 0.22     | 0.05                       | 0.17     | 0.22     |
| 1000           | 66.86                  | 69.23    | 69.80    | 0.03                      | 0.16     | 0.23     | 0.04                       | 0.16     | 0.23     |
| 1200           | 74.67                  | 78.99    | 74.88    | 0.03                      | 0.17     | 0.24     | 0.03                       | 0.17     | 0.24     |
| 1300           | 81.52                  | 78.00    | 75.03    | 0.02                      | 0.18     | 0.25     | 0.03                       | 0.19     | 0.27     |
| 1400           | 89.61                  | 77.01    | 84.11    | 0.04                      | 0.19     | 0.28     | 0.03                       | 0.20     | 0.28     |
| 1500           | 82.76                  | 86.05    | 85.90    | 0.02                      | 0.18     | 0.28     | 0.03                       | 0.20     | 0.29     |
| 1600           | 75.18                  | 74.69    | 73.88    | 0.04                      | 0.21     | 0.31     | 0.05                       | 0.22     | 0.31     |
| 1800           | 67.64                  | 69.34    | 72.29    | 0.06                      | 0.24     | 0.35     | 0.05                       | 0.25     | 0.34     |
| 2000           | 75.90                  | 68.89    | 72.14    | 0.06                      | 0.25     | 0.35     | 0.04                       | 0.24     | 0.36     |
| 2200           | 62.66                  | 66.63    | 68.00    | 0.08                      | 0.28     | 0.39     | 0.05                       | 0.26     | 0.38     |
| 2250           | 57.61                  | 59.47    | 53.38    | 0.09                      | 0.29     | 0.40     | 0.06                       | 0.26     | 0.39     |
| 2300           | 66.77                  | 60.53    | 61.14    | 0.09                      | 0.29     | 0.41     | 0.06                       | 0.28     | 0.39     |
| 2400           | 66.51                  | 58.77    | 57.74    | 0.08                      | 0.29     | 0.42     | 0.06                       | 0.26     | 0.40     |
| 2500           | 59.89                  | 57.99    | 52.74    | 0.09                      | 0.30     | 0.45     | 0.07                       | 0.30     | 0.44     |
| 2600           | 57.04                  | 52.15    | 54.36    | 0.11                      | 0.31     | 0.47     | 0.05                       | 0.30     | 0.42     |
| 2800           | 46.58                  | 48.32    | 45.73    | 0.14                      | 0.33     | 0.49     | 0.08                       | 0.31     | 0.48     |
| 3000           | 45.38                  | 45.07    | 47.59    | 0.09                      | 0.33     | 0.49     | 0.07                       | 0.33     | 0.50     |
| 3200           | 42.40                  | 40.81    | 40.67    | 0.17                      | 0.39     | 0.60     | 0.16                       | 0.39     | 0.56     |
| 3300           | 46.54                  | 39.84    | 44.17    | 0.10                      | 0.36     | 0.55     | 0.15                       | 0.40     | 0.59     |
| 3400           | 37.94                  | 40.79    | 40.00    | 0.15                      | 0.40     | 0.62     | 0.10                       | 0.39     | 0.56     |
| 3500           | 38.69                  | 36.00    | 36.13    | 0.19                      | 0.47     | 0.67     | 0.18                       | 0.44     | 0.67     |
| 3600           | 37.02                  | 38.49    | 38.21    | 0.14                      | 0.43     | 0.60     | 0.23                       | 0.47     | 0.68     |
| 3800           | 34.82                  | 37.97    | 36.15    | 0.14                      | 0.47     | 0.65     | 0.17                       | 0.48     | 0.68     |
| 4000           | 30.09                  | 32.35    | 33.81    | 0.26                      | 0.61     | 0.85     | 0.41                       | 0.64     | 0.89     |
| 4200           | 30.07                  | 30.19    | 28.16    | 0.41                      | 0.84     | 1.11     | 0.60                       | 0.69     | 1.14     |
| 4300           | 29.73                  | 30.46    | 28.55    | 0.32                      | 0.91     | 1.13     | 0.35                       | 0.69     | 1.05     |
| 4400           | 25.10                  | 27.39    | 28.18    | 0.62                      | 0.98     | 1.51     | 0.53                       | 1.02     | 1.30     |
| 4500           | 24.60                  | 27.05    | 24.80    | 0.61                      | 1.19     | 1.46     | 0.69                       | 1.24     | 1.67     |
| 4600           | 25.34                  | 25.43    | 27.86    | 0.77                      | 1.32     | 1.46     | 0.95                       | 1.23     | 1.44     |
| 4800           | 21.13                  | 23.20    | 22.20    | 1.00                      | 1.53     | 1.86     | 1.31                       | 1.56     | 2.46     |
| 5000           | 21.62                  | 18.25    | 25.62    | 1.49                      | 2.27     | 2.26     | 1.85                       | 4.56     | 3.09     |

REV. X2  
SXBP-507+  
101121  
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Surface Mount Band Pass Filter

## SXBP-507+

### Typical Performance Data

| FREQ.<br>(MHz) | GROUP DELAY<br>(nsec) |          |          |
|----------------|-----------------------|----------|----------|
|                | @ -40° C              | @ +25° C | @ +85° C |
| 160            | 0.56                  | 0.27     | 0.77     |
| 170            | 1.00                  | 0.59     | 0.55     |
| 180            | 0.56                  | 0.73     | 0.38     |
| 190            | 0.88                  | 0.52     | 0.60     |
| 200            | 0.62                  | 0.53     | 0.53     |
| 220            | 0.81                  | 0.63     | 0.75     |
| 230            | 0.81                  | 0.79     | 0.77     |
| 240            | 0.83                  | 0.74     | 0.81     |
| 250            | 0.82                  | 0.77     | 0.83     |
| 260            | 0.90                  | 0.91     | 0.92     |
| 270            | 1.09                  | 1.10     | 1.10     |
| 280            | 1.22                  | 1.17     | 1.22     |
| 290            | 1.20                  | 1.24     | 1.24     |
| 300            | 1.28                  | 1.28     | 1.34     |
| 320            | 1.81                  | 1.82     | 1.90     |
| 330            | 2.14                  | 2.18     | 2.26     |
| 340            | 2.56                  | 2.62     | 2.69     |
| 350            | 3.10                  | 3.20     | 3.30     |
| 360            | 4.04                  | 4.15     | 4.28     |
| 370            | 5.52                  | 5.65     | 5.79     |
| 380            | 7.45                  | 7.53     | 7.61     |
| 390            | 8.89                  | 8.83     | 8.81     |
| 400            | 8.97                  | 8.83     | 8.73     |
| 410            | 7.96                  | 7.85     | 7.75     |
| 420            | 6.89                  | 6.83     | 6.80     |
| 430            | 6.26                  | 6.24     | 6.24     |
| 440            | 6.00                  | 6.00     | 6.01     |
| 450            | 5.90                  | 5.90     | 5.91     |
| 460            | 5.84                  | 5.85     | 5.86     |
| 465            | 5.83                  | 5.84     | 5.86     |
| 470            | 5.84                  | 5.85     | 5.87     |
| 475            | 5.87                  | 5.88     | 5.91     |
| 480            | 5.90                  | 5.91     | 5.92     |
| 485            | 5.94                  | 5.94     | 5.97     |
| 490            | 5.98                  | 5.98     | 6.01     |
| 495            | 6.02                  | 6.03     | 6.06     |
| 500            | 6.06                  | 6.08     | 6.11     |
| 505            | 6.13                  | 6.15     | 6.18     |
| 507            | 6.21                  | 6.25     | 6.28     |
| 510            | 6.32                  | 6.37     | 6.41     |
| 515            | 6.48                  | 6.53     | 6.60     |
| 520            | 6.68                  | 6.76     | 6.84     |
| 525            | 6.92                  | 7.02     | 7.14     |
| 530            | 7.22                  | 7.33     | 7.48     |
| 535            | 7.58                  | 7.72     | 7.87     |
| 540            | 7.99                  | 8.14     | 8.29     |
| 545            | 8.45                  | 8.60     | 8.75     |
| 550            | 9.01                  | 9.16     | 9.32     |
| 555            | 9.72                  | 9.94     | 10.17    |
| 560            | 10.80                 | 11.14    | 11.49    |
| 570            | 14.15                 | 14.39    | 14.60    |
| 580            | 15.17                 | 14.76    | 14.38    |
| 590            | 11.90                 | 10.96    | 10.15    |
| 600            | 6.91                  | 6.26     | 5.75     |
| 610            | 3.99                  | 3.58     | 3.26     |

REV. X2  
SXBP-507+  
101121  
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



## Typical Performance Curves




### Outline Dimensions



 METALLIZATION  
 SOLDER RESIST

### PCB Land Pattern



| CASE # | A              | B              | C             | D              | E             | F              | G              | H               | J              | K               | L              | M              | WT. GRAMS |
|--------|----------------|----------------|---------------|----------------|---------------|----------------|----------------|-----------------|----------------|-----------------|----------------|----------------|-----------|
| HF1139 | .44<br>(11.18) | .74<br>(18.80) | .27<br>(6.86) | .200<br>(5.08) | .07<br>(1.78) | .060<br>(1.52) | .040<br>(1.02) | .660<br>(16.76) | .200<br>(5.08) | .470<br>(11.94) | .055<br>(1.40) | .060<br>(1.52) | 3.0       |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm 0.015$ "; 3 Pl.  $\pm 0.01$ "

#### Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
  - For RoHS Case Styles: 2-5  $\mu$  inch (.05-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate.
  - For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



# Tape & Reel Packaging TR-F5



| Tape Width,<br>mm | Device Cavity<br>Pitch, mm | Reel Size,<br>inches | Devices per Reel |
|-------------------|----------------------------|----------------------|------------------|
| 32                | 16                         | 13                   | 500              |

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



**Distribution Centers** NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION              | DATE  | DR | AUTH |
|-----|---------|--------------------------|-------|----|------|
| OR  | M101757 | NEW RELEASE (FROM RAVON) | 11/05 | DK | HH   |
| OR  | R62293  | NEW RELEASE (FROM RAVON) | 11/05 | DK | HH   |
|     |         |                          |       |    |      |
|     |         |                          |       |    |      |

**SUGGESTED MOUNTING CONFIGURATION**  
**FOR HF1139 CASE STYLE, cr PIN CONNECTION, 50 OHM.**



## NOTE:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025" ± .002". COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS            | DATE      |
|----------------------------|---------------------|-----------|
| DIMENSIONS ARE IN INCHES   | DRAWN DK (RAVON)    | 29 NOV 05 |
| TOLERANCES ON:             | CHECKED RZ (RAVON)  | 29 NOV 05 |
| 2 PL DECIMALS ±            | APPROVED HH (RAVON) | 29 NOV 05 |
| 3 PL DECIMALS ± .005       |                     |           |
| ANGLES ±                   |                     |           |
| FRACTIONS ±                |                     |           |

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

PL, cr, HF1139, SCLF, TB-368

| SIZE  | CODE IDENT | DRAWING NO: | REV:          |
|-------|------------|-------------|---------------|
| A     | 15542      | 98-PL-230   | OR            |
| FILE: | 98PL230    | SCALE: 4:1  | SHEET: 1 OF 1 |

# Evaluation Board and Circuit



TB-368



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C                                                                                                                                   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak                                                                                          | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |