

2 Way-0° 50Ω 5 to 2500 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	0.5W max.
Internal Dissipation	0.05W max.
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

SUM PORT	8
PORT 1	4
PORT 2	5
GROUND	1,2,3,6,7

Outline Drawing




PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (inch mm)

A	.38	B	.50	C	.25	D	.020	E	.115	F	.070	G	.035	H	.050	J	.090	K	.040
	9.65		12.70		6.35		0.51		2.92		1.78		0.89		1.27		2.29		1.02
L	.105	M	.140	N	.095	P	.010	Q	.055	R	.185	S	--	T	--	wt			
	2.67		3.56		2.41		0.25		1.40		4.70		--		--	grams			0.52

Demo Board MCL P/N: TB-427+
Suggested PCB Layout (PL-274)

- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wideband, 5 to 2500 MHz. useable 0.5 to 2800 MHz
- low amplitude unbalance, 0.1 dB typ.
- low phase unbalance, 1 deg. typ.

Applications

- VHF/UHF
- communications systems
- receivers & transmitters
- instrumentation
- CATV
- cellular, GPS, PCS

Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION (dB)			INSERTION LOSS (dB) ABOVE 3.0 dB			PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)		
	L	M	U	L	M	U	L	M	U	L	M	U
f _L -f _U	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Max.	Typ. Max.	Typ. Max.	Max.	Max.	Max.	Max.	Max.	Max.
5-2500	24 15	18 15	17 14	0.4 0.6	0.7 1.4	1.3 2.4	1.0	3.0	5.0	0.1	0.3	0.5

L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U]

Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
5.00	3.34	3.33	0.01	22.24	0.00	1.07	1.38	1.38
60.00	3.37	3.36	0.01	28.39	0.05	1.08	1.27	1.27
100.00	3.40	3.39	0.01	28.04	0.06	1.10	1.27	1.27
200.00	3.45	3.43	0.01	26.77	0.12	1.14	1.26	1.27
400.00	3.53	3.51	0.03	23.93	0.25	1.22	1.27	1.28
600.00	3.63	3.60	0.04	21.49	0.42	1.31	1.28	1.29
800.00	3.74	3.70	0.04	19.78	0.56	1.38	1.30	1.30
1000.00	3.85	3.84	0.01	18.61	0.61	1.46	1.30	1.29
1200.00	3.97	3.99	0.02	17.78	0.61	1.53	1.31	1.29
1400.00	4.10	4.13	0.02	17.19	0.50	1.60	1.31	1.29
1800.00	4.40	4.37	0.03	16.65	0.09	1.73	1.34	1.30
2000.00	4.54	4.47	0.07	16.74	0.07	1.77	1.36	1.29
2200.00	4.68	4.56	0.13	17.06	0.17	1.77	1.37	1.28
2400.00	4.83	4.65	0.18	17.59	0.20	1.74	1.35	1.25
2500.00	4.92	4.70	0.22	17.88	0.19	1.71	1.33	1.23

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



Generic photo used for illustration purposes only

CASE STYLE: AH202

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

Reel Size 13" Devices/Reel 200

2 Way-0° Power Splitter/Combiner

SYPS-2-252+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR		
	S-1	S-2				S	(:1) 1	2
5	3.30	3.31	0.01	0.01	22.14	1.06	1.37	1.37
10	3.30	3.31	0.01	0.01	24.97	1.06	1.32	1.32
20	3.31	3.32	0.01	0.02	28.32	1.07	1.28	1.28
30	3.32	3.33	0.01	0.04	28.94	1.07	1.27	1.27
40	3.33	3.34	0.01	0.02	29.04	1.07	1.27	1.27
50	3.34	3.34	0.00	0.00	29.02	1.07	1.27	1.27
100	3.36	3.37	0.01	0.00	28.80	1.09	1.26	1.27
150	3.39	3.39	0.00	0.01	28.38	1.11	1.26	1.26
200	3.40	3.41	0.01	0.07	27.85	1.12	1.26	1.26
250	3.42	3.44	0.02	0.06	27.31	1.14	1.26	1.26
300	3.44	3.46	0.02	0.11	26.71	1.16	1.26	1.26
350	3.45	3.47	0.02	0.12	26.07	1.18	1.26	1.26
400	3.47	3.49	0.02	0.15	25.42	1.19	1.26	1.26
450	3.48	3.51	0.03	0.21	24.77	1.21	1.26	1.26
500	3.50	3.54	0.04	0.19	24.15	1.23	1.27	1.27
600	3.53	3.58	0.05	0.22	22.97	1.26	1.27	1.27
700	3.57	3.63	0.06	0.26	21.98	1.30	1.28	1.27
800	3.61	3.68	0.07	0.34	21.14	1.33	1.28	1.27
900	3.65	3.72	0.08	0.42	20.40	1.37	1.29	1.27
1000	3.69	3.78	0.09	0.41	19.74	1.41	1.29	1.28
1050	3.70	3.81	0.09	0.42	19.45	1.43	1.30	1.28
1100	3.74	3.84	0.10	0.48	19.16	1.45	1.30	1.28
1150	3.77	3.87	0.10	0.53	18.88	1.47	1.30	1.28
1200	3.80	3.90	0.10	0.57	18.63	1.49	1.31	1.28
1250	3.82	3.93	0.11	0.60	18.40	1.51	1.32	1.29
1300	3.85	3.95	0.10	0.67	18.18	1.53	1.33	1.29
1350	3.88	3.99	0.11	0.74	17.98	1.55	1.33	1.30
1400	3.91	4.02	0.11	0.82	17.80	1.57	1.34	1.31
1450	3.94	4.05	0.11	0.89	17.64	1.60	1.35	1.31
1500	3.98	4.09	0.11	0.93	17.51	1.62	1.36	1.32
1550	4.02	4.12	0.10	1.00	17.38	1.64	1.37	1.33
1600	4.05	4.15	0.10	1.07	17.26	1.66	1.38	1.34
1650	4.09	4.19	0.10	1.12	17.19	1.69	1.39	1.35
1700	4.12	4.22	0.10	1.17	17.12	1.71	1.40	1.36
1750	4.16	4.25	0.09	1.22	17.08	1.72	1.41	1.37
1800	4.20	4.28	0.08	1.26	17.06	1.74	1.42	1.38
1850	4.23	4.31	0.08	1.38	17.06	1.76	1.43	1.39
1900	4.27	4.33	0.06	4.42	17.10	1.77	1.44	1.40
1950	4.30	4.35	0.05	1.45	17.16	1.78	1.45	1.41
2000	4.33	4.36	0.03	1.53	17.23	1.78	1.45	1.41
2050	4.36	4.37	0.01	1.67	17.34	1.78	1.46	1.41
2100	4.38	4.39	0.01	1.74	17.48	1.77	1.46	1.41
2150	4.41	4.39	0.02	1.81	17.66	1.76	1.46	1.41
2200	4.43	4.39	0.04	1.92	17.84	1.74	1.45	1.40
2250	4.44	4.40	0.04	2.05	18.08	1.72	1.44	1.39
2300	4.46	4.39	0.07	2.11	18.37	1.68	1.43	1.38
2350	4.48	4.40	0.08	2.25	18.66	1.65	1.42	1.37
2400	4.49	4.41	0.08	2.23	19.00	1.61	1.40	1.36
2450	4.51	4.38	0.13	2.28	19.42	1.56	1.38	1.33
2500	4.53	4.39	0.14	2.33	19.81	1.51	1.36	1.31
2600	4.58	4.39	0.19	2.42	20.83	1.40	1.31	1.26
2700	4.64	4.42	0.22	2.38	21.98	1.30	1.26	1.21
3000	5.15	4.71	0.44	1.94	24.94	1.18	1.18	1.19
3500	7.50	6.67	0.83	2.72	16.72	1.08	1.19	1.24

¹ Total Loss = Insertion Loss+ 3dB Splitter Loss

REV. X2
SYPS-2-252+
100706
Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



2 Way-0° Power Splitter/Combiner

SYPS-2-252+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR		
	S-1	S-2				S	(:1) 1	2
5	3.34	3.35	0.01	0.02	15.31	1.11	1.73	1.73
10	3.28	3.29	0.01	0.02	18.72	1.10	1.47	1.47
20	3.22	3.23	0.01	0.02	24.40	1.09	1.27	1.26
30	3.22	3.23	0.01	0.02	28.33	1.09	1.21	1.21
40	3.23	3.23	0.00	0.01	31.45	1.09	1.19	1.18
50	3.23	3.24	0.01	0.04	34.30	1.10	1.18	1.17
100	3.25	3.26	0.01	0.11	44.90	1.11	1.15	1.16
150	3.26	3.27	0.01	0.21	38.59	1.12	1.15	1.16
200	3.28	3.28	0.00	0.33	34.01	1.15	1.16	1.16
250	3.29	3.30	0.01	0.42	31.72	1.16	1.16	1.17
300	3.31	3.32	0.01	0.57	29.98	1.18	1.17	1.17
350	3.32	3.34	0.02	0.66	28.54	1.20	1.18	1.18
400	3.34	3.35	0.01	0.79	27.41	1.22	1.18	1.19
450	3.35	3.36	0.01	0.94	26.42	1.24	1.19	1.19
500	3.36	3.38	0.02	1.01	25.59	1.26	1.20	1.20
600	3.39	3.41	0.02	1.24	24.20	1.29	1.21	1.21
700	3.41	3.44	0.03	1.48	23.06	1.33	1.22	1.22
800	3.45	3.48	0.03	1.78	22.08	1.37	1.24	1.23
900	3.47	3.51	0.04	2.08	21.26	1.40	1.25	1.24
1000	3.51	3.56	0.05	2.20	20.59	1.44	1.27	1.25
1050	3.54	3.59	0.05	2.32	20.26	1.46	1.27	1.26
1100	3.55	3.60	0.05	2.52	19.95	1.48	1.28	1.27
1150	3.57	3.63	0.06	2.68	19.65	1.50	1.29	1.28
1200	3.60	3.65	0.05	2.83	19.39	1.52	1.30	1.28
1250	3.62	3.67	0.05	2.95	19.15	1.54	1.31	1.29
1300	3.64	3.70	0.06	3.14	18.94	1.57	1.32	1.30
1350	3.67	3.72	0.05	3.37	18.74	1.59	1.34	1.31
1400	3.70	3.75	0.05	3.54	18.56	1.61	1.35	1.32
1450	3.72	3.78	0.06	3.77	18.40	1.64	1.36	1.33
1500	3.76	3.81	0.05	3.87	18.26	1.66	1.37	1.34
1550	3.78	3.83	0.05	4.05	18.15	1.68	1.38	1.35
1600	3.81	3.86	0.05	4.24	18.04	1.71	1.40	1.36
1650	3.85	3.89	0.04	4.38	17.94	1.74	1.41	1.38
1700	3.88	3.92	0.04	4.53	17.89	1.76	1.43	1.39
1750	3.92	3.95	0.03	4.69	17.87	1.79	1.45	1.41
1800	3.95	3.97	0.02	4.87	17.86	1.80	1.46	1.42
1850	3.98	4.00	0.02	5.08	17.92	1.82	1.47	1.43
1900	4.02	4.02	0.00	5.28	17.90	1.84	1.49	1.44
1950	4.04	4.06	0.02	5.31	18.04	1.85	1.50	1.46
2000	4.07	4.06	0.01	5.76	18.14	1.85	1.50	1.46
2050	4.10	4.06	0.04	5.69	18.39	1.85	1.51	1.47
2100	4.11	4.07	0.04	5.90	18.53	1.84	1.51	1.47
2150	4.14	4.06	0.07	6.06	18.78	1.84	1.51	1.47
2200	4.15	4.07	0.08	6.27	19.05	1.82	1.51	1.46
2250	4.16	4.09	0.07	6.65	19.34	1.80	1.51	1.47
2300	4.17	4.05	0.12	6.63	19.75	1.76	1.50	1.44
2350	4.18	4.05	0.13	6.88	20.21	1.71	1.48	1.43
2400	4.18	4.03	0.15	7.06	20.74	1.67	1.47	1.42
2450	4.20	4.00	0.20	7.15	21.29	1.63	1.45	1.39
2500	4.21	4.00	0.20	7.39	21.90	1.57	1.43	1.37
2600	4.22	4.02	0.20	7.72	23.07	1.45	1.36	1.33
2700	4.27	3.97	0.30	7.75	24.80	1.32	1.30	1.24
3000	4.68	4.22	0.46	7.92	25.32	1.20	1.17	1.16
3500	6.61	5.78	0.84	4.61	17.62	1.10	1.11	1.16

¹ Total Loss = Insertion Loss+ 3dB Splitter Loss

REV. X2
SYPS-2-252+
100706
Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



2 Way-0° Power Splitter/Combiner

SYPS-2-252+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR		
	S-1	S-2				S	(:1) 1	2
5	3.40	3.42	0.02	0.05	20.46	1.05	1.47	1.47
10	3.40	3.42	0.02	0.05	21.58	1.05	1.44	1.44
20	3.41	3.43	0.02	0.06	22.78	1.05	1.40	1.40
30	3.42	3.44	0.02	0.08	22.84	1.05	1.39	1.40
40	3.43	3.45	0.02	0.08	22.82	1.05	1.39	1.40
50	3.43	3.46	0.03	0.08	22.81	1.05	1.39	1.40
100	3.46	3.49	0.03	0.13	23.00	1.07	1.39	1.39
150	3.49	3.51	0.02	0.10	23.09	1.09	1.38	1.38
200	3.50	3.53	0.03	0.07	23.09	1.10	1.37	1.37
250	3.52	3.56	0.04	0.08	23.17	1.12	1.36	1.36
300	3.54	3.58	0.04	0.04	22.99	1.14	1.36	1.35
350	3.55	3.60	0.05	0.07	22.77	1.16	1.35	1.35
400	3.58	3.62	0.04	0.04	22.53	1.17	1.35	1.35
450	3.59	3.64	0.05	0.01	22.20	1.19	1.35	1.35
500	3.60	3.67	0.07	0.06	21.88	1.21	1.35	1.34
600	3.65	3.73	0.08	0.09	21.25	1.24	1.35	1.34
700	3.69	3.78	0.09	0.12	20.64	1.28	1.34	1.33
800	3.74	3.84	0.10	0.06	20.02	1.31	1.34	1.33
900	3.78	3.90	0.12	0.01	19.41	1.35	1.34	1.32
1000	3.83	3.97	0.14	0.20	18.84	1.39	1.34	1.32
1050	3.87	4.01	0.14	0.24	18.56	1.41	1.34	1.32
1100	3.91	4.04	0.13	0.19	18.30	1.43	1.34	1.32
1150	3.93	4.07	0.14	0.16	18.04	1.46	1.35	1.32
1200	3.97	4.11	0.14	0.16	17.82	1.47	1.35	1.32
1250	4.00	4.14	0.14	0.18	17.60	1.50	1.35	1.32
1300	4.03	4.18	0.15	0.11	17.39	1.52	1.36	1.32
1350	4.07	4.22	0.15	0.00	17.22	1.54	1.36	1.33
1400	4.10	4.26	0.16	0.05	17.05	1.57	1.37	1.33
1450	4.14	4.29	0.15	0.14	16.89	1.59	1.37	1.33
1500	4.17	4.33	0.16	0.09	16.77	1.61	1.38	1.34
1550	4.22	4.37	0.15	0.14	16.66	1.63	1.39	1.35
1600	4.25	4.39	0.14	0.17	16.54	1.65	1.39	1.35
1650	4.29	4.43	0.14	0.18	16.48	1.67	1.40	1.36
1700	4.33	4.46	0.13	0.19	16.41	1.69	1.41	1.37
1750	4.36	4.50	0.14	0.26	16.36	1.70	1.42	1.37
1800	4.39	4.52	0.13	0.29	16.34	1.71	1.42	1.37
1850	4.43	4.56	0.13	0.31	16.35	1.73	1.43	1.38
1900	4.47	4.58	0.11	0.40	16.36	1.73	1.43	1.39
1950	4.49	4.61	0.12	0.31	16.44	1.74	1.43	1.39
2000	4.52	4.61	0.09	0.62	16.45	1.73	1.44	1.38
2050	4.56	4.63	0.07	0.48	16.60	1.73	1.44	1.39
2100	4.58	4.64	0.06	0.56	16.67	1.72	1.43	1.38
2150	4.61	4.64	0.03	0.62	16.80	1.71	1.43	1.38
2200	4.63	4.66	0.03	0.70	16.98	1.69	1.42	1.38
2250	4.64	4.66	0.02	0.84	17.16	1.66	1.41	1.36
2300	4.67	4.66	0.01	0.79	17.39	1.63	1.40	1.35
2350	4.69	4.67	0.02	0.90	17.63	1.60	1.38	1.34
2400	4.70	4.68	0.02	0.90	17.85	1.56	1.37	1.32
2450	4.74	4.67	0.07	0.87	18.19	1.52	1.35	1.30
2500	4.76	4.69	0.07	0.95	18.49	1.48	1.32	1.28
2600	4.81	4.71	0.09	0.84	19.18	1.39	1.28	1.24
2700	4.90	4.72	0.18	0.85	20.07	1.30	1.24	1.20
3000	5.41	5.07	0.34	0.19	22.48	1.22	1.19	1.21
3500	7.58	6.92	0.66	4.33	17.10	1.04	1.24	1.31

¹ Total Loss = Insertion Loss+ 3dB Splitter Loss

REV. X2
SYPS-2-252+
100706
Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




2 Way-0° Power Splitter/Combiner


SYPS-2-252+

Typical Performance Curves


Total Loss




Total Loss S-1 vs. TEMPERATURE




Amplitude Unbalance vs. TEMPERATURE



Phase Unbalance vs. TEMPERATURE



Isolation 1-2 vs. TEMPERATURE



REV. X2
SYPS-2-252+
100706
Page 1 of 2



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



2 Way-0° Power Splitter/Combiner

SYPS-2-252+

Typical Performance Curves



REV. X2
SYPS-2-252+
100706
Page 2 of 2



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see


Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Outline Dimensions

AH202-2



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P
AH202-2	.38 (9.65)	.50 (12.70)	.25 (6.35)	.020 (0.51)	.115 (2.92)	.070 (1.78)	.035 (0.89)	.050 (1.27)	.090 (2.29)	.040 (1.02)	.105 (2.67)	.140 (3.56)	.095 (2.41)	.010 (0.25)
CASE#	Q	R	WT, GRAM											
AH202-2	.055 (1.40)	.185 (4.70)	.52											

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm.01$; 3 Pl. $\pm.005$

Notes:

- Case material: Plastic.
- Base material: Printed wiring laminate.
- Termination finish:
 For RoHS 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 All models, (+) suffix.
 For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits
 ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F61



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	12	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M110938	NEW RELEASE	04/12/07	AV	HY

SUGGESTED MOUNTING CONFIGURATION FOR
AH202-2 CASE STYLE, "sb" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

AV

04/11/07

TOLERANCES ON:

CHECKED

IL


04/12/07

2 PL DECIMALS $\pm$

APPROVED

HY

04/12/07

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$ 

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
 Brooklyn NY 11235

PL, sb, AH202-2, SYPS-2, TB-427+

SIZE
 A

CODE IDENT
 15542

DRAWING NO:
 98-PL-274


REV:
 OR

FILE: 98PL274


SCALE: 6:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-427+



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or its equivalent, Dielectric Constant=3.5, Thickness=.030"

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215