

Bandpass Filter

SXBP-100+

50Ω 87 to 117 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.25W Max.
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

INPUT	1
OUTPUT	8
GROUND	2, 3, 4, 5, 6, 7

Outline Drawing





Outline Dimensions (inch/mm)

A	B	C	D	E	F	
.44	.74	.27	.200	.07	.060	
11.18	18.80	6.86	5.08	1.78	1.52	
G	H	J	K	L	M	wt.
.040	.660	.200	.470	.055	.060	grams
1.02	16.76	5.08	11.94	1.40	1.52	3.0

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-368 Suggested PCB Layout (PL-230)



Features

- high rejection
- good VSWR, 1.3:1 typ @ passband
- shielded case
- aqueous washable


Applications

- radio
- test equipment
- receivers / transmitters
- harmonic rejection


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 3dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss > 40dB		Passband		Stopband
F _c	F ₁ - F ₂	F ₃	F ₄	F ₅	F ₆	Typ.	Max.	Typ.
100	87 - 117	66	143	55	175 - 1500	1.3	1.7	20

Typical Frequency Response





Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
	$\bar{x}$	σ			
1	101.48	3.67	0.01	87	32.84
55	48.64	0.58	0.07	88	30.34
66	29.62	0.77	0.27	89	29.32
70	21.58	0.91	0.49	90	28.52
75	10.14	1.07	2.15	92	27.22
78	4.46	0.73	7.86	94	26.42
80	2.65	0.36	17.52	96	25.80
87	1.55	0.05	16.07	98	25.30
95	1.42	0.03	19.31	100	24.88
100	1.43	0.04	27.69	102	24.53
110	1.64	0.05	17.02	104	24.22
117	2.08	0.07	20.71	106	24.12
125	5.20	0.70	5.54	108	24.37
130	11.60	0.86	2.39	110	24.85
140	24.55	0.66	1.02	111	25.33
143	27.66	0.62	0.89	112	25.77
175	48.35	0.58	0.48	113	26.35
1500	61.87	0.63	0.62	117	29.46



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount Band Pass Filter

SXBP-100+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
0.5	104.64	94.31	104.84	0.01	0.00	0.01	0.01	0.01	0.01
1	105.32	98.03	96.01	0.00	0.00	0.01	0.01	0.00	0.01
10	105.44	104.95	99.77	0.01	0.01	0.01	0.00	0.00	0.00
55	48.68	48.41	48.12	0.07	0.08	0.09	0.05	0.08	0.09
60	40.57	40.25	39.95	0.11	0.13	0.15	0.09	0.13	0.15
66	29.81	29.46	29.13	0.24	0.28	0.32	0.22	0.27	0.31
70	21.64	21.28	20.95	0.48	0.56	0.64	0.44	0.52	0.59
75	10.09	9.83	9.62	1.93	2.25	2.55	1.75	2.02	2.24
78	4.22	4.25	4.28	6.54	7.39	8.19	5.79	6.35	6.77
80	2.37	2.54	2.68	14.11	15.62	17.08	11.60	12.09	12.38
87	1.39	1.56	1.69	16.71	16.87	17.12	19.19	19.98	20.90
95	1.27	1.40	1.52	17.27	18.10	19.02	16.86	17.77	18.71
100	1.22	1.38	1.50	30.84	30.30	30.62	22.25	22.51	22.92
110	1.40	1.57	1.72	28.98	27.77	26.54	30.28	30.63	29.49
117	1.81	2.03	2.22	19.31	20.28	21.49	17.96	18.28	18.43
200	61.84	62.24	62.49	0.22	0.25	0.27	0.19	0.24	0.26
300	80.79	80.80	80.36	0.15	0.19	0.21	0.12	0.18	0.21
400	84.75	84.90	86.91	0.15	0.19	0.22	0.11	0.18	0.21
500	86.62	88.10	85.01	0.16	0.21	0.24	0.11	0.20	0.23
600	85.96	84.80	85.37	0.16	0.22	0.26	0.12	0.22	0.26
700	88.81	86.29	88.62	0.18	0.25	0.29	0.14	0.25	0.30
800	88.41	85.69	84.33	0.19	0.28	0.33	0.15	0.28	0.34
900	82.05	82.72	78.12	0.23	0.32	0.38	0.17	0.30	0.37
1000	72.39	76.19	71.79	0.26	0.35	0.42	0.19	0.33	0.40
1100	73.20	72.87	73.01	0.27	0.38	0.45	0.22	0.37	0.45
1200	74.15	70.38	74.32	0.30	0.41	0.49	0.25	0.41	0.50
1300	70.38	68.32	69.09	0.34	0.46	0.54	0.27	0.45	0.54
1400	67.34	67.13	67.23	0.37	0.50	0.60	0.30	0.49	0.59
1500	63.07	66.65	66.01	0.42	0.56	0.67	0.34	0.53	0.64
1600	59.08	64.24	58.91	0.47	0.63	0.75	0.38	0.58	0.70
1700	62.10	61.92	66.31	0.54	0.71	0.85	0.41	0.63	0.76
1800	56.16	54.54	56.62	0.61	0.80	0.97	0.44	0.68	0.83
1900	56.72	54.41	53.23	0.73	0.94	1.13	0.50	0.76	0.93
2000	52.63	61.08	54.57	0.80	1.05	1.25	0.61	0.87	1.07
2100	53.25	51.48	51.60	1.09	1.38	1.63	0.68	0.99	1.19
2200	49.50	51.23	52.56	1.44	1.75	2.04	0.83	1.16	1.37
2300	53.22	50.28	54.33	1.84	2.18	2.42	1.05	1.39	1.62
2400	62.09	59.87	64.28	2.22	2.47	2.64	1.29	1.60	1.79
2500	42.41	46.04	41.80	2.51	2.61	2.76	1.44	1.75	1.95
2600	38.38	40.15	38.93	2.44	2.62	2.86	1.52	1.83	2.06
2700	38.84	38.43	37.56	2.51	2.75	3.03	1.63	1.99	2.31
2800	43.47	40.39	40.07	2.65	2.98	3.40	1.91	2.38	2.76
2900	37.78	38.15	35.21	3.14	3.65	4.22	2.35	3.02	3.66
3000	35.70	33.21	32.43	3.86	4.70	5.69	3.20	4.41	5.40
3100	28.07	27.02	26.64	5.37	6.62	7.78	5.25	7.09	7.87
3200	23.16	22.82	23.53	7.66	9.58	10.69	8.88	8.79	7.56
3300	20.15	21.59	22.60	11.40	12.37	11.27	7.17	6.16	5.45
3400	19.87	22.03	23.36	12.14	10.26	8.87	4.55	4.66	4.78
3500	20.89	23.83	25.74	8.15	7.35	6.79	3.78	4.43	5.19
3600	22.89	25.13	28.60	6.30	6.38	6.62	4.19	5.16	6.04
3700	25.99	26.91	27.61	6.24	6.73	7.18	5.25	6.54	7.79
3800	25.42	26.28	26.93	6.31	6.88	7.38	7.00	8.28	9.34
3900	24.44	24.59	24.77	6.66	7.04	7.58	8.80	10.07	10.75
4000	22.38	23.42	22.85	6.94	7.59	7.81	11.33	11.91	12.22

REV. X2

SXBP-100+

101118

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Band Pass Filter

SXBP-100+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
40	1.18	3.83	1.87
50	3.44	4.10	4.21
60	7.04	7.18	7.40
70	17.28	17.94	18.53
80	50.99	49.84	48.86
87	32.20	31.94	31.72
88	30.91	30.70	30.53
89	29.80	29.64	29.52
90	28.82	28.72	28.64
91	28.01	27.95	27.89
92	27.36	27.32	27.28
93	26.81	26.80	26.77
94	26.37	26.36	26.34
95	26.03	26.02	26.00
96	25.73	25.72	25.69
97	25.49	25.46	25.44
98	25.27	25.25	25.20
99	25.05	25.02	24.98
100	24.86	24.83	24.80
101	24.66	24.64	24.60
102	24.48	24.46	24.44
103	24.33	24.32	24.32
104	24.24	24.25	24.27
105	24.19	24.22	24.25
106	24.20	24.26	24.30
107	24.29	24.35	24.40
108	24.43	24.50	24.57
109	24.61	24.69	24.76
110	24.84	24.92	25.00
111	25.10	25.20	25.28
112	25.40	25.50	25.59
113	25.69	25.83	25.94
114	26.03	26.20	26.33
115	26.45	26.66	26.85
116	26.95	27.23	27.49
117	27.62	27.98	28.29
120	31.25	31.78	32.16
130	23.72	22.67	21.82
140	8.28	8.22	8.17
150	4.93	4.97	4.99
160	3.01	3.06	3.03
170	2.32	2.21	2.11
180	1.77	1.69	1.65
190	1.56	1.49	1.61
200	1.38	1.33	1.35
210	1.18	1.18	1.17
220	1.11	1.21	1.23
230	0.96	0.85	0.94
240	0.92	0.96	0.79
250	0.82	0.60	1.19
260	0.76	0.68	0.58
270	1.40	0.06	0.58
280	0.98	0.85	0.78
290	0.29	0.98	0.62
300	0.49	1.58	0.62

REV. X2
SXBP-100+
101118
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE





OUTPUT RETURN LOSS vs. TEMPERATURE



Typical Performance Curves




Outline Dimensions



METALLIZATION
 SOLDER RESIST

PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
HF1139	.44 (11.18)	.74 (18.80)	.27 (6.86)	.200 (5.08)	.07 (1.78)	.060 (1.52)	.040 (1.02)	.660 (16.76)	.200 (5.08)	.470 (11.94)	.055 (1.40)	.060 (1.52)	3.0

Dimensions are in inches (mm). Tolerances: 2 Pl. ± 0.015 "; 3 Pl. ± 0.01 "

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101757	NEW RELEASE (FROM RAVON)	11/05	DK	HH
OR	R62293	NEW RELEASE (FROM RAVON)	11/05	DK	HH

SUGGESTED MOUNTING CONFIGURATION
FOR HF1139 CASE STYLE, cr PIN CONNECTION, 50 OHM.



NOTE:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: $.025 \pm .002$ ". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK


UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$ 

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, cr, HF1139, SCLF, TB-368

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-230

REV:

OR

FILE:

98PL230


SCALE:

4:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-368



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: ROGERS R04350B or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215