



Mini-Circuits®

SURFACE MOUNT

Bi-Directional Coupler

SYDC-19-52HP+

50Ω 19 dB Coupling 30 to 512 MHz 50 Watt

FEATURES

- High power, 50W max. with output load VSWR 2.0 max
- High power, 20W max. with output open or short
- Low mainline loss, 0.3 dB typ.
- Good VSWR, 1.05 typ.



Generic photo used for illustration purposes only

CASE STYLE: AH1647

APPLICATIONS

- Military mobile

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT 25°C¹

Parameter	Condition (MHz)	Min.	Typ.	Max.	Units
Frequency Range		30		512	MHz
Mainline Loss (above theoretical loss 0.05 dB)	30	—	0.2	0.4	dB
	450	—	0.35	0.6	
	512	—	0.4	0.6	
Coupling	30-512	—	19.5	—	dB
	30	19	19.5	20	
	450	19	19.9	20.8	
	512	19	20.0	21	
Coupling Flatness(±)	30-512	—	0.4	0.6	dB
Directivity	30	22	35	—	dB
	450	18	25	—	
	512	16	22	—	
Return Loss (Input)	30	20	30	—	dB
	450	20	23	—	
	512	17	22	—	
Return Loss (Output)	30	26	31	—	dB
	450	23	26	—	
	512	18	24	—	
Return Loss (Coupling)	30	20	30	—	dB
	450	20	25	—	
	512	17	22	—	
Input Power ²	30-100	—	—	30	W
	100-450	—	—	50	
	450-512	—	—	40	

1. Tested on Evaluation Board TB-SYDC1952HP+

2. The user must provide adequate means of heat removal to limit the temperature of ground connections under the PCB to 65°C, in order to ensure proper performance.


At 25°C ambient temperature this requires thermal resistance of the user's PC board heat sink to be 10°C/W or less when the unit is driven at maximum specified RF input power, # W. At higher ambient temperature, with the same heat sink. Input power in watts must not exceed # W x (65°C-Tambient)÷40°C. *Where # =30 W at 30-100 MHz, 50 W at 100-450 MHz and 40 W over 450 to 512 MHz.

MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to 65°C Case*
Storage Temperature	-55°C to 100°C

*Case temperature is defined as temperature on ground leads.
Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



*Electrical schematic is for Bi-Directional coupler with internal transformer(s) that routes DC from all ports to ground

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
ECO-015468
SYDC-19-52HP+
CH/CP/AM
221024

PAGE 1 OF 3



Mini-Circuits

SURFACE MOUNT

Bi-Directional Coupler

SYDC-19-52HP+

50Ω 19 dB Coupling 30 to 512 MHz 50 Watt


PAD CONNECTIONS

INPUT	1
OUTPUT	8
COUPLED (FORWARD)	4
COUPLED (REVERSE)	5
GROUND	2, 3, 6, 7

***PRODUCT MARKING:** SYDC-19-52HP

*Marking may contain other features or characters for internal lot control


SUGGESTED PCB LAYOUT (PL-351)
REFER TO APPLICATION NOTE: [AN-00-017](#)




- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $.030'' \pm .002''$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. SUGGEST TO PROVIDE BRASS COIN FOR BETTER HEAT TRANSFER FROM THE UNIT. OTHERWISE PROVIDE ARRAY OF THERMAL VIAS ADEQUATE TO LIMIT TEMPERATURE OF GROUND CONNECTIONS UNDER THE UNIT TO 65°C.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK
 DENOTES BRASS COIN.

OUTLINE DRAWING



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

OUTLINE DIMENSIONS (Inches mm)

A	B	C	E	F	G	H	J	K
.433	.690	.415	.100	.476	.394	.045	.060	.276
11.00	17.53	10.54	2.54	12.09	10.01	1.14	1.52	7.01
L	M	N	P	Q	R	S	T	wt
.194	.257	.560	.475	.561	.258	.069	.061	grams
4.93	6.53	14.22	12.07	14.25	6.55	1.75	1.55	2.80



Mini-Circuits

SURFACE MOUNT




Bi-Directional Coupler

SYDC-19-52HP+

50Ω 19 dB Coupling 30 to 512 MHz 50 Watt

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)		Directivity (dB)		Return Loss (dB)			
	In-Out	In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd	Cpl Rev
30.00	0.20	19.53	19.39	35.44	35.50	30.87	32.42	31.49	32.72
100.00	0.23	19.66	19.57	35.65	35.56	34.30	36.09	34.74	36.52
150.00	0.23	19.70	19.66	34.87	33.97	36.74	37.48	35.35	38.24
200.00	0.25	19.73	19.73	33.09	33.07	35.32	36.68	34.82	37.69
300.00	0.28	19.77	19.86	29.46	29.31	31.78	34.90	31.48	36.27
350.00	0.31	19.79	19.91	27.51	27.57	29.37	33.28	29.43	35.15
400.00	0.33	19.80	19.93	25.71	25.76	27.22	31.60	27.29	33.32
450.00	0.36	19.81	19.94	23.69	23.83	25.29	29.58	25.50	31.16
500.00	0.40	19.82	19.91	21.89	21.95	23.53	27.79	23.80	29.02
512.00	0.41	19.82	19.90	21.51	21.52	23.16	27.41	23.40	28.52



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Bi-Directional Coupler

SYDC-19-52HP+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS		COUPLING		DIRECTIVITY		RETURN LOSS			
	(dB)		(dB)		(dB)		(dB)			
	IN-OUT	FWD-REV	IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
30.0	0.20	0.23	19.53	19.39	35.50	35.44	30.87	32.42	31.49	32.72
40.0	0.22	0.25	19.57	19.42	36.32	36.30	31.50	33.60	32.29	33.81
50.0	0.23	0.25	19.60	19.45	36.09	36.33	32.04	34.21	32.75	34.44
60.0	0.23	0.25	19.62	19.47	35.95	36.29	32.56	34.71	33.27	35.02
70.0	0.23	0.25	19.64	19.50	36.10	36.18	33.06	35.17	33.67	35.62
80.0	0.23	0.25	19.65	19.53	35.84	35.86	33.66	35.56	34.12	36.10
90.0	0.23	0.25	19.66	19.55	35.81	35.80	34.02	35.86	34.44	36.37
100.0	0.23	0.25	19.66	19.57	35.56	35.65	34.30	36.09	34.74	36.52
150.0	0.23	0.26	19.70	19.66	33.97	34.87	36.74	37.48	35.35	38.24
175.0	0.24	0.26	19.72	19.69	33.59	33.89	35.78	36.94	35.36	37.47
200.0	0.25	0.27	19.73	19.73	33.07	33.09	35.32	36.68	34.82	37.69
225.0	0.26	0.28	19.74	19.77	32.35	32.22	34.71	36.49	34.19	37.83
250.0	0.26	0.29	19.76	19.80	31.39	31.34	33.83	36.11	33.37	37.33
275.0	0.27	0.30	19.77	19.84	30.31	30.39	32.86	35.57	32.44	36.86
300.0	0.28	0.31	19.77	19.86	29.31	29.46	31.78	34.90	31.48	36.27
325.0	0.29	0.32	19.78	19.89	28.42	28.41	30.58	34.06	30.47	35.79
350.0	0.31	0.33	19.79	19.91	27.57	27.51	29.37	33.28	29.43	35.15
375.0	0.32	0.34	19.79	19.93	26.65	26.61	28.23	32.45	28.32	34.25
400.0	0.33	0.36	19.80	19.93	25.76	25.71	27.22	31.60	27.29	33.32
425.0	0.34	0.37	19.81	19.94	24.78	24.69	26.27	30.63	26.38	32.27
450.0	0.36	0.39	19.81	19.94	23.83	23.69	25.29	29.58	25.50	31.16
475.0	0.38	0.40	19.82	19.93	22.85	22.76	24.36	28.62	24.61	30.05
500.0	0.40	0.42	19.82	19.91	21.95	21.89	23.53	27.79	23.80	29.02
505.0	0.40	0.43	19.82	19.91	21.77	21.73	23.39	27.62	23.64	28.78
510.0	0.40	0.43	19.82	19.90	21.58	21.55	23.23	27.44	23.48	28.57
512.0	0.41	0.43	19.82	19.90	21.52	21.51	23.16	27.41	23.40	28.52
525.0	0.41	0.44	19.82	19.89	21.08	20.99	22.77	26.94	23.00	28.00



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS







REV. OR
SYDC-19-52HP+
9/7/2012
Page 1 of 1

Bi-Directional Coupler

SYDC-19-52HP+

Typical Performance Curves



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


IF/RF MICROWAVE COMPONENTS



REV. OR
SYDC-19-52HP+
9/7/2012
Page 1 of 1

Outline Dimensions

AH1647



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
AH1647	.433 (11.00)	.690 (17.53)	.415 (10.54)	- -	.100 (2.54)	.476 (12.09)	.394 (10.01)	.045 (1.14)	.060 (1.52)	.276 (7.01)	.194 (4.93)	.257 (6.53)	.560 (14.22)

CASE #	P	Q	R	S	T	WT, GRAM
AH1647	.475 (12.07)	.561 (14.25)	.258 (6.55)	.069 (1.75)	.061 (1.55)	2.80

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm.01$; 3 Pl. $\pm.005$

Notes:

- Case material: Nickel Silver alloy.
- Base material: Printed wiring laminate.
- Termination finish: Tin copper solder alloy up to 0.07% Nickel. All models, (+) suffix.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F109




Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.


Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION		REVISIONS					
		REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
		OR	M133287	NEW RELEASE	08/26/11	GF	WP

**SUGGESTED MOUNTING CONFIGURATION FOR
AH1647 CASE STYLE, "08DC05" PIN CODE**



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. SUGGEST TO PROVIDE BRASS COIN FOR BETTER HEAT TRANSFER FROM THE UNIT. OTHERWISE PROVIDE ARRAY OF THERMAL VIAS ADEQUATE TO LIMIT TEMPERATURE OF GROUND CONNECTIONS UNDER THE UNIT TO 65°C.
3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK
-  DENOTES BRASS COIN.


UNLESS OTHERWISE SPECIFIED		INITIALS		DATE		Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235			
DIMENSIONS ARE IN INCHES		DRAWN	GF	08/22/11		PL, 08DC05, AH1647, TB-630+			
TOLERANCES ON:		CHECKED	IL	08/25/11					
2 PL DECIMALS ±		APPROVED	WP	08/26/11					
3 PL DECIMALS ± .005									
ANGLES ±									
FRACTIONS ±									
Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY INTENDED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, & MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.									
ASHEETA1.DWG REV:A						DATE:01/12/95			
SIZE A		CODE IDENT 15542		DRAWING NO: 98-PL-351		REV: OR			
FILE: 98PL351		SCALE: 4:1		SHEET: 1 OF 1					

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit



Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent.
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 65° C Case Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215