

Surface Mount Directional Coupler

50Ω 10 to 750 MHz

TCD-10-1WX+

Features

- wideband, 10 to 750 MHz
- low mainline loss, 1.2 dB typ.
- aqueous washable
- leads for excellent solderability
- protected by US Patent 6,140,887

Applications

- VHF/UHF
- signal sampling
- communications



Generic photo used for illustration purposes only

CASE STYLE: DB1627

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500
13"	1000, 2000

Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		10		750	MHz
Mainline Loss ¹	10 - 100	—	1.3	2.1	dB
	100 - 350	—	1.2	1.6	
	350 - 750	—	1.4	2.0	
Nominal Coupling		—	10.3±0.5	—	dB
Coupling Flatness(±)		—	±0.8	—	dB
Directivity	10 - 100	17	22	—	dB
	100 - 350	14	18	—	
	350 - 750	—	15	—	
VSWR	10 - 750		1.3		:1
Input Power	10 - 100	—	—	0.5	W
	100 - 750	—	—	1.0	

1. Mainline loss includes theoretical power loss at coupled port.

Maximum Ratings

Parameter	Ratings
Operating Temperature	-40°C to 85°C*
Storage Temperature	-55°C to 100°C


Permanent damage may occur if any of these limits are exceeded.

* Case temperature is defined as temperature on ground leads.


Pin Connections

Function	Pin Number
INPUT	3
OUTPUT	4
COUPLED	1
GROUND	2
50Ω TERM EXTERNAL	6
NOT USED	5

Product Marking



Electrical Schematic




* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M151107
ED-8551
TCD-10-1WX+
WP/CP/AM
191009
Page 1 of 2


Outline Drawing




Outline Dimensions (inch)

A	B	C	D	E	F
.160	.150	.160	.050	.040	.025
4.06	3.81	4.06	1.27	1.02	0.64
G	H	J	K	wt	
.028	.065	.190	.030	grams	
0.71	1.65	4.83	0.76	0.15	

PCB Land Pattern



Demo Board MCL P/N: TB-71
Suggested PCB Layout (PL-009)






RESISTOR R1: 49.9 ± 1% Ohm, 0805 SIZE

- NOTES:**
1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	In	Return Loss (dB) Out	Cpl
9.00	1.18	10.17	22.87	17.95	27.94	17.96
15.00	1.18	10.14	22.85	18.48	30.46	18.53
24.00	1.18	10.13	22.75	18.67	31.68	18.74
30.00	1.18	10.14	22.68	18.71	31.90	18.79
50.00	1.20	10.16	22.53	18.77	31.89	18.87
70.00	1.21	10.16	22.38	18.78	31.59	18.90
100.00	1.21	10.17	22.13	18.78	30.97	18.93
300.00	1.25	10.31	19.54	18.13	26.04	18.34
500.00	1.32	10.49	16.70	17.08	22.79	17.34
800.00	1.47	10.73	13.13	15.61	19.73	15.58



Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Directional Coupler

TCD-10-1WX+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
10.0	1.14	9.98	21.77	18.91	30.69	18.75
20.0	1.14	10.00	21.89	19.11	32.82	18.88
30.0	1.15	10.01	21.87	19.16	33.20	18.90
40.0	1.15	10.01	21.85	19.20	33.12	18.91
50.0	1.16	10.02	21.81	19.22	33.18	18.93
100.0	1.17	10.06	21.59	19.35	32.16	19.02
150.0	1.18	10.09	21.27	19.39	30.87	19.04
200.0	1.19	10.12	20.82	19.37	29.52	19.00
250.0	1.20	10.14	20.34	19.31	28.33	18.91
300.0	1.21	10.17	19.78	19.21	27.27	18.78
350.0	1.22	10.19	19.20	19.06	26.43	18.62
375.0	1.23	10.19	18.91	19.00	26.04	18.54
400.0	1.23	10.20	18.60	18.93	25.62	18.46
450.0	1.25	10.22	17.98	18.79	24.93	18.28
500.0	1.26	10.24	17.35	18.67	24.32	18.10
550.0	1.28	10.26	16.72	18.49	23.83	17.92
600.0	1.29	10.27	16.10	18.33	23.38	17.76
650.0	1.31	10.29	15.47	18.21	22.89	17.59
700.0	1.33	10.30	14.88	18.10	22.48	17.45
750.0	1.35	10.32	14.32	17.94	22.12	17.32
800.0	1.37	10.33	13.73	17.84	21.88	17.20
900.0	1.42	10.33	12.69	17.61	21.34	17.02
1000.0	1.48	10.34	11.70	17.35	20.97	16.89
1100.0	1.54	10.34	10.78	17.16	20.70	16.79
1200.0	1.62	10.33	9.95	16.91	20.50	16.72
1300.0	1.70	10.31	9.17	16.70	20.46	16.65
1400.0	1.80	10.29	8.46	16.46	20.46	16.62
1500.0	1.91	10.29	7.78	16.22	20.48	16.59
1600.0	2.03	10.28	7.13	15.93	20.72	16.57
1700.0	2.16	10.28	6.55	15.58	20.98	16.49
1800.0	2.31	10.29	5.98	15.17	21.37	16.34
1900.0	2.48	10.31	5.49	14.75	21.79	16.14
2000.0	2.67	10.36	5.00	14.24	22.34	15.86
2100.0	2.87	10.42	4.57	13.73	22.92	15.48
2200.0	3.10	10.51	4.13	13.16	23.63	14.99
2300.0	3.33	10.63	3.67	12.57	24.72	14.41
2400.0	3.58	10.78	3.33	11.95	25.37	13.73
2500.0	3.85	10.94	2.97	11.38	26.18	13.07
2600.0	4.13	11.12	2.63	10.79	26.20	12.41
2700.0	4.42	11.33	2.33	10.21	25.17	11.76
2800.0	4.71	11.57	2.08	9.66	23.64	11.09
2900.0	5.01	11.84	1.88	9.14	21.80	10.40
3000.0	5.30	12.10	1.65	8.65	20.37	9.82
3100.0	5.58	12.38	1.50	8.18	18.96	9.26
3200.0	5.86	12.64	1.34	7.77	17.63	8.77
3300.0	6.13	12.93	1.26	7.37	16.46	8.31
3400.0	6.39	13.19	1.21	7.04	15.43	7.89
3500.0	6.64	13.45	1.19	6.70	14.51	7.51
3600.0	6.89	13.71	1.22	6.40	13.59	7.16
3700.0	7.11	13.95	1.26	6.12	12.94	6.88
3800.0	7.29	14.15	1.42	5.90	12.35	6.61
3900.0	7.52	14.35	1.59	5.68	11.80	6.40
4000.0	7.72	14.53	1.79	5.50	11.32	6.18



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. X1

TCD-10-1WX+

10/18/2011

Page 1 of 3

Directional Coupler

TCD-10-1WX+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
10.0	1.19	9.94	20.65	17.64	22.95	17.51
20.0	1.07	9.87	21.22	19.22	27.61	19.02
30.0	1.04	9.87	21.52	19.77	29.96	19.52
40.0	1.03	9.87	21.74	20.09	31.20	19.81
50.0	1.02	9.87	21.87	20.29	32.01	20.01
100.0	1.02	9.90	21.66	20.29	31.97	20.07
150.0	1.02	9.92	21.35	20.21	31.09	20.05
200.0	1.04	9.93	21.11	20.22	29.12	20.04
250.0	1.05	9.94	20.52	19.95	27.82	19.70
300.0	1.06	9.96	20.05	19.86	27.00	19.49
350.0	1.08	9.97	19.49	19.55	26.05	19.16
375.0	1.08	9.98	19.19	19.43	25.63	19.03
400.0	1.09	9.98	18.92	19.33	25.22	18.92
450.0	1.11	10.00	18.35	19.05	24.35	18.62
500.0	1.12	10.01	17.71	18.83	23.66	18.35
550.0	1.14	10.02	17.13	18.60	23.12	18.12
600.0	1.15	10.03	16.51	18.36	22.65	17.82
650.0	1.17	10.04	15.91	18.22	22.18	17.62
700.0	1.19	10.04	15.35	18.02	21.70	17.39
750.0	1.21	10.05	14.81	17.84	21.34	17.18
800.0	1.23	10.05	14.27	17.68	21.03	17.00
900.0	1.28	10.05	13.20	17.31	20.40	16.78
1000.0	1.34	10.05	12.20	16.97	19.94	16.50
1100.0	1.40	10.04	11.22	16.64	19.49	16.31
1200.0	1.47	10.02	10.39	16.36	19.25	16.48
1300.0	1.54	10.00	9.56	16.09	19.14	16.09
1400.0	1.64	9.98	8.78	15.84	19.13	16.31
1500.0	1.74	9.96	8.09	15.60	19.12	16.00
1600.0	1.85	9.95	7.36	15.41	19.39	16.12
1700.0	1.98	9.95	6.75	15.02	19.61	15.94
1800.0	2.12	9.96	6.18	14.69	20.05	15.84
1900.0	2.29	9.99	5.62	14.21	20.34	15.49
2000.0	2.48	10.03	5.13	13.67	20.97	15.59
2100.0	2.70	10.11	4.58	13.04	21.48	15.17
2200.0	2.92	10.22	4.15	12.74	22.62	14.34
2300.0	3.16	10.35	3.65	12.03	23.68	14.00
2400.0	3.44	10.53	3.24	11.33	24.66	13.14
2500.0	3.71	10.72	2.85	10.81	26.16	12.48
2600.0	4.01	10.94	2.50	10.30	26.98	11.65
2700.0	4.31	11.19	2.16	9.74	26.37	11.08
2800.0	4.64	11.49	1.88	9.13	24.35	10.35
2900.0	4.97	11.84	1.65	8.53	21.89	9.52
3000.0	5.26	12.13	1.40	8.08	20.21	9.14
3100.0	5.56	12.46	1.24	7.59	18.65	8.67
3200.0	5.85	12.81	1.08	7.16	17.16	8.04
3300.0	6.11	13.11	0.99	6.80	15.99	7.80
3400.0	6.38	13.44	0.93	6.43	14.87	7.28
3500.0	6.62	13.74	0.96	6.11	13.89	6.97
3600.0	6.86	14.04	0.97	5.81	13.00	6.67
3700.0	7.07	14.30	1.09	5.56	12.35	6.40
3800.0	7.25	14.52	1.30	5.33	11.77	6.17
3900.0	7.44	14.72	1.57	5.14	11.23	6.02
4000.0	7.64	14.93	1.81	4.91	10.78	5.74



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. X1

TCD-10-1WX+

10/18/2011

Page 2 of 3

Directional Coupler

TCD-10-1WX+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +85°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
10.0	1.36	10.19	21.76	17.49	26.57	17.45
20.0	1.36	10.19	21.69	17.60	27.21	17.52
30.0	1.37	10.20	21.57	17.62	27.40	17.50
40.0	1.38	10.21	21.45	17.61	27.45	17.47
50.0	1.38	10.23	21.36	17.62	27.58	17.46
100.0	1.39	10.26	21.18	17.93	27.29	17.65
150.0	1.40	10.30	20.81	18.13	26.91	17.81
200.0	1.40	10.34	20.20	18.14	26.96	17.79
250.0	1.40	10.37	19.76	18.27	26.68	17.86
300.0	1.40	10.40	19.16	18.24	26.18	17.83
350.0	1.41	10.44	18.53	18.18	25.85	17.77
375.0	1.41	10.46	18.23	18.20	25.63	17.76
400.0	1.41	10.47	17.93	18.19	25.35	17.73
450.0	1.43	10.51	17.28	18.14	24.89	17.65
500.0	1.43	10.55	16.62	18.13	24.51	17.56
550.0	1.45	10.58	15.99	18.07	24.20	17.49
600.0	1.46	10.61	15.37	18.00	23.92	17.43
650.0	1.47	10.64	14.75	17.97	23.59	17.39
700.0	1.49	10.67	14.17	17.93	23.28	17.32
750.0	1.51	10.69	13.63	17.86	23.03	17.24
800.0	1.53	10.71	13.09	17.86	22.91	17.21
900.0	1.57	10.73	12.11	17.80	22.55	17.15
1000.0	1.63	10.75	11.21	17.64	22.29	17.12
1100.0	1.70	10.76	10.38	17.50	22.07	17.07
1200.0	1.78	10.76	9.60	17.28	21.89	16.98
1300.0	1.86	10.74	8.90	17.12	21.90	17.01
1400.0	1.97	10.73	8.25	16.90	21.92	16.92
1500.0	2.08	10.72	7.65	16.70	21.95	16.95
1600.0	2.20	10.71	7.06	16.39	22.18	16.88
1700.0	2.33	10.70	6.53	16.02	22.35	16.82
1800.0	2.47	10.70	6.00	15.61	22.71	16.73
1900.0	2.63	10.70	5.56	15.26	23.11	16.64
2000.0	2.80	10.72	5.12	14.85	23.66	16.24
2100.0	2.98	10.74	4.79	14.45	24.01	15.90
2200.0	3.18	10.79	4.39	13.79	24.17	15.61
2300.0	3.37	10.84	3.99	13.31	24.88	15.12
2400.0	3.59	10.91	3.71	12.78	24.86	14.62
2500.0	3.80	10.98	3.42	12.27	24.78	14.02
2600.0	4.04	11.07	3.15	11.70	24.06	13.46
2700.0	4.28	11.18	2.89	11.15	23.07	12.78
2800.0	4.52	11.29	2.67	10.63	21.84	12.28
2900.0	4.78	11.43	2.51	10.14	20.67	11.69
3000.0	5.03	11.57	2.30	9.59	19.66	11.07
3100.0	5.27	11.72	2.16	9.15	18.54	10.38
3200.0	5.53	11.85	1.99	8.71	17.52	9.93
3300.0	5.78	12.03	1.91	8.33	16.47	9.33
3400.0	6.04	12.18	1.82	7.94	15.51	8.88
3500.0	6.31	12.35	1.74	7.51	14.71	8.42
3600.0	6.58	12.53	1.67	7.16	13.88	8.01
3700.0	6.83	12.71	1.64	6.83	13.17	7.65
3800.0	7.05	12.88	1.69	6.57	12.56	7.22
3900.0	7.32	13.04	1.70	6.27	12.00	6.93
4000.0	7.54	13.20	1.76	6.07	11.44	6.70



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. X1

TCD-10-1WX+

10/18/2011


Page 3 of 3

Directional Coupler


Typical Performance Curves

TCD-10-1WX+


Insertion Loss




Insertion Loss vs. TEMPERATURE



Coupling Loss vs. TEMPERATURE






Directivity vs. TEMPERATURE



Directional Coupler

Typical Performance Curves

TCD-10-1WX+



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS

minicircuits.com


REV. X1
TCD-10-1WX+
10/18/2011
Page 2 of 2

Outline Dimensions

DB1627



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
DB1627	.160 (4.06)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (0.64)	.028 (0.71)	.065 (1.65)	.190 (4.83)	.030 (0.76)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
12	8	13	1000, 2000
		7	20, 50, 100, 200, 500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M73159	NEW RELEASE	08/00	IL	DB
A	M82377	UPDATED DRAWING	07/21/02	AV	LC
B	M102713	UPDATED NOTES	01/12/08	GF	IL


SUGGESTED MOUNTING CONFIGURATION FOR DB714 CASE STYLE, "mm" PIN CONNECTION



RESISTOR R1: $49.9 \pm 1\%$ Ohm, 0805 SIZE

NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $0.030'' \pm 0.002''$; COPPER: $1/2$ OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
2 PL DECIMALS $\pm .005$
3 PL DECIMALS $\pm$
ANGLES $\pm$
FRACTIONS $\pm$

DRAWN

IL

08/03/00

CHECKED

WP

08/08/00

APPROVED

DB

08/08/00

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, mm, DB714, TCD, TB-71

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-009


REV:
B

FILE: 98PL009


SCALE: 10:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-71



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215