



Mini-Circuits®

SURFACE MOUNT 

# Directional Coupler

**TCD-9-1W-75X+**

75Ω

5 to 2000 MHz

## FEATURES

- Wideband, 5 to 2000 MHz
- Low mainline loss, 1.3 dB typ. (5-1000 MHz)
- Aqueous washable
- Leads for excellent solderability
- Protected by US Patent 6,140,887



Generic photo used for illustration purposes only

CASE STYLE: DB1627

## APPLICATIONS

- GPS
- Cellular
- Satellite distribution
- CATV

### +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## ELECTRICAL SPECIFICATIONS AT 25°C

| Parameter                                             | Frequency (MHz) | Min. | Typ.    | Max. | Unit |
|-------------------------------------------------------|-----------------|------|---------|------|------|
| Frequency Range                                       | —               | 5    | —       | 2000 | MHz  |
| Mainline Loss <sup>1</sup> (above theoretical 0.1 dB) | 5-50            | —    | 1.3     | 2.1  | dB   |
|                                                       | 50-500          | —    | 1.3     | 2.0  |      |
|                                                       | 500-1000        | —    | 1.8     | 2.4  |      |
|                                                       | 1000-2000       | —    | 2.5     | —    |      |
| Coupling                                              | 5-1000          | —    | 8.9±0.5 | —    | dB   |
|                                                       | 1000-2000       | —    | 8.5±0.5 | —    |      |
| Coupling Flatness (±)                                 | 5-2000          | —    | ±0.6    | —    |      |
| Directivity                                           | 5-50            | 17   | 21      | —    | dB   |
|                                                       | 50-500          | —    | 15      | —    |      |
|                                                       | 500-1000        | —    | 10      | —    |      |
|                                                       | 1000-2000       | —    | 10      | —    |      |
| VSWR                                                  | 5-1000          | —    | 1.30    | —    | :1   |
|                                                       | 1000-2000       | —    | 1.60    | —    |      |
| Input Power                                           | 5-1000          | —    | —       | 0.5  | W    |
|                                                       | 1000-2000       | —    | —       | 1.0  |      |

1. Mainline loss includes theoretical power loss at coupled port.


## MAXIMUM RATINGS

| Parameter             | Ratings        |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C* |
| Storage Temperature   | -55°C to 100°C |

Permanent damage may occur if any of these limits are exceeded.

\* Case temperature is defined as temperature on ground leads.

## ELECTRICAL SCHEMATIC



\*Electrical schematic is for Directional coupler with internal transformer(s) and external termination

Mini-Circuits®

[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)

REV. C  
ECO-014186  
TCD-9-1W-75X+  
WP/CP/AM  
220627  
PAGE 1 OF 3



Mini-Circuits®

SURFACE MOUNT 

## Directional Coupler

TCD-9-1W-75X+


75Ω

5 to 2000 MHz

## PIN CONNECTIONS

|                   |   |
|-------------------|---|
| INPUT             | 3 |
| OUTPUT            | 4 |
| COUPLED           | 1 |
| GROUND            | 2 |
| 75Ω TERM EXTERNAL | 6 |
| NOT USED          | 5 |

PRODUCT MARKING: DL

DEMO BOARD MCL P/N: TB-72  
SUGGESTED PCB LAYOUT (PL-010)

RESISTOR R1: 75 ± 1% Ohm, 0805 SIZE


NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## OUTLINE DRAWING



## PCB Land Pattern



SUGGESTED LAYOUT  
TOLERANCE TO BE WITHIN ±.002

## OUTLINE DIMENSIONS (Inches mm)

| A    | B    | C    | D    | E    | F     |
|------|------|------|------|------|-------|
| .160 | .150 | .160 | .050 | .040 | .025  |
| 4.06 | 3.81 | 4.06 | 1.27 | 1.02 | 0.64  |
| G    | H    | J    | K    |      | wt    |
| .028 | .065 | .190 | .030 |      | grams |
| 0.71 | 1.65 | 4.83 | 0.76 |      | 0.15  |

## TAPE &amp; REEL INFORMATION: F47



Mini-Circuits

SURFACE MOUNT 

# Directional Coupler




TCD-9-1W-75X+

75Ω

5 to 2000 MHz

## TYPICAL PERFORMANCE DATA

| Frequency<br>(MHz) | Mainline Loss<br>(dB) | Coupling<br>(dB) | Directivity<br>(dB) | Return Loss<br>(dB) |       |       |
|--------------------|-----------------------|------------------|---------------------|---------------------|-------|-------|
|                    | In-Out                | In-Cpl           |                     | In                  | Out   | Cpl   |
| 5.00               | 1.29                  | 8.99             | 21.24               | 16.92               | 25.24 | 16.42 |
| 200.00             | 1.28                  | 8.94             | 17.61               | 17.17               | 24.67 | 16.49 |
| 600.00             | 1.46                  | 8.84             | 11.06               | 12.00               | 15.49 | 12.84 |
| 800.00             | 1.63                  | 8.98             | 9.49                | 11.14               | 14.69 | 11.57 |
| 1000.00            | 1.87                  | 8.81             | 8.59                | 11.05               | 14.44 | 10.62 |
| 1200.00            | 2.06                  | 8.50             | 8.12                | 11.15               | 14.53 | 9.81  |
| 1400.00            | 2.27                  | 8.43             | 7.88                | 11.16               | 14.51 | 9.22  |
| 1600.00            | 2.50                  | 8.66             | 7.63                | 11.20               | 15.36 | 8.91  |
| 1800.00            | 2.71                  | 9.00             | 7.19                | 11.56               | 15.46 | 8.40  |
| 2000.00            | 2.73                  | 8.92             | 6.49                | 11.81               | 14.35 | 8.53  |



### NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



# Directional Coupler

# TCD-9-1W-75X+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0 dBm @Temperature = +25°C

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | COUPLING<br>LOSS<br>(dB) | DIRECTIVITY<br>(dB) | RETURN LOSS<br>(dB) |       |       |
|--------------------|---------------------------|--------------------------|---------------------|---------------------|-------|-------|
|                    |                           |                          |                     | IN                  | OUT   | CPL   |
| 5.0                | 1.29                      | 8.93                     | 20.25               | 17.98               | 28.46 | 18.08 |
| 10.0               | 1.26                      | 8.93                     | 20.44               | 18.34               | 34.66 | 18.43 |
| 20.0               | 1.25                      | 8.94                     | 20.55               | 18.59               | 45.81 | 18.68 |
| 50.0               | 1.27                      | 8.96                     | 20.36               | 18.59               | 38.89 | 18.69 |
| 100.0              | 1.29                      | 8.98                     | 19.73               | 18.36               | 30.57 | 18.54 |
| 150.0              | 1.31                      | 8.99                     | 18.88               | 17.87               | 26.57 | 18.22 |
| 200.0              | 1.33                      | 9.00                     | 17.87               | 17.20               | 23.96 | 17.77 |
| 250.0              | 1.35                      | 9.01                     | 16.92               | 16.42               | 22.01 | 17.27 |
| 300.0              | 1.37                      | 9.02                     | 15.98               | 15.73               | 20.51 | 16.69 |
| 350.0              | 1.40                      | 9.03                     | 15.10               | 15.12               | 19.29 | 16.16 |
| 400.0              | 1.43                      | 9.02                     | 14.38               | 14.47               | 18.32 | 15.67 |
| 450.0              | 1.47                      | 9.04                     | 13.60               | 13.87               | 17.53 | 15.18 |
| 500.0              | 1.50                      | 9.05                     | 12.88               | 13.47               | 16.90 | 14.74 |
| 550.0              | 1.54                      | 9.05                     | 12.28               | 13.13               | 16.39 | 14.34 |
| 600.0              | 1.59                      | 9.05                     | 11.78               | 12.75               | 15.97 | 13.98 |
| 650.0              | 1.64                      | 9.06                     | 11.33               | 12.42               | 15.64 | 13.65 |
| 700.0              | 1.68                      | 9.05                     | 10.96               | 12.30               | 15.43 | 13.36 |
| 750.0              | 1.72                      | 9.03                     | 10.71               | 12.19               | 15.29 | 13.13 |
| 800.0              | 1.74                      | 8.98                     | 10.43               | 12.01               | 15.18 | 12.90 |
| 850.0              | 1.78                      | 8.96                     | 10.15               | 11.90               | 15.14 | 12.75 |
| 900.0              | 1.80                      | 8.92                     | 9.90                | 11.93               | 15.14 | 12.60 |
| 950.0              | 1.82                      | 8.88                     | 9.76                | 11.87               | 15.18 | 12.49 |
| 1000.0             | 1.86                      | 8.81                     | 9.76                | 11.68               | 15.15 | 12.37 |
| 1050.0             | 1.85                      | 8.70                     | 9.88                | 11.70               | 15.24 | 12.23 |
| 1100.0             | 1.85                      | 8.63                     | 9.78                | 11.79               | 15.33 | 12.08 |
| 1150.0             | 1.85                      | 8.56                     | 9.60                | 11.65               | 15.40 | 11.90 |
| 1200.0             | 1.86                      | 8.50                     | 9.43                | 11.49               | 15.48 | 11.70 |
| 1300.0             | 1.92                      | 8.44                     | 8.84                | 11.47               | 15.58 | 11.24 |
| 1350.0             | 1.98                      | 8.43                     | 8.53                | 11.21               | 15.57 | 11.00 |
| 1400.0             | 2.05                      | 8.43                     | 8.07                | 11.02               | 15.56 | 10.77 |
| 1450.0             | 2.12                      | 8.42                     | 7.69                | 10.96               | 15.48 | 10.51 |
| 1500.0             | 2.21                      | 8.44                     | 7.35                | 10.78               | 15.35 | 10.26 |
| 1550.0             | 2.33                      | 8.55                     | 6.75                | 10.41               | 15.13 | 9.99  |
| 1600.0             | 2.48                      | 8.66                     | 6.25                | 10.15               | 14.88 | 9.71  |
| 1650.0             | 2.63                      | 8.73                     | 6.06                | 9.98                | 14.58 | 9.39  |
| 1700.0             | 2.80                      | 8.84                     | 5.77                | 9.72                | 14.28 | 9.10  |
| 1750.0             | 2.97                      | 8.93                     | 5.52                | 9.38                | 13.91 | 8.80  |
| 1800.0             | 3.14                      | 9.00                     | 5.42                | 9.21                | 13.58 | 8.51  |
| 1850.0             | 3.28                      | 9.07                     | 5.37                | 9.10                | 13.23 | 8.26  |
| 1900.0             | 3.37                      | 8.99                     | 5.53                | 8.90                | 12.88 | 8.03  |
| 1950.0             | 3.43                      | 8.89                     | 5.87                | 8.71                | 12.50 | 7.83  |
| 2000.0             | 3.51                      | 8.92                     | 5.87                | 8.66                | 12.16 | 7.67  |
| 2050.0             | 3.55                      | 8.93                     | 5.90                | 8.54                | 11.76 | 7.53  |
| 2100.0             | 3.55                      | 8.87                     | 6.35                | 8.29                | 11.38 | 7.40  |
| 2200.0             | 3.50                      | 8.79                     | 7.24                | 8.06                | 10.63 | 7.19  |
| 2300.0             | 3.62                      | 8.97                     | 7.36                | 7.87                | 9.94  | 7.05  |
| 2400.0             | 3.80                      | 9.22                     | 6.96                | 8.00                | 9.43  | 6.97  |
| 2500.0             | 4.17                      | 9.62                     | 6.00                | 8.09                | 9.03  | 6.96  |
| 2600.0             | 4.61                      | 9.84                     | 5.67                | 8.34                | 8.64  | 7.05  |
| 2700.0             | 5.43                      | 10.35                    | 4.90                | 8.35                | 8.22  | 7.22  |
| 2800.0             | 6.04                      | 10.56                    | 4.96                | 8.62                | 7.93  | 7.42  |
| 2900.0             | 6.37                      | 10.11                    | 5.61                | 8.89                | 7.76  | 7.65  |
| 3000.0             | 6.60                      | 9.66                     | 5.77                | 9.39                | 7.72  | 7.94  |



REV. X1

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS

TCD-9-1W-75X+

2/23/2012

Page 1 of 3

# Directional Coupler

# TCD-9-1W-75X+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | COUPLING<br>LOSS<br>(dB) | DIRECTIVITY<br>(dB) | RETURN LOSS<br>(dB) |       |       |
|--------------------|---------------------------|--------------------------|---------------------|---------------------|-------|-------|
|                    |                           |                          |                     | IN                  | OUT   | CPL   |
| 5.0                | 1.45                      | 8.99                     | 19.35               | 16.12               | 20.55 | 16.19 |
| 10.0               | 1.29                      | 8.89                     | 19.86               | 17.86               | 25.20 | 17.94 |
| 20.0               | 1.16                      | 8.82                     | 20.30               | 19.53               | 32.14 | 19.59 |
| 50.0               | 1.13                      | 8.82                     | 20.37               | 20.87               | 37.04 | 20.94 |
| 100.0              | 1.14                      | 8.83                     | 19.82               | 20.19               | 29.65 | 20.39 |
| 150.0              | 1.16                      | 8.84                     | 18.99               | 18.78               | 26.32 | 19.20 |
| 200.0              | 1.18                      | 8.85                     | 18.06               | 18.49               | 24.63 | 19.18 |
| 250.0              | 1.21                      | 8.85                     | 17.11               | 16.95               | 23.05 | 17.84 |
| 300.0              | 1.23                      | 8.87                     | 16.19               | 15.96               | 21.49 | 16.96 |
| 350.0              | 1.26                      | 8.87                     | 15.34               | 15.25               | 19.98 | 16.39 |
| 400.0              | 1.29                      | 8.87                     | 14.62               | 14.21               | 18.64 | 15.45 |
| 450.0              | 1.32                      | 8.88                     | 13.86               | 13.60               | 17.56 | 14.91 |
| 500.0              | 1.36                      | 8.89                     | 13.12               | 13.05               | 16.76 | 14.29 |
| 550.0              | 1.40                      | 8.90                     | 12.53               | 12.61               | 16.13 | 13.76 |
| 600.0              | 1.44                      | 8.89                     | 12.05               | 12.23               | 15.63 | 13.39 |
| 650.0              | 1.49                      | 8.89                     | 11.58               | 11.89               | 15.21 | 13.03 |
| 700.0              | 1.53                      | 8.87                     | 11.26               | 11.90               | 14.92 | 12.88 |
| 750.0              | 1.57                      | 8.84                     | 11.02               | 11.87               | 14.73 | 12.74 |
| 800.0              | 1.58                      | 8.79                     | 10.79               | 11.88               | 14.65 | 12.76 |
| 850.0              | 1.61                      | 8.75                     | 10.53               | 11.98               | 14.70 | 12.85 |
| 900.0              | 1.63                      | 8.70                     | 10.33               | 12.21               | 14.87 | 12.91 |
| 950.0              | 1.63                      | 8.64                     | 10.24               | 12.50               | 15.18 | 13.13 |
| 1000.0             | 1.66                      | 8.59                     | 10.28               | 12.43               | 15.38 | 13.19 |
| 1050.0             | 1.64                      | 8.43                     | 10.49               | 12.61               | 15.80 | 13.21 |
| 1100.0             | 1.63                      | 8.34                     | 10.45               | 12.72               | 16.14 | 13.08 |
| 1150.0             | 1.62                      | 8.25                     | 10.31               | 12.38               | 16.45 | 12.76 |
| 1200.0             | 1.61                      | 8.18                     | 10.16               | 12.04               | 16.71 | 12.37 |
| 1300.0             | 1.66                      | 8.11                     | 9.49                | 11.21               | 16.92 | 11.11 |
| 1350.0             | 1.71                      | 8.10                     | 9.10                | 10.64               | 16.85 | 10.47 |
| 1400.0             | 1.76                      | 8.10                     | 8.53                | 10.10               | 16.67 | 9.88  |
| 1450.0             | 1.83                      | 8.09                     | 8.08                | 9.66                | 16.35 | 9.35  |
| 1500.0             | 1.92                      | 8.11                     | 7.66                | 9.33                | 15.91 | 8.93  |
| 1550.0             | 2.03                      | 8.24                     | 6.96                | 8.95                | 15.36 | 8.61  |
| 1600.0             | 2.17                      | 8.36                     | 6.41                | 8.56                | 14.78 | 8.30  |
| 1650.0             | 2.32                      | 8.43                     | 6.17                | 8.52                | 14.20 | 8.12  |
| 1700.0             | 2.49                      | 8.55                     | 5.87                | 8.64                | 13.69 | 8.11  |
| 1750.0             | 2.67                      | 8.65                     | 5.65                | 8.63                | 13.22 | 8.14  |
| 1800.0             | 2.83                      | 8.71                     | 5.54                | 8.97                | 12.85 | 8.27  |
| 1850.0             | 2.98                      | 8.77                     | 5.50                | 9.36                | 12.59 | 8.50  |
| 1900.0             | 3.05                      | 8.70                     | 5.69                | 9.60                | 12.42 | 8.81  |
| 1950.0             | 3.09                      | 8.59                     | 6.11                | 10.17               | 12.30 | 9.14  |
| 2000.0             | 3.17                      | 8.59                     | 6.17                | 10.45               | 12.21 | 9.38  |
| 2050.0             | 3.18                      | 8.57                     | 6.24                | 10.29               | 12.05 | 9.38  |
| 2100.0             | 3.13                      | 8.50                     | 6.76                | 10.18               | 11.89 | 9.17  |
| 2200.0             | 3.04                      | 8.44                     | 7.77                | 9.17                | 11.41 | 8.14  |
| 2300.0             | 3.10                      | 8.60                     | 7.87                | 7.60                | 10.81 | 6.79  |
| 2400.0             | 3.24                      | 8.87                     | 7.25                | 6.56                | 10.19 | 5.61  |
| 2500.0             | 3.60                      | 9.34                     | 5.86                | 5.46                | 9.52  | 4.78  |
| 2600.0             | 4.03                      | 9.61                     | 5.26                | 5.32                | 8.81  | 4.50  |
| 2700.0             | 4.85                      | 10.15                    | 4.38                | 5.33                | 8.07  | 4.86  |
| 2800.0             | 5.48                      | 10.52                    | 4.16                | 6.07                | 7.53  | 5.78  |
| 2900.0             | 5.88                      | 10.02                    | 4.98                | 8.01                | 7.22  | 7.39  |
| 3000.0             | 6.13                      | 9.70                     | 5.05                | 10.59               | 7.20  | 9.72  |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS

REV. X1

TCD-9-1W-75X+

2/23/2012

Page 2 of 3

# Directional Coupler

## TCD-9-1W-75X+

### Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0 dBm @ Temperature = +85°C

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | COUPLING<br>LOSS<br>(dB) | DIRECTIVITY<br>(dB) | RETURN LOSS<br>(dB) |       |       |
|--------------------|---------------------------|--------------------------|---------------------|---------------------|-------|-------|
|                    |                           |                          |                     | IN                  | OUT   | CPL   |
| 5.0                | 1.49                      | 9.11                     | 20.00               | 16.94               | 26.92 | 17.05 |
| 10.0               | 1.46                      | 9.10                     | 20.14               | 17.19               | 29.78 | 17.31 |
| 20.0               | 1.46                      | 9.10                     | 20.19               | 17.29               | 32.27 | 17.39 |
| 50.0               | 1.47                      | 9.12                     | 19.96               | 16.77               | 32.12 | 16.83 |
| 100.0              | 1.48                      | 9.14                     | 19.40               | 16.86               | 29.12 | 16.93 |
| 150.0              | 1.49                      | 9.14                     | 18.66               | 17.26               | 26.10 | 17.52 |
| 200.0              | 1.51                      | 9.15                     | 17.67               | 16.46               | 23.64 | 17.00 |
| 250.0              | 1.52                      | 9.15                     | 16.82               | 16.17               | 21.76 | 17.07 |
| 300.0              | 1.54                      | 9.15                     | 15.92               | 15.92               | 20.41 | 17.03 |
| 350.0              | 1.57                      | 9.15                     | 15.07               | 15.29               | 19.39 | 16.41 |
| 400.0              | 1.59                      | 9.15                     | 14.38               | 14.96               | 18.65 | 16.32 |
| 450.0              | 1.63                      | 9.16                     | 13.63               | 14.59               | 18.08 | 16.19 |
| 500.0              | 1.66                      | 9.16                     | 12.92               | 14.23               | 17.66 | 15.69 |
| 550.0              | 1.70                      | 9.17                     | 12.33               | 13.98               | 17.30 | 15.35 |
| 600.0              | 1.74                      | 9.17                     | 11.81               | 13.58               | 16.99 | 14.97 |
| 650.0              | 1.78                      | 9.18                     | 11.34               | 13.14               | 16.70 | 14.45 |
| 700.0              | 1.83                      | 9.17                     | 10.98               | 12.96               | 16.45 | 14.09 |
| 750.0              | 1.87                      | 9.16                     | 10.68               | 12.70               | 16.22 | 13.77 |
| 800.0              | 1.89                      | 9.12                     | 10.41               | 12.35               | 16.01 | 13.34 |
| 850.0              | 1.92                      | 9.09                     | 10.13               | 12.11               | 15.78 | 13.11 |
| 900.0              | 1.95                      | 9.08                     | 9.85                | 12.02               | 15.61 | 12.92 |
| 950.0              | 1.98                      | 9.04                     | 9.69                | 11.89               | 15.47 | 12.51 |
| 1000.0             | 2.01                      | 8.99                     | 9.67                | 11.65               | 15.28 | 12.25 |
| 1050.0             | 2.02                      | 8.89                     | 9.77                | 11.61               | 15.18 | 12.16 |
| 1100.0             | 2.04                      | 8.83                     | 9.65                | 11.76               | 15.12 | 11.97 |
| 1150.0             | 2.04                      | 8.77                     | 9.44                | 11.84               | 15.13 | 11.78 |
| 1200.0             | 2.05                      | 8.72                     | 9.27                | 11.83               | 15.18 | 11.74 |
| 1300.0             | 2.13                      | 8.67                     | 8.67                | 12.34               | 15.43 | 11.69 |
| 1350.0             | 2.19                      | 8.66                     | 8.37                | 12.30               | 15.60 | 11.65 |
| 1400.0             | 2.27                      | 8.65                     | 7.93                | 12.24               | 15.81 | 11.64 |
| 1450.0             | 2.35                      | 8.64                     | 7.58                | 12.38               | 16.00 | 11.68 |
| 1500.0             | 2.45                      | 8.66                     | 7.27                | 12.24               | 16.13 | 11.67 |
| 1550.0             | 2.56                      | 8.74                     | 6.71                | 11.84               | 16.15 | 11.45 |
| 1600.0             | 2.72                      | 8.83                     | 6.25                | 11.42               | 16.06 | 11.11 |
| 1650.0             | 2.87                      | 8.90                     | 6.06                | 11.01               | 15.87 | 10.70 |
| 1700.0             | 3.03                      | 8.98                     | 5.82                | 10.56               | 15.52 | 10.16 |
| 1750.0             | 3.19                      | 9.05                     | 5.59                | 9.95                | 15.05 | 9.48  |
| 1800.0             | 3.35                      | 9.10                     | 5.49                | 9.49                | 14.51 | 8.85  |
| 1850.0             | 3.49                      | 9.15                     | 5.46                | 9.21                | 13.94 | 8.37  |
| 1900.0             | 3.58                      | 9.08                     | 5.60                | 8.87                | 13.35 | 7.93  |
| 1950.0             | 3.63                      | 8.98                     | 5.93                | 8.56                | 12.75 | 7.54  |
| 2000.0             | 3.70                      | 9.00                     | 5.93                | 8.46                | 12.21 | 7.34  |
| 2050.0             | 3.75                      | 9.03                     | 5.94                | 8.40                | 11.68 | 7.19  |
| 2100.0             | 3.74                      | 8.96                     | 6.37                | 8.24                | 11.21 | 7.09  |
| 2200.0             | 3.70                      | 8.89                     | 7.20                | 8.31                | 10.45 | 7.23  |
| 2300.0             | 3.84                      | 9.06                     | 7.25                | 8.60                | 9.93  | 7.61  |
| 2400.0             | 4.03                      | 9.28                     | 6.83                | 9.22                | 9.70  | 8.20  |
| 2500.0             | 4.42                      | 9.61                     | 5.91                | 9.64                | 9.60  | 8.65  |
| 2600.0             | 4.86                      | 9.79                     | 5.60                | 9.99                | 9.44  | 8.89  |
| 2700.0             | 5.64                      | 10.23                    | 4.90                | 9.68                | 9.08  | 8.76  |
| 2800.0             | 6.20                      | 10.42                    | 5.00                | 9.41                | 8.67  | 8.19  |
| 2900.0             | 6.46                      | 10.05                    | 5.67                | 9.05                | 8.25  | 7.64  |
| 3000.0             | 6.59                      | 9.69                     | 5.88                | 9.04                | 7.98  | 7.28  |



REV. X1

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS

TCD-9-1W-75X+

2/23/2012


Page 3 of 3

# Directional Coupler


## Typical Performance Curves

**TCD-9-1W-75X+**


Insertion Loss




Insertion Loss vs. TEMPERATURE



Coupling Loss vs. TEMPERATURE




Directivity vs. TEMPERATURE



# Directional Coupler

# TCD-9-1W-75X+


## Typical Performance Curves






## Outline Dimensions

DB1627



## PCB Land Pattern



| CASE # | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| DB1627 | .160<br>(4.06) | .150<br>(3.81) | .160<br>(4.06) | .050<br>(1.27) | .040<br>(1.02) | .025<br>(0.64) | .028<br>(0.71) | .065<br>(1.65) | .190<br>(4.83) | .030<br>(0.76) | .15      |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F47

## DEVICE ORIENTATION IN T&R



| Tape Width,<br>mm | Device Cavity<br>Pitch, mm | Reel Size,<br>inches | Devices per Reel<br>see note |
|-------------------|----------------------------|----------------------|------------------------------|
| 12                | 8                          | 13                   | 1000, 2000                   |
|                   |                            | 7                    | 20, 50, 100, 200, 500        |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

| REV | ECN No. | DESCRIPTION     | DATE     | DR | AUTH |
|-----|---------|-----------------|----------|----|------|
| OR  | M73159  | NEW RELEASE     | 08/00    | IL | DB   |
| A   | M82377  | UPDATED DRAWING | 07/30/02 | AV | LC   |
| B   | M102713 | UPDATED NOTES   | 01/12/06 | GF | IL   |
|     |         |                 |          |    |      |

.018  
 .010  
 .085  
 .052  
 .035  
 .030 TYP  
 TRACE WIDTH  
 (SEE NOTE BELOW)  
 PACKAGE OUTLINE  
 .015 TYP  
 .015  
 .030  
 .047 TYP  
 .023  
 .024  
 .030  
 .108  
 .017  
 4X .0475  
 .275  
 .018  
 PIN 1  
 R1  
 7X  $\varnothing$ .015 PTH FOR GROUND

NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030"  $\pm$  0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.



UNLESS OTHERWISE SPECIFIED

INITIALS

DATE \_\_\_\_\_

**DIMENSIONS ARE IN INCHES**

DRAWN

---

IL

08/03/00

**TOLERANCES ON:**

**CHECKED**

08/08/00

2 PL DECIMALS  $\pm$   
3 PL DECIMALS  $\pm$ 

**APPROVED**

08 / 00 / 00

ANGLES  $\pm$   
FRACTIONS  $\pm$

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.



# Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, mm, 75, DB714, TCD, TB-72

**SIZE**  
**A**

CODE IDENT  
15542

DRAWING NO:  
98-PL-010

REV: B


FILE: 98PL010

SCALE: 10:1


|        |        |
|--------|--------|
| SHEET: | 1 OF 1 |
|--------|--------|

ASHEETA1.DWG REV:A DATE:01/12/95

# Evaluation Board and Circuit



TB-72



Schematic Diagram

## Notes:

1. 75 Ohm BNC Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C                                                                                                                                   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak                                                                                          | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |