## Surface Mount **T** 650 to 4000 MHz

50Ω

#### Features

- wideband, 650 to 4000 MHz
- balanced transmission line
- good return loss
- excellent amplitude unbalance, 0.5 dB typ. and phase unbalance, 3 deg typ. in 1 dB bandwidth
- plastic base with leads
- aqueous washable

#### Applications

- · balanced to unbalanced transformation
- push-pull amplifiers
- PCS/DCS
- MMDS

#### Electri

• MMDS					
Electrical Specifications at 25°	C				
Parameter	Condition	Min.	Тур.	Max.	Unit
Impedance Ratio			1		Ohm
Frequency Range		650		4000	MHz
Insertion Loss*	650-4000 800-3000		2.0 1.0		dB
Amplitude Unbalance	800-3000		0.5		dB
	650-4000 800-3000		0.5		

650-4000

\*Insertion Loss is referenced to mid-band loss, 0.5 dB typ.

#### **Maximum Ratings**

Phase Unbalance

Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mA

Permanent damage may occur if any of these limits are exceeded.


**Product Marking** 

#### **Pin Connections**

4

Function	Pin Number
PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	3
NOT USED	2

Config. G



REV. A HEV. A M151107 TC1-1-43X+ ED-13728A/2 IG/CP/AM 190619 Page 1 of 2

**Mini-Circuits**<sup>®</sup> www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

## TC1-1-43X+



Generic photo used for illustration purposes only

CASE STYLE: AT1521


+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Degree

## TC1-1-43X+

#### **Outline Drawing**




#### Outline Dimensions (inch)

A	B	C	D	E	F
.150	.150	.160	.050	.040	.025
3.81	3.81	4.06	1.27	1.02	0.64
G	H	J	K		wt
.028	.065	.190	.030		grams
0.71	1.65	4.83	0.76		0.15

#### **Typical Performance Data**

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (Deg.)
650.00	0.30	19.40	0.72	7.04
700.00	0.30	19.03	0.70	6.11
800.00	0.32	19.01	0.65	4.73
1000.00	0.35	18.85	0.50	3.45
1600.00	0.45	16.34	0.15	0.32
2000.00	0.53	15.36	0.05	0.42
2600.00	0.62	16.20	0.40	0.66
3000.00	0.57	20.76	0.56	1.07
3800.00	1.34	9.18	0.41	4.79
4000.00	1.71	7.51	0.09	5.95



#### **Additional Notes**

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



## **RF Transformer**

Typical Performance Data

FREQUENCY	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
	(UD)	(0.5)	(db)	(deg.)
650.0	0.30	19.40	0.72	7.04
700.0	0.30	19.03	0.70	6.11
750.0	0.31	19.48	0.65	5.46
800.0	0.32	19.01	0.65	4.73
900.0	0.33	19.01	0.59	4.12
1000.0	0.35	18.85	0.50	3.45
1200.0	0.40	18.26	0.37	1.90
1400.0	0.42	17.29	0.27	1.06
1600.0	0.45	16.34	0.15	0.32
1800.0	0.48	15.68	0.04	0.37
2000.0	0.53	15.36	0.05	0.42
2200.0	0.58	15.34	0.18	0.52
2400.0	0.62	15.45	0.29	0.05
2600.0	0.62	16.20	0.40	0.66
2800.0	0.60	17.83	0.49	1.00
3000.0	0.57	20.76	0.56	1.07
3200.0	0.61	21.60	0.69	0.63
3400.0	0.75	16.64	0.74	1.98
3600.0	1.00	12.03	0.67	3.49
3800.0	1.34	9.18	0.41	4.79
3900.0	1.52	8.24	0.24	5.41
3950.0	1.61	7.64	0.20	5.57
4000.0	1.71	7.51	0.09	5.95





P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site TC1-1-43X+


REV. X1

## **RF Transformer**

### Typical Performance Data









REV. X1 te TC1-1-43X+ 9/8/2011 Page 1 of 1


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

## Case Style

### **Outline Dimensions**

**PCB Land Pattern** 

AT1521



Suggested Layout, Tolerance to be within ±.002

CASE #	А	В	С	D	Е	F	G	Н	J	K	WT. GRAMS
AT1521	.150 (3.81)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (.64)	.028 (.71)	.065 (1.65)	.190 (4.83)	.030 (.76)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. + .01; 3 Pl. + .005

#### Notes:

- 1. Case material: Plastic.
- 2. Termination finish:
  - For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
- 3. Orientation Dot on Top Hat & Marking on the Substrate both refers to Pin #1 of the Unit.
- 4. Top-Hat total thickness: .013 inches MAX.






P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



AT1521 Rev.: AQ (08/05/19) M175718 File:AT1521.DOC This document and its contents are the property of Mini-Circuits. **RF/IF MICROWAVE COMPONENTS** 

# Tape & Reel Packaging TR-F17



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices	s per Reel
			Small	20
			quantity	50
		7	standards	100
12	8		(see note)	200
				500
		13	Standard	1000
		13	Standard	2000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf






P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

**RF/IF MICROWAVE COMPONENTS** 

98-TR-Rev.: C (02/13/18) M166283 File: 98-TR-F17.docx This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTI	ON			REVISIONS			
		ECN No.		SCRIPTION	DATE	DR	AUTH
	OR	M106563		NEW RELEASE	08/23/06		IG
	'   -						
			1		I	1	1
	JGGESTED N					C	
FOR AT224/DB						2	
<u>(FOR S</u>	INGLE ENDE	<u>U TO E</u>	BALANCE	D APPLICATIO	<u>(nc</u>		
.050, 2 PL. FOR GROUND .040 .040 PACKAGE OUTLINE .113 .015 TYP .015 PIN 6 .033							
NOTES: 1. TRACE WID	45° TYP044 TRACE WIDTH, 3 PL. (SEE NOTE 1)						
NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE. 3. THIS PAD IS NOT REQUIRED FOR AT224 CASE STYLE. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER) DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK							
UNLESS OTHERWISE SPECIFIED INITIALS DATE DIMENSIONS ARE IN INCHES 10 DERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± 4 PPROVED IG 08/23/06							
ANGLES ± FRACTIONS ± Mini-Circuits ® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY O	F MINI-CIRCUITS.	PL, g	gs/ha/hd	, AT224/DB714	4, TC/TCM,	TB-	-145
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS AND THE UNITED STATES GOVERNMENT, MINI-CIRCUTS RE DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHT THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DI PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISS	S VENDORS, VENDEE SERVES ALL PROPRIETARY S THERETO. SCLOSED TO ANY OUTSIDE	SIZE A FILE: O	CODE IDENT	DRAWING NO: 98-PL			OR
ASHEETA1.DWG	REV:A DATE:01/12/95		8PL244	SCALE: 8:1		OF	1



## Mini-Circuits

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

ENV02T1 Rev: B 02/25/11 M130240 File: ENV02T1.pdf

This document and its contents are the property of Mini-Circuits.