



Mini-Circuits®

SURFACE MOUNT

## Directional Coupler

TCD-18-4+

50Ω

5 to 1000 MHz

## FEATURES

- Wideband, 5 to 1000 MHz
- Low mainline loss, 0.7 dB typ.
- Aqueous washable
- Leads for excellent solderability
- Protected by US Patent 6,140,887

## APPLICATIONS

- Communications
- Signal sampling
- Level detection



Generic photo used for illustration purposes only

CASE STYLE: DB714

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## ELECTRICAL SPECIFICATIONS AT 25°C

| Parameter                  | Frequency (MHz) | Min. | Typ.     | Max. | Unit |
|----------------------------|-----------------|------|----------|------|------|
| Frequency Range            | —               | 5    | —        | 1000 | MHz  |
| Mainline Loss <sup>1</sup> | 5-50            | —    | 0.7      | 1.3  | dB   |
|                            | 50-500          | —    | 0.7      | 1.3  |      |
|                            | 500-1000        | —    | 1.0      | 1.4  |      |
| Coupling                   | 5-1000          | —    | 17.9±0.5 | —    | dB   |
| Coupling Flatness (±)      | 5-1000          | —    | ±0.6     | —    | dB   |
| Directivity                | 5-50            | 11   | 22       | —    | dB   |
|                            | 50-500          | 15   | 20       | —    |      |
|                            | 500-1000        | —    | 18       | —    |      |
| VSWR                       | 5-1000          | —    | 1.2      | —    | :1   |
| Input Power                | 5-50            | —    | —        | 1.0  | W    |
|                            | 50-1000         | —    | —        | 1.0  |      |

1. Mainline loss includes theoretical power loss at coupled port.


## MAXIMUM RATINGS

| Parameter             | Ratings        |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C* |
| Storage Temperature   | -55°C to 100°C |

Permanent damage may occur if any of these limits are exceeded.

\* Case temperature is defined as temperature on ground leads.

## ELECTRICAL SCHEMATIC



\*Electrical schematic is for Directional coupler with internal transformer(s) and external termination






# Directional Coupler

## TCD-18-4+

5 to 1000 MHz

|                   |   |
|-------------------|---|
| INPUT             | 3 |
| OUTPUT            | 4 |
| COUPLED           | 1 |
| GROUND            | 2 |
| 50Ω TERM EXTERNAL | 6 |
| NOT USED          | 5 |

**DEMO BOARD MCL P/N:** TB-71  
**SUGGESTED PCB LAYOUT** (PL-009)



2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- 
- Lead #1 identifier shall be located in the cross-hatched area shown. Identifier may be either a molded or marked feature.
- COMPONENT AREA
- PICK & PLACE SURFACE AREA (.03X.075)MIN.
- PLASTIC SHAPE ADJACENT TO LEADS MAY VARY
- Dimensions: A, B, C MAX, D TYP, E  $\begin{matrix} +.005 \\ -.009 \end{matrix}$  TYP, F TYP
- Tolerances: .000, .008

Suggested Layout,  
Tolerance to be within  $\pm .002$

|      |      |      |      |      |       |
|------|------|------|------|------|-------|
| A    | B    | C    | D    | E    | F     |
| .160 | .150 | .160 | .050 | .040 | .025  |
| 4.06 | 3.81 | 4.06 | 1.27 | 1.02 | 0.64  |
| G    | H    | J    | K    |      | wt    |
| .028 | .065 | .190 | .030 |      | grams |
| 0.71 | 1.65 | 4.83 | 0.76 |      | 0.15  |





Mini-Circuits

SURFACE MOUNT

# Directional Coupler




TCD-18-4+

50Ω

5 to 1000 MHz

## TYPICAL PERFORMANCE DATA

| Frequency<br>(MHz) | Mainline Loss<br>(dB) | Coupling<br>(dB) | Directivity<br>(dB) | Return Loss<br>(dB) |       |       |
|--------------------|-----------------------|------------------|---------------------|---------------------|-------|-------|
|                    | In-Out                | In-Cpl           |                     | In                  | Out   | Cpl   |
| 5.00               | 0.71                  | 17.93            | 22.13               | 20.96               | 23.54 | 21.00 |
| 100.00             | 0.62                  | 17.76            | 30.64               | 24.40               | 28.02 | 24.20 |
| 200.00             | 0.64                  | 17.80            | 28.81               | 24.53               | 28.17 | 23.85 |
| 300.00             | 0.67                  | 17.85            | 26.73               | 24.53               | 28.03 | 23.28 |
| 400.00             | 0.64                  | 17.89            | 24.88               | 24.44               | 27.55 | 22.54 |
| 500.00             | 0.73                  | 17.92            | 23.27               | 24.18               | 26.78 | 21.86 |
| 600.00             | 0.80                  | 17.96            | 21.85               | 23.87               | 25.93 | 21.34 |
| 700.00             | 0.80                  | 18.00            | 20.56               | 23.48               | 25.07 | 20.77 |
| 800.00             | 0.84                  | 18.03            | 19.55               | 23.03               | 24.24 | 20.27 |
| 1000.00            | 0.92                  | 18.08            | 17.79               | 22.00               | 22.68 | 19.42 |



- NOTES
- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
  - Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
  - The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



# Directional Coupler

# TCD-18-4+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | COUPLING<br>LOSS<br>(dB) | DIRECTIVITY<br>(dB) | RETURN LOSS |       |       |
|--------------------|---------------------------|--------------------------|---------------------|-------------|-------|-------|
|                    |                           |                          |                     | IN          | OUT   | CPL   |
| 5                  | 0.60                      | 17.72                    | 32.43               | 22.70       | 24.99 | 22.66 |
| 10                 | 0.59                      | 17.70                    | 32.68               | 23.13       | 25.73 | 23.09 |
| 20                 | 0.58                      | 17.68                    | 33.19               | 23.97       | 27.22 | 23.94 |
| 50                 | 0.59                      | 17.69                    | 33.64               | 24.25       | 27.82 | 24.18 |
| 100                | 0.61                      | 17.72                    | 34.27               | 24.50       | 28.01 | 24.34 |
| 150                | 0.62                      | 17.74                    | 35.47               | 24.67       | 28.08 | 24.37 |
| 200                | 0.63                      | 17.75                    | 37.18               | 24.82       | 28.21 | 24.33 |
| 250                | 0.63                      | 17.76                    | 38.20               | 24.92       | 28.23 | 24.26 |
| 300                | 0.64                      | 17.77                    | 37.20               | 25.06       | 28.23 | 24.13 |
| 350                | 0.65                      | 17.78                    | 34.85               | 25.25       | 28.15 | 24.02 |
| 400                | 0.66                      | 17.79                    | 32.14               | 25.43       | 28.01 | 23.88 |
| 450                | 0.67                      | 17.80                    | 29.72               | 25.53       | 27.98 | 23.72 |
| 500                | 0.69                      | 17.80                    | 27.68               | 25.66       | 28.03 | 23.54 |
| 550                | 0.70                      | 17.82                    | 25.81               | 25.81       | 27.91 | 23.37 |
| 600                | 0.71                      | 17.82                    | 24.19               | 26.01       | 27.84 | 23.22 |
| 650                | 0.73                      | 17.84                    | 22.78               | 26.05       | 27.79 | 23.04 |
| 700                | 0.74                      | 17.85                    | 21.43               | 26.10       | 27.84 | 22.85 |
| 750                | 0.76                      | 17.86                    | 20.30               | 26.17       | 27.81 | 22.68 |
| 800                | 0.78                      | 17.87                    | 19.22               | 26.36       | 27.76 | 22.54 |
| 850                | 0.80                      | 17.87                    | 18.28               | 26.50       | 27.66 | 22.40 |
| 900                | 0.81                      | 17.87                    | 17.42               | 26.49       | 27.65 | 22.27 |
| 950                | 0.82                      | 17.86                    | 16.62               | 26.52       | 27.68 | 22.13 |
| 1000               | 0.84                      | 17.85                    | 15.92               | 26.64       | 27.57 | 21.99 |
| 1050               | 0.86                      | 17.84                    | 15.25               | 26.76       | 27.52 | 21.87 |
| 1100               | 0.88                      | 17.82                    | 14.67               | 26.91       | 27.59 | 21.75 |
| 1200               | 0.92                      | 17.77                    | 13.51               | 26.97       | 27.55 | 21.56 |
| 1300               | 0.95                      | 17.67                    | 12.66               | 27.21       | 27.51 | 21.32 |
| 1400               | 0.99                      | 17.55                    | 11.90               | 27.19       | 27.30 | 21.10 |
| 1500               | 1.04                      | 17.42                    | 11.24               | 27.20       | 27.10 | 20.89 |
| 1600               | 1.08                      | 17.25                    | 10.71               | 27.30       | 27.01 | 20.71 |
| 1700               | 1.14                      | 17.10                    | 10.16               | 27.31       | 26.67 | 20.50 |
| 1800               | 1.19                      | 16.91                    | 9.75                | 27.24       | 26.16 | 20.30 |
| 1900               | 1.25                      | 16.69                    | 9.46                | 27.11       | 25.58 | 20.15 |
| 2000               | 1.31                      | 16.49                    | 9.04                | 27.01       | 24.91 | 20.04 |
| 2250               | 1.50                      | 15.96                    | 8.43                | 26.74       | 23.14 | 19.91 |
| 2500               | 1.73                      | 15.45                    | 8.01                | 26.15       | 20.88 | 20.19 |
| 2750               | 2.00                      | 15.02                    | 7.83                | 24.53       | 18.63 | 20.91 |
| 3000               | 2.31                      | 14.79                    | 7.64                | 21.80       | 16.77 | 21.58 |
| 3250               | 2.65                      | 14.69                    | 7.64                | 18.82       | 15.08 | 21.06 |
| 3500               | 2.99                      | 14.78                    | 7.61                | 16.20       | 13.59 | 19.20 |
| 3750               | 3.34                      | 15.04                    | 7.86                | 14.19       | 12.49 | 17.03 |
| 4000               | 3.64                      | 15.40                    | 8.09                | 12.72       | 11.64 | 15.40 |
| 4250               | 3.93                      | 15.72                    | 8.50                | 11.77       | 11.08 | 14.18 |
| 4500               | 4.22                      | 16.02                    | 8.96                | 11.18       | 10.63 | 13.38 |
| 4750               | 4.52                      | 16.32                    | 9.41                | 10.86       | 10.43 | 12.92 |
| 5000               | 4.88                      | 16.44                    | 9.72                | 10.71       | 10.38 | 12.36 |
| 5250               | 5.32                      | 16.46                    | 9.42                | 10.48       | 10.40 | 11.64 |
| 5500               | 5.81                      | 16.49                    | 8.77                | 10.14       | 10.32 | 10.62 |
| 5750               | 6.45                      | 16.46                    | 8.19                | 9.68        | 10.39 | 9.52  |
| 6000               | 7.06                      | 16.21                    | 6.95                | 8.73        | 10.35 | 8.33  |
| 6250               | 7.95                      | 16.11                    | 6.13                | 8.25        | 10.03 | 7.38  |
| 6500               | 8.55                      | 15.90                    | 5.16                | 7.28        | 9.78  | 6.52  |
| 7000               | 10.02                     | 15.61                    | 4.68                | 6.48        | 9.84  | 5.52  |

REV. X1  
TCD-18-4+  
080821  
Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Directional Coupler

# TCD-18-4+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | COUPLING<br>LOSS<br>(dB) | DIRECTIVITY<br>(dB) | RETURN LOSS |             |       |
|--------------------|---------------------------|--------------------------|---------------------|-------------|-------------|-------|
|                    |                           |                          |                     | IN          | (dB)<br>OUT | CPL   |
| 5                  | 0.66                      | 17.60                    | 25.75               | 20.36       | 21.75       | 20.31 |
| 10                 | 0.61                      | 17.53                    | 29.73               | 21.82       | 23.71       | 21.73 |
| 20                 | 0.50                      | 17.38                    | 37.68               | 24.76       | 27.64       | 24.55 |
| 50                 | 0.47                      | 17.35                    | 45.83               | 26.52       | 29.71       | 26.28 |
| 100                | 0.47                      | 17.38                    | 42.35               | 26.35       | 30.88       | 26.15 |
| 150                | 0.48                      | 17.38                    | 41.08               | 26.37       | 31.37       | 26.27 |
| 200                | 0.49                      | 17.39                    | 39.67               | 26.37       | 30.28       | 26.12 |
| 250                | 0.49                      | 17.39                    | 36.12               | 26.05       | 30.03       | 25.55 |
| 300                | 0.50                      | 17.39                    | 34.58               | 26.35       | 29.30       | 25.31 |
| 350                | 0.51                      | 17.39                    | 32.37               | 26.18       | 28.79       | 24.79 |
| 400                | 0.52                      | 17.39                    | 30.64               | 26.21       | 28.49       | 24.61 |
| 450                | 0.54                      | 17.39                    | 29.05               | 26.02       | 28.02       | 24.16 |
| 500                | 0.55                      | 17.39                    | 27.39               | 25.83       | 27.60       | 23.80 |
| 550                | 0.56                      | 17.38                    | 26.13               | 25.82       | 27.18       | 23.47 |
| 600                | 0.57                      | 17.38                    | 24.77               | 25.81       | 26.89       | 23.16 |
| 650                | 0.58                      | 17.37                    | 23.64               | 25.87       | 26.79       | 22.90 |
| 700                | 0.60                      | 17.36                    | 22.53               | 25.75       | 26.59       | 22.70 |
| 750                | 0.61                      | 17.35                    | 21.60               | 25.71       | 26.28       | 22.43 |
| 800                | 0.63                      | 17.34                    | 20.62               | 25.52       | 26.09       | 22.06 |
| 850                | 0.65                      | 17.32                    | 19.74               | 25.48       | 25.97       | 21.81 |
| 900                | 0.67                      | 17.31                    | 18.93               | 25.33       | 25.74       | 21.51 |
| 950                | 0.69                      | 17.29                    | 18.16               | 25.28       | 25.58       | 21.38 |
| 1000               | 0.71                      | 17.26                    | 17.47               | 25.12       | 25.34       | 21.09 |
| 1050               | 0.73                      | 17.24                    | 16.72               | 24.93       | 25.24       | 20.99 |
| 1100               | 0.75                      | 17.21                    | 16.06               | 24.95       | 25.19       | 20.98 |
| 1200               | 0.79                      | 17.13                    | 15.00               | 24.89       | 24.95       | 20.76 |
| 1300               | 0.83                      | 17.04                    | 13.89               | 24.60       | 24.63       | 19.97 |
| 1400               | 0.88                      | 16.93                    | 13.05               | 24.44       | 24.28       | 19.78 |
| 1500               | 0.93                      | 16.81                    | 12.21               | 24.46       | 24.33       | 19.52 |
| 1600               | 0.99                      | 16.66                    | 11.57               | 24.46       | 24.18       | 19.34 |
| 1700               | 1.05                      | 16.56                    | 10.87               | 24.31       | 24.05       | 18.84 |
| 1800               | 1.12                      | 16.35                    | 10.39               | 24.09       | 23.60       | 19.38 |
| 1900               | 1.18                      | 16.16                    | 9.97                | 23.85       | 23.17       | 18.11 |
| 2000               | 1.26                      | 15.97                    | 9.58                | 23.46       | 22.62       | 18.50 |
| 2250               | 1.47                      | 15.48                    | 8.67                | 23.55       | 21.60       | 17.85 |
| 2500               | 1.75                      | 14.98                    | 8.10                | 23.51       | 19.76       | 18.44 |
| 2750               | 2.07                      | 14.66                    | 7.84                | 23.72       | 18.14       | 18.60 |
| 3000               | 2.42                      | 14.37                    | 7.67                | 22.18       | 16.52       | 19.65 |
| 3250               | 2.79                      | 14.41                    | 7.76                | 18.85       | 14.70       | 19.67 |
| 3500               | 3.15                      | 14.59                    | 7.72                | 16.11       | 13.28       | 18.54 |
| 3750               | 3.48                      | 14.94                    | 7.86                | 14.02       | 12.13       | 17.06 |
| 4000               | 3.77                      | 15.40                    | 8.09                | 12.31       | 11.33       | 15.45 |
| 4250               | 4.02                      | 15.86                    | 8.56                | 11.43       | 10.86       | 14.49 |
| 4500               | 4.25                      | 16.17                    | 8.80                | 10.89       | 10.54       | 14.12 |
| 4750               | 4.50                      | 16.41                    | 9.43                | 10.66       | 10.53       | 13.93 |
| 5000               | 4.78                      | 16.51                    | 9.51                | 10.39       | 10.47       | 13.42 |
| 5250               | 5.03                      | 16.50                    | 9.78                | 10.65       | 10.81       | 12.40 |
| 5500               | 5.45                      | 16.32                    | 9.21                | 10.36       | 10.94       | 11.24 |
| 5750               | 5.90                      | 16.18                    | 8.55                | 9.80        | 11.28       | 9.89  |
| 6000               | 6.53                      | 16.00                    | 7.28                | 8.90        | 11.41       | 8.18  |
| 6250               | 7.10                      | 15.62                    | 6.82                | 8.28        | 11.16       | 6.99  |
| 6500               | 7.84                      | 15.44                    | 6.15                | 7.63        | 10.73       | 6.03  |
| 7000               | 9.19                      | 14.65                    | 5.40                | 6.62        | 10.24       | 4.83  |

REV. X1  
TCD-18-4+  
080821  
Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Directional Coupler

# TCD-18-4+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +85°C

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | COUPLING<br>LOSS<br>(dB) | DIRECTIVITY<br>(dB) | RETURN LOSS |       |       |
|--------------------|---------------------------|--------------------------|---------------------|-------------|-------|-------|
|                    |                           |                          |                     | IN          | OUT   | CPL   |
| 5                  | 0.74                      | 17.96                    | 28.44               | 21.33       | 23.50 | 21.44 |
| 10                 | 0.74                      | 17.96                    | 28.77               | 21.52       | 23.88 | 21.62 |
| 20                 | 0.74                      | 17.94                    | 29.43               | 21.90       | 24.64 | 21.97 |
| 50                 | 0.76                      | 17.96                    | 30.40               | 21.85       | 25.15 | 21.86 |
| 100                | 0.77                      | 17.99                    | 30.87               | 22.36       | 25.11 | 22.23 |
| 150                | 0.78                      | 18.00                    | 31.60               | 22.70       | 25.26 | 22.42 |
| 200                | 0.78                      | 18.03                    | 33.02               | 22.81       | 25.81 | 22.45 |
| 250                | 0.78                      | 18.05                    | 33.17               | 23.15       | 26.07 | 22.67 |
| 300                | 0.79                      | 18.08                    | 31.87               | 23.26       | 26.43 | 22.61 |
| 350                | 0.80                      | 18.11                    | 30.46               | 23.49       | 26.66 | 22.65 |
| 400                | 0.81                      | 18.15                    | 28.46               | 23.67       | 26.82 | 22.64 |
| 450                | 0.82                      | 18.19                    | 26.48               | 23.87       | 27.18 | 22.63 |
| 500                | 0.83                      | 18.23                    | 24.66               | 24.15       | 27.43 | 22.66 |
| 550                | 0.85                      | 18.28                    | 23.13               | 24.49       | 27.71 | 22.70 |
| 600                | 0.86                      | 18.32                    | 21.71               | 24.83       | 27.97 | 22.76 |
| 650                | 0.87                      | 18.36                    | 20.46               | 25.10       | 28.32 | 22.73 |
| 700                | 0.88                      | 18.40                    | 19.25               | 25.35       | 28.72 | 22.75 |
| 750                | 0.89                      | 18.43                    | 18.29               | 25.72       | 28.90 | 22.79 |
| 800                | 0.91                      | 18.45                    | 17.38               | 26.03       | 29.25 | 22.77 |
| 850                | 0.92                      | 18.46                    | 16.57               | 26.39       | 29.60 | 22.78 |
| 900                | 0.94                      | 18.47                    | 15.84               | 26.89       | 30.00 | 22.74 |
| 950                | 0.95                      | 18.47                    | 15.22               | 27.31       | 30.20 | 22.73 |
| 1000               | 0.97                      | 18.47                    | 14.60               | 27.67       | 30.48 | 22.81 |
| 1050               | 0.98                      | 18.45                    | 14.06               | 28.18       | 30.83 | 22.81 |
| 1100               | 1.00                      | 18.43                    | 13.59               | 28.41       | 30.75 | 22.67 |
| 1200               | 1.03                      | 18.36                    | 12.70               | 29.00       | 30.74 | 22.52 |
| 1300               | 1.07                      | 18.25                    | 12.01               | 29.84       | 30.61 | 22.59 |
| 1400               | 1.11                      | 18.13                    | 11.45               | 30.15       | 29.90 | 22.37 |
| 1500               | 1.16                      | 17.98                    | 10.94               | 30.11       | 29.23 | 22.17 |
| 1600               | 1.20                      | 17.82                    | 10.53               | 29.82       | 28.30 | 22.00 |
| 1700               | 1.26                      | 17.69                    | 10.21               | 29.76       | 27.71 | 21.70 |
| 1800               | 1.31                      | 17.48                    | 9.74                | 29.67       | 26.72 | 21.65 |
| 1900               | 1.36                      | 17.27                    | 9.52                | 28.86       | 25.54 | 21.55 |
| 2000               | 1.42                      | 17.08                    | 9.18                | 28.47       | 24.77 | 21.22 |
| 2250               | 1.58                      | 16.62                    | 8.59                | 26.21       | 22.26 | 20.99 |
| 2500               | 1.79                      | 16.16                    | 8.18                | 24.74       | 20.18 | 20.83 |
| 2750               | 2.02                      | 15.81                    | 7.85                | 22.38       | 18.33 | 21.03 |
| 3000               | 2.28                      | 15.45                    | 7.59                | 20.45       | 16.90 | 21.10 |
| 3250               | 2.57                      | 15.23                    | 7.37                | 18.24       | 15.44 | 20.41 |
| 3500               | 2.89                      | 15.06                    | 7.09                | 16.25       | 14.13 | 18.94 |
| 3750               | 3.26                      | 15.07                    | 7.02                | 14.30       | 12.90 | 16.97 |
| 4000               | 3.62                      | 15.02                    | 6.95                | 12.82       | 11.97 | 15.54 |
| 4250               | 4.01                      | 15.16                    | 7.22                | 11.57       | 11.04 | 13.75 |
| 4500               | 4.40                      | 15.20                    | 7.21                | 10.81       | 10.28 | 12.64 |
| 4750               | 4.80                      | 15.29                    | 7.65                | 10.23       | 9.68  | 11.88 |
| 5000               | 5.20                      | 15.31                    | 7.79                | 9.93        | 9.15  | 11.41 |
| 5250               | 5.62                      | 15.30                    | 8.16                | 9.85        | 8.67  | 11.18 |
| 5500               | 6.12                      | 15.10                    | 8.23                | 9.94        | 8.48  | 11.03 |
| 5750               | 6.59                      | 14.73                    | 8.30                | 9.97        | 8.17  | 10.48 |
| 6000               | 7.30                      | 14.44                    | 7.23                | 10.05       | 8.15  | 9.91  |
| 6250               | 7.97                      | 14.05                    | 6.69                | 9.61        | 7.90  | 9.26  |
| 6500               | 8.87                      | 13.53                    | 6.39                | 9.16        | 7.76  | 8.22  |
| 7000               | 10.09                     | 12.43                    | 5.50                | 7.36        | 8.78  | 6.00  |

REV. X1  
TCD-18-4+  
080821  
Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661







The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Directional Coupler

## Typical Performance Curves

**TCD-18-4+**




# Directional Coupler


## TCD-18-4+

### Typical Performance Curves


Return Loss




Return Loss In vs. TEMPERATURE



Return Loss Out vs. TEMPERATURE



Return Loss Cpl vs. TEMPERATURE



REV. X1  
TCD-18-4+  
080821  
Page 2 of 2




**Mini-Circuits®**  
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




## Outline Dimensions

DB714



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE # | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| DB714  | .160<br>(4.06) | .150<br>(3.81) | .160<br>(4.06) | .050<br>(1.27) | .040<br>(1.02) | .025<br>(0.64) | .028<br>(0.71) | .065<br>(1.65) | .190<br>(4.83) | .030<br>(0.76) | .15      |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Lead #1 identifier shall be located in the cross-hatched area shown.  
Identifier may be either a molded or marked feature.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F47

## DEVICE ORIENTATION IN T&R



| Tape Width,<br>mm | Device Cavity<br>Pitch, mm | Reel Size,<br>inches | Devices per Reel<br>see note |
|-------------------|----------------------------|----------------------|------------------------------|
| 12                | 8                          | 13                   | 1000, 2000                   |
|                   |                            | 7                    | 20, 50, 100, 200, 500        |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

| REV | ECN No. | DESCRIPTION     | DATE     | DR | AUTH |
|-----|---------|-----------------|----------|----|------|
| OR  | M73159  | NEW RELEASE     | 08/00    | IL | DB   |
| A   | M82377  | UPDATED DRAWING | 07/21/02 | AV | LC   |
| B   | M102713 | UPDATED NOTES   | 01/12/06 | GF | IL   |
|     |         |                 |          |    |      |

.030 X 45° CHAMFER, TYP  
 6X Ø.015 PTH FOR GROUND  
 .064 TYP TRACE WIDTH (SEE NOTE BELOW)  
 .035 TYP  
 .015 .030  
 .015 TYP  
 PACKAGE OUTLINE  
 .052 .035  
 .031  
 .014 .090 2X .040 .050  
 .047 .023 .024 .017  
 PIN 1  
 R1  
 .018 .025


NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030"  $\pm$  0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)


 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

|        |        |
|--------|--------|
| SHEET: | 1 OF 1 |
|--------|--------|

# Evaluation Board and Circuit



TB-71



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C                                                                                                                                   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak                                                                                          | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |