



Mini-Circuits®

SURFACE MOUNT 

Directional Coupler

TCD-18-4X+

50Ω

5 to 1000 MHz

FEATURES

- Wideband, 5 to 1000 MHz
- Low mainline loss, 0.7 dB typ.
- Aqueous washable
- Leads for excellent solderability
- Protected by US Patent 6,140,887

APPLICATIONS

- Communications
- Signal sampling
- Level detection



Generic photo used for illustration purposes only

CASE STYLE: DB1627

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range	—	5	—	1000	MHz
Mainline Loss ¹	5-50	—	0.7	1.3	dB
	50-500	—	0.7	1.3	
	500-1000	—	1.0	1.4	
Coupling	5-1000	—	17.9±0.5	—	dB
Coupling Flatness (±)	5-1000	—	±0.6	—	dB
Directivity	5-50	11	22	—	dB
	50-500	15	20	—	
	500-1000	—	18	—	
VSWR	5-1000	—	1.2	—	:1
Input Power	5-50	—	—	1.0	W
	50-1000	—	—	1.0	

1. Mainline loss includes theoretical power loss at coupled port.


MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to 85°C*
Storage Temperature	-55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

* Case temperature is defined as temperature on ground leads.

ELECTRICAL SCHEMATIC



*Electrical schematic is for Directional coupler with internal transformer(s) and external termination

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
ECO-014204
TCD-18-4X+
WP/CP/AM
220627
PAGE 1 OF 3



Directional Coupler

TCD-18-4X+

5 to 1000 MHz



Mini-Circuits

SURFACE MOUNT 

Directional Coupler




TCD-18-4X+

50Ω

5 to 1000 MHz

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)	Directivity (dB)	Return Loss (dB)		
	In-Out			In	Out	Cpl
5.00	0.71	17.93	22.13	20.96	23.54	21.00
100.00	0.62	17.76	30.64	24.40	28.02	24.20
200.00	0.64	17.80	28.81	24.53	28.17	23.85
300.00	0.67	17.85	26.73	24.53	28.03	23.28
400.00	0.64	17.89	24.88	24.44	27.55	22.54
500.00	0.73	17.92	23.27	24.18	26.78	21.86
600.00	0.80	17.96	21.85	23.87	25.93	21.34
700.00	0.80	18.00	20.56	23.48	25.07	20.77
800.00	0.84	18.03	19.55	23.03	24.24	20.27
1000.00	0.92	18.08	17.79	22.00	22.68	19.42



- NOTES
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Directional Coupler

TCD-18-4X+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	(dB) OUT	CPL
5	0.60	17.72	32.43	22.70	24.99	22.66
10	0.59	17.70	32.68	23.13	25.73	23.09
20	0.58	17.68	33.19	23.97	27.22	23.94
50	0.59	17.69	33.64	24.25	27.82	24.18
100	0.61	17.72	34.27	24.50	28.01	24.34
150	0.62	17.74	35.47	24.67	28.08	24.37
200	0.63	17.75	37.18	24.82	28.21	24.33
250	0.63	17.76	38.20	24.92	28.23	24.26
300	0.64	17.77	37.20	25.06	28.23	24.13
350	0.65	17.78	34.85	25.25	28.15	24.02
400	0.66	17.79	32.14	25.43	28.01	23.88
450	0.67	17.80	29.72	25.53	27.98	23.72
500	0.69	17.80	27.68	25.66	28.03	23.54
550	0.70	17.82	25.81	25.81	27.91	23.37
600	0.71	17.82	24.19	26.01	27.84	23.22
650	0.73	17.84	22.78	26.05	27.79	23.04
700	0.74	17.85	21.43	26.10	27.84	22.85
750	0.76	17.86	20.30	26.17	27.81	22.68
800	0.78	17.87	19.22	26.36	27.76	22.54
850	0.80	17.87	18.28	26.50	27.66	22.40
900	0.81	17.87	17.42	26.49	27.65	22.27
950	0.82	17.86	16.62	26.52	27.68	22.13
1000	0.84	17.85	15.92	26.64	27.57	21.99
1050	0.86	17.84	15.25	26.76	27.52	21.87
1100	0.88	17.82	14.67	26.91	27.59	21.75
1200	0.92	17.77	13.51	26.97	27.55	21.56
1300	0.95	17.67	12.66	27.21	27.51	21.32
1400	0.99	17.55	11.90	27.19	27.30	21.10
1500	1.04	17.42	11.24	27.20	27.10	20.89
1600	1.08	17.25	10.71	27.30	27.01	20.71
1700	1.14	17.10	10.16	27.31	26.67	20.50
1800	1.19	16.91	9.75	27.24	26.16	20.30
1900	1.25	16.69	9.46	27.11	25.58	20.15
2000	1.31	16.49	9.04	27.01	24.91	20.04
2250	1.50	15.96	8.43	26.74	23.14	19.91
2500	1.73	15.45	8.01	26.15	20.88	20.19
2750	2.00	15.02	7.83	24.53	18.63	20.91
3000	2.31	14.79	7.64	21.80	16.77	21.58
3250	2.65	14.69	7.64	18.82	15.08	21.06
3500	2.99	14.78	7.61	16.20	13.59	19.20
3750	3.34	15.04	7.86	14.19	12.49	17.03
4000	3.64	15.40	8.09	12.72	11.64	15.40
4250	3.93	15.72	8.50	11.77	11.08	14.18
4500	4.22	16.02	8.96	11.18	10.63	13.38
4750	4.52	16.32	9.41	10.86	10.43	12.92
5000	4.88	16.44	9.72	10.71	10.38	12.36
5250	5.32	16.46	9.42	10.48	10.40	11.64
5500	5.81	16.49	8.77	10.14	10.32	10.62
5750	6.45	16.46	8.19	9.68	10.39	9.52
6000	7.06	16.21	6.95	8.73	10.35	8.33
6250	7.95	16.11	6.13	8.25	10.03	7.38
6500	8.55	15.90	5.16	7.28	9.78	6.52
7000	10.02	15.61	4.68	6.48	9.84	5.52

REV. X1
TCD-18-4X+
111003
Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Directional Coupler

TCD-18-4X+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	(dB) OUT	CPL
5	0.66	17.60	25.75	20.36	21.75	20.31
10	0.61	17.53	29.73	21.82	23.71	21.73
20	0.50	17.38	37.68	24.76	27.64	24.55
50	0.47	17.35	45.83	26.52	29.71	26.28
100	0.47	17.38	42.35	26.35	30.88	26.15
150	0.48	17.38	41.08	26.37	31.37	26.27
200	0.49	17.39	39.67	26.37	30.28	26.12
250	0.49	17.39	36.12	26.05	30.03	25.55
300	0.50	17.39	34.58	26.35	29.30	25.31
350	0.51	17.39	32.37	26.18	28.79	24.79
400	0.52	17.39	30.64	26.21	28.49	24.61
450	0.54	17.39	29.05	26.02	28.02	24.16
500	0.55	17.39	27.39	25.83	27.60	23.80
550	0.56	17.38	26.13	25.82	27.18	23.47
600	0.57	17.38	24.77	25.81	26.89	23.16
650	0.58	17.37	23.64	25.87	26.79	22.90
700	0.60	17.36	22.53	25.75	26.59	22.70
750	0.61	17.35	21.60	25.71	26.28	22.43
800	0.63	17.34	20.62	25.52	26.09	22.06
850	0.65	17.32	19.74	25.48	25.97	21.81
900	0.67	17.31	18.93	25.33	25.74	21.51
950	0.69	17.29	18.16	25.28	25.58	21.38
1000	0.71	17.26	17.47	25.12	25.34	21.09
1050	0.73	17.24	16.72	24.93	25.24	20.99
1100	0.75	17.21	16.06	24.95	25.19	20.98
1200	0.79	17.13	15.00	24.89	24.95	20.76
1300	0.83	17.04	13.89	24.60	24.63	19.97
1400	0.88	16.93	13.05	24.44	24.28	19.78
1500	0.93	16.81	12.21	24.46	24.33	19.52
1600	0.99	16.66	11.57	24.46	24.18	19.34
1700	1.05	16.56	10.87	24.31	24.05	18.84
1800	1.12	16.35	10.39	24.09	23.60	19.38
1900	1.18	16.16	9.97	23.85	23.17	18.11
2000	1.26	15.97	9.58	23.46	22.62	18.50
2250	1.47	15.48	8.67	23.55	21.60	17.85
2500	1.75	14.98	8.10	23.51	19.76	18.44
2750	2.07	14.66	7.84	23.72	18.14	18.60
3000	2.42	14.37	7.67	22.18	16.52	19.65
3250	2.79	14.41	7.76	18.85	14.70	19.67
3500	3.15	14.59	7.72	16.11	13.28	18.54
3750	3.48	14.94	7.86	14.02	12.13	17.06
4000	3.77	15.40	8.09	12.31	11.33	15.45
4250	4.02	15.86	8.56	11.43	10.86	14.49
4500	4.25	16.17	8.80	10.89	10.54	14.12
4750	4.50	16.41	9.43	10.66	10.53	13.93
5000	4.78	16.51	9.51	10.39	10.47	13.42
5250	5.03	16.50	9.78	10.65	10.81	12.40
5500	5.45	16.32	9.21	10.36	10.94	11.24
5750	5.90	16.18	8.55	9.80	11.28	9.89
6000	6.53	16.00	7.28	8.90	11.41	8.18
6250	7.10	15.62	6.82	8.28	11.16	6.99
6500	7.84	15.44	6.15	7.63	10.73	6.03
7000	9.19	14.65	5.40	6.62	10.24	4.83

REV. X1
TCD-18-4X+
111003
Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Directional Coupler

TCD-18-4X+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +85°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	(dB) OUT	CPL
5	0.74	17.96	28.44	21.33	23.50	21.44
10	0.74	17.96	28.77	21.52	23.88	21.62
20	0.74	17.94	29.43	21.90	24.64	21.97
50	0.76	17.96	30.40	21.85	25.15	21.86
100	0.77	17.99	30.87	22.36	25.11	22.23
150	0.78	18.00	31.60	22.70	25.26	22.42
200	0.78	18.03	33.02	22.81	25.81	22.45
250	0.78	18.05	33.17	23.15	26.07	22.67
300	0.79	18.08	31.87	23.26	26.43	22.61
350	0.80	18.11	30.46	23.49	26.66	22.65
400	0.81	18.15	28.46	23.67	26.82	22.64
450	0.82	18.19	26.48	23.87	27.18	22.63
500	0.83	18.23	24.66	24.15	27.43	22.66
550	0.85	18.28	23.13	24.49	27.71	22.70
600	0.86	18.32	21.71	24.83	27.97	22.76
650	0.87	18.36	20.46	25.10	28.32	22.73
700	0.88	18.40	19.25	25.35	28.72	22.75
750	0.89	18.43	18.29	25.72	28.90	22.79
800	0.91	18.45	17.38	26.03	29.25	22.77
850	0.92	18.46	16.57	26.39	29.60	22.78
900	0.94	18.47	15.84	26.89	30.00	22.74
950	0.95	18.47	15.22	27.31	30.20	22.73
1000	0.97	18.47	14.60	27.67	30.48	22.81
1050	0.98	18.45	14.06	28.18	30.83	22.81
1100	1.00	18.43	13.59	28.41	30.75	22.67
1200	1.03	18.36	12.70	29.00	30.74	22.52
1300	1.07	18.25	12.01	29.84	30.61	22.59
1400	1.11	18.13	11.45	30.15	29.90	22.37
1500	1.16	17.98	10.94	30.11	29.23	22.17
1600	1.20	17.82	10.53	29.82	28.30	22.00
1700	1.26	17.69	10.21	29.76	27.71	21.70
1800	1.31	17.48	9.74	29.67	26.72	21.65
1900	1.36	17.27	9.52	28.86	25.54	21.55
2000	1.42	17.08	9.18	28.47	24.77	21.22
2250	1.58	16.62	8.59	26.21	22.26	20.99
2500	1.79	16.16	8.18	24.74	20.18	20.83
2750	2.02	15.81	7.85	22.38	18.33	21.03
3000	2.28	15.45	7.59	20.45	16.90	21.10
3250	2.57	15.23	7.37	18.24	15.44	20.41
3500	2.89	15.06	7.09	16.25	14.13	18.94
3750	3.26	15.07	7.02	14.30	12.90	16.97
4000	3.62	15.02	6.95	12.82	11.97	15.54
4250	4.01	15.16	7.22	11.57	11.04	13.75
4500	4.40	15.20	7.21	10.81	10.28	12.64
4750	4.80	15.29	7.65	10.23	9.68	11.88
5000	5.20	15.31	7.79	9.93	9.15	11.41
5250	5.62	15.30	8.16	9.85	8.67	11.18
5500	6.12	15.10	8.23	9.94	8.48	11.03
5750	6.59	14.73	8.30	9.97	8.17	10.48
6000	7.30	14.44	7.23	10.05	8.15	9.91
6250	7.97	14.05	6.69	9.61	7.90	9.26
6500	8.87	13.53	6.39	9.16	7.76	8.22
7000	10.09	12.43	5.50	7.36	8.78	6.00

REV. X1
TCD-18-4X+
111003
Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Directional Coupler


Typical Performance Curves

TCD-18-4X+


Insertion Loss




Insertion Loss vs. TEMPERATURE



Coupling Loss vs. TEMPERATURE



Directivity vs. TEMPERATURE



REV. X1
TCD-18-4X+
111003
Page 1 of 2

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Directional Coupler


TCD-18-4X+

Typical Performance Curves


Return Loss




Return Loss In vs. TEMPERATURE



Return Loss Out vs. TEMPERATURE



Return Loss Cpl vs. TEMPERATURE



REV. X1
TCD-18-4X+
111003
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Outline Dimensions

DB1627



PCB Land Pattern



CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
DB1627	.160 (4.06)	.150 (3.81)	.160 (4.06)	.050 (1.27)	.040 (1.02)	.025 (0.64)	.028 (0.71)	.065 (1.65)	.190 (4.83)	.030 (0.76)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- Top-Hat total thickness: .013 inches MAX.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
12	8	13	1000, 2000
		7	20, 50, 100, 200, 500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Evaluation Board and Circuit



TB-71



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215