

# RF Transformer

50Ω 600 to 1200 MHz

## Maximum Ratings


|                       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| Input RF Power        | 3W             |

## Pad Connections

|                               |     |
|-------------------------------|-----|
| PRIMARY DOT (Unbalanced Port) | 5   |
| PRIMARY (GND)                 | 4,6 |
| SECONDARY DOT (Balanced)      | 3   |
| SECONDARY (Balanced)          | 1   |
| NO CONNECTION                 | 2   |

Pads 1,3,4,6 are DC-connected internally


## Outline Drawing



## Outline Dimensions (Inch/mm)

| A    | B    | C    | D    | E    | F     |
|------|------|------|------|------|-------|
| .126 | .063 | .035 | .024 | .022 | .011  |
| 3.20 | 1.60 | 0.89 | 0.61 | 0.56 | 0.28  |
| G    | H    | J    | K    | L    | wt    |
| .039 | .024 | .042 | .123 |      | grams |
| 0.99 | 0.61 | 1.07 | 3.12 |      | .020  |

## Demo Board MCL P/N: TB-417+ Suggested PCB Layout (PL-265)



### NOTES:

- COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK


### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

# TCN2-122+



Generic photo used for illustration purposes only

CASE STYLE: FV1206-1

## +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

| Reel Size | Devices/Reel                      |
|-----------|-----------------------------------|
| 7"        | 20, 50, 100, 200, 500, 1000, 3000 |

## Features

- wideband, 600 to 1200 MHz
- low phase unbalance, 4 deg. typ. and amplitude unbalance, 0.3 dB typ.
- miniature size, 0.12"x.06"x.037"
- LTCC construction
- low cost
- aqueous washable

## Applications

- GSM
- WCDMA
- ISM

## Electrical Specifications (T<sub>AMB</sub>=25°C)

| Ω RATIO<br>(Secondary/Primary) | FREQUENCY<br>(MHz) | INSERTION*<br>LOSS<br>(dB) | PHASE<br>UNBALANCE†<br>(Deg.)<br>Typ. | AMPLITUDE<br>UNBALANCE<br>(dB)<br>Typ. |
|--------------------------------|--------------------|----------------------------|---------------------------------------|----------------------------------------|
| 2                              | 600-1200           | 1.0                        | 4                                     | 0.3                                    |




\* Insertion Loss is referenced to mid-band loss, 0.7 dB. Reference Demo Board TB-417+

† Relative to 180°


## Typical Performance Data at 25°C\*\*

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | INPUT<br>R. LOSS<br>(dB) | AMPLITUDE<br>UNBALANCE<br>(dB) | PHASE<br>UNBALANCE<br>(Deg.) |
|--------------------|---------------------------|--------------------------|--------------------------------|------------------------------|
| 600.00             | 0.36                      | 11.90                    | 0.15                           | 7.52                         |
| 700.00             | 0.08                      | 17.72                    | 0.38                           | 6.76                         |
| 800.00             | 0.00                      | 27.57                    | 0.54                           | 5.17                         |
| 900.00             | 0.02                      | 27.76                    | 0.62                           | 3.01                         |
| 1000.00            | 0.07                      | 21.96                    | 0.62                           | 0.30                         |
| 1060.00            | 0.10                      | 20.45                    | 0.57                           | 1.40                         |
| 1100.00            | 0.13                      | 19.81                    | 0.52                           | 2.79                         |
| 1140.00            | 0.15                      | 19.40                    | 0.46                           | 4.01                         |
| 1160.00            | 0.16                      | 19.32                    | 0.42                           | 4.66                         |
| 1200.00            | 0.17                      | 19.29                    | 0.33                           | 6.10                         |

\*\* Measured with Agilent E5071B network analyzer using impedance conversion and port extension.



## configuration J



\*Internal open circuit


*Typical Performance Data*

| FREQUENCY<br>(MHz) | AVERAGE<br>INSERTION<br>LOSS* | INPUT<br>RETURN<br>LOSS | AMPLITUDE<br>UNBALANCE | PHASE<br>UNBALANCE** |
|--------------------|-------------------------------|-------------------------|------------------------|----------------------|
| (dB)               | (dB)                          | (dB)                    | (dB)                   | (deg)                |
| 600                | 0.36                          | 11.90                   | 0.15                   | 7.52                 |
| 625                | 0.26                          | 13.13                   | 0.20                   | 7.40                 |
| 650                | 0.19                          | 14.49                   | 0.26                   | 7.21                 |
| 675                | 0.12                          | 16.02                   | 0.32                   | 6.97                 |
| 700                | 0.08                          | 17.72                   | 0.38                   | 6.76                 |
| 720                | 0.06                          | 19.22                   | 0.41                   | 6.52                 |
| 740                | 0.03                          | 20.90                   | 0.44                   | 6.22                 |
| 760                | 0.02                          | 22.76                   | 0.47                   | 5.89                 |
| 780                | 0.01                          | 24.99                   | 0.51                   | 5.51                 |
| 800                | 0.00                          | 27.57                   | 0.54                   | 5.17                 |
| 820                | 0.00                          | 30.29                   | 0.57                   | 4.77                 |
| 840                | 0.00                          | 32.28                   | 0.58                   | 4.44                 |
| 860                | 0.01                          | 31.95                   | 0.60                   | 3.99                 |
| 880                | 0.01                          | 29.87                   | 0.61                   | 3.47                 |
| 900                | 0.02                          | 27.76                   | 0.62                   | 3.01                 |
| 920                | 0.03                          | 26.10                   | 0.63                   | 2.52                 |
| 940                | 0.04                          | 24.79                   | 0.64                   | 2.06                 |
| 960                | 0.05                          | 23.71                   | 0.63                   | 1.50                 |
| 980                | 0.06                          | 22.73                   | 0.63                   | 0.88                 |
| 1000               | 0.07                          | 21.96                   | 0.62                   | 0.30                 |
| 1020               | 0.08                          | 21.35                   | 0.61                   | 0.28                 |
| 1040               | 0.09                          | 20.84                   | 0.60                   | 0.83                 |
| 1060               | 0.10                          | 20.45                   | 0.57                   | 1.40                 |
| 1080               | 0.12                          | 20.09                   | 0.55                   | 2.13                 |
| 1100               | 0.13                          | 19.81                   | 0.52                   | 2.79                 |
| 1120               | 0.14                          | 19.57                   | 0.49                   | 3.45                 |
| 1140               | 0.15                          | 19.40                   | 0.46                   | 4.01                 |
| 1160               | 0.16                          | 19.32                   | 0.42                   | 4.66                 |
| 1180               | 0.17                          | 19.29                   | 0.38                   | 5.38                 |
| 1200               | 0.17                          | 19.29                   | 0.33                   | 6.10                 |




\* Insertion Loss is referenced to mid-band loss , 0.7 dB.

\*\*Phase Unbalance is relative to 180°

## Typical Performance Curves




\* Insertion Loss is referenced to mid-band loss , 0.7 dB.




\*\*Phase Unbalance is relative to 180°

### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE #   | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L  | M  | N  | P  | WT. GRAM |
|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----|----|----|----|----------|
| FV1206-1 | .126<br>(3.20) | .063<br>(1.60) | .035<br>(0.89) | .024<br>(0.61) | .022<br>(0.56) | .011<br>(0.28) | .039<br>(0.99) | .024<br>(0.61) | .042<br>(1.07) | .123<br>(3.12) | -- | -- | -- | -- | .020     |

Dimensions are in inches (mm). Tolerances: 2 PL.  $\pm .01$ ; 3 PL.  $\pm .005$

#### Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**  
 For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
 For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging

# TR-F75

## DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

| Applicable Case Styles |
|------------------------|
| FV1206-1               |
| FV1206-3               |

| Applicable Case Styles |
|------------------------|
| FV1206-4               |
| FV1206-5               |
| FV1206-6               |
| FV1206-7               |
| FV1206-9               |
| JC0603C-1              |

| Applicable Case Styles |
|------------------------|
| NL1008C-6              |
| FV1206-12              |
| NL1008C-9              |
| NL1008C-10             |

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         |                   | Standard                            | 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)

Mini-Circuits ISO 9001 & ISO 14001 Certified

**Mini-Circuits®**

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

|     |         |             |          |    |      |
|-----|---------|-------------|----------|----|------|
| REV | ECN No. | DESCRIPTION | DATE     | DR | AUTH |
| OR  | M109527 | NEW RELEASE | 01/31/07 | PW | DJ   |
|     |         |             |          |    |      |
|     |         |             |          |    |      |

Top view of the package outline. Dimensions include: .084 (left side), .104 (top center), .012 4 PL. (left side), .104 (left side), .009, 2 PL. (right side), .005, 2 PL. (right side), .072 (bottom center), .143 (bottom center). Features include: PACKAGE OUTLINE, PIN 1, COPLANAR WAVEGUIDE, .038 TRACE WIDTH, .013 GAP, 3 PL. (SEE NOTE 1), and 45° 4 PL. (top right).

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020"  $\pm$  .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE \_\_\_\_\_

**DIMENSIONS ARE IN INCHES**

DRAWN

PW

01/29/07

**TOLERANCES ON:**

01000100

---

II

01 / 31 / 07

2 PL DECIMALS  $\pm$  0.05

**CHECKED**

**APPROVED**

---

01 / 01 / 01

ANGLES  $\pm 1^\circ$

|          |
|----------|
| APPROVED |
|          |

**DJ**

01/31/07

FRACTIONS  $\pm$ 

\_\_\_\_\_

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.



**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

13 Neptune Avenue  
Brooklyn NY 11235

PL, sa, FV1206-1, TCN, TB-417+

**SIZE**  
**A**

CODE IDENT  
15542

DRAWING NO:  
98-PL-265

|      |    |
|------|----|
| REV: | OR |
|------|----|


FILE: 98PL265

SCALE: 10:1


|        |        |
|--------|--------|
| SHEET: | 1 OF 1 |
|--------|--------|

ASHEETA1.DWG REV:A DATE:01/12/95

# Evaluation Board and Circuit



TB-417+



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.010 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                           | Reference/Spec                                                                                       |
|----------------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature      | -40° to 85° C<br>Ambient Environment                                                | Individual Model Data Sheet                                                                          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                               | Individual Model Data Sheet                                                                          |
| Humidity                   | 90 to 95% RH, 240 hours, 50°C                                                       | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock              | -55° to 100°C, 100 cycles                                                           | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat         | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak              | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability              | 10X Magnification                                                                   | J-STD-002, Para 4.2.5, Test S, 95% Coverage                                                          |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                   | MIL-STD-202, Method 213, Condition A                                                                 |