MMIC REFLECTIONLESS


Low Pass Filter

XLF-732+

50Ω DC to 7300 MHz

THE BIG DEAL

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent Power handling
- Temperature stable, up to +105°C
- Small size, 3 x 3 mm
- Protected by US Patent No. 8,392,495



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant
The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Harmonics Rejection
- Wideband Matching
- Transmitters / Receivers

PRODUCT OVERVIEW

Mini-Circuits' XLF-732+ reflectionless filter employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level. These reflections interact with neighboring components and often result in inter-modulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

KEY FEATURES

Features	Advantages
Reflectionless Technology	Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range and saving board space.
50Ω Match in Stopband	Reflectionless filters maintain good impedance matching in the stopband, allowing for integration with high gain, wideband amplifiers without the risk of creating out-of-band instabilities.
Excellent RF Performance Repeatability	Fabricated on a GaAs process, X-series filters are inherently repeatable for large-volume production.
Excellent Stability over temperature	With ±0.3 dB variation over temperature, is ideal for use in wide temperature range applications without the need for additional temperature compensation.
Excellent Power Handling in a Compact Package	High power handling extends the usability of these filters to the transmit path for inter-stage filtering.

REV. B
ECO-020994
XLF-732+
MCL NY
240226

Low Pass Filter

XLF-732+

50Ω DC to 7300 MHz

ELECTRICAL SPECIFICATIONS[1] AT +25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC - F1	DC - 7300	—	1.1	1.5	dB
	Frequency Cut-off	F2	9800	—	3.0	—	dB
	VSWR	DC - F1	DC - 7300	—	1.2	—	:1
Stop Band	Rejection	F3 - F5	14300 - 34000	13	16	—	dB
	VSWR	F3 - F4	14300 - 25000	—	2.5	—	:1
		F4 - F5	25000 - 34000	—	3.0	—	:1


1. Measured on Mini-Circuits Characterization Test Board TB-844-732+

ABSOLUTE MAXIMUM RATINGS[4]

Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-65°C to +150°C
RF Power Input, Passband (DC-F1)[2]	2 W at 25°C
RF Power Input, Stopband (F2-F5)[3]	0.2 W at 25°C

2. Passband rating derates linearly to 1 W at 105°C ambient
3. Stopband rating derates linearly to 0.1 W at 105°C ambient
4. Permanent damage may occur if any of these limits are exceeded.

SPECIFICATION DEFINITION





Low Pass Filter

XLF-732+

50Ω DC to 7300 MHz


SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION





Function	Pad Number	Description
RF-IN	2	RF Input Pad
RF-OUT	8	RF Output Pad
GND	1,3,7,9, Paddle	Connected to ground
NC (GND Externally)	4,5,6,10,11,12	No internal connection

PRODUCT MARKING



Marking may contain other features or characters for internal lot control


Low Pass Filter


XLF-732+

50Ω DC to 7300 MHz

TYPICAL PERFORMANCE DATA AT +25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.40	1.03
100	0.38	1.02
200	0.39	1.04
400	0.40	1.09
800	0.44	1.17
1600	0.52	1.28
3200	0.57	1.21
5000	0.69	1.19
7300	1.09	1.10
9800	2.97	1.51
12000	7.38	1.51
14300	15.66	1.50
17000	26.40	1.94
19500	22.31	3.14
22000	20.23	3.22
25000	18.17	2.38
27000	17.64	1.82
29500	17.81	2.15
32000	20.13	4.24
34000	21.50	6.90





Low Pass Filter

XLF-732+

50Ω DC to 7300 MHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS CLICK HERE

Performance Data and Graphs	Data Graphs S-Parameter (S3P Files) Data Set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle lead finish: matte-tin
Tape & Reel **Standard quantities available on reel**	F66 7" reels with 20, 50, 100, 200, 500 ,1000, 2000, 3000 devices
Suggested Layout for PCB Design	PL-451
Evaluation Board	TB-844-732+ (without connectors) TB-844-732C+ (with connectors) B20-118-F1+ Connector sold separately
Environmental Ratings	ENV82

ESD RATING

Human body model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD 5.1-2001

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D


Low Pass Filter

XLF-732+

50Ω DC to 7300 MHz

REFLECTIONLESS FILTER APPLICATION NOTE

Application Circuit Example: Pairing mixers with reflectionless filters to improve system dynamic range



Test block diagram: IF output reflection spectrum with single input frequency




Figure 1. IF output reflection spectrum without filter





Figure 2. IF output reflection spectrum with conventional filter



An application circuit was assembled to measure the IF reflection spectrum at the output of a mixer when the mixer was paired with a conventional filter versus a reflectionless filter.

While the conventional filter reduces the reflections present when the mixer is used alone (no filter), the reflectionless filter virtually eliminates those reflections altogether.

The reflected signal at marker 1 in the figures above exhibits a reduction of more than 20 dB from -28.7 dBm to -50.3 dBm when the reflectionless filter is used as compared to the conventional filter, thus eliminating unwanted spurious mixing products and improvingsystem dynamic range.

For more information, refer to application note AN-75-007.

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data


FREQ.	INSERTION LOSS					GROUP DELAY				
(MHz)	(dB)					(nsec)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
10	0.38	0.36	0.40	0.43	0.45	0.12	0.13	0.13	0.13	0.15
50	0.34	0.35	0.38	0.40	0.43	0.08	0.09	0.09	0.09	0.10
100	0.34	0.35	0.39	0.41	0.43	0.05	0.06	0.05	0.06	0.06
200	0.34	0.36	0.40	0.43	0.44	0.05	0.05	0.05	0.05	0.05
300	0.35	0.36	0.40	0.44	0.46	0.05	0.05	0.05	0.05	0.05
400	0.34	0.36	0.41	0.45	0.46	0.05	0.05	0.05	0.05	0.05
500	0.35	0.37	0.42	0.46	0.48	0.05	0.05	0.04	0.05	0.05
600	0.35	0.37	0.43	0.48	0.50	0.05	0.05	0.05	0.05	0.05
700	0.35	0.37	0.44	0.49	0.51	0.05	0.05	0.04	0.05	0.05
800	0.36	0.37	0.44	0.49	0.51	0.05	0.05	0.05	0.05	0.05
900	0.37	0.38	0.45	0.50	0.53	0.05	0.05	0.04	0.05	0.05
1000	0.37	0.39	0.46	0.52	0.53	0.05	0.05	0.05	0.05	0.05
1200	0.39	0.41	0.48	0.55	0.56	0.05	0.05	0.04	0.05	0.05
1400	0.40	0.43	0.51	0.57	0.59	0.05	0.05	0.05	0.05	0.05
1600	0.43	0.45	0.52	0.59	0.61	0.05	0.05	0.04	0.05	0.05
1800	0.44	0.46	0.54	0.60	0.62	0.04	0.05	0.04	0.05	0.05
2000	0.44	0.47	0.55	0.61	0.63	0.05	0.05	0.04	0.05	0.05
2500	0.45	0.48	0.57	0.64	0.66	0.05	0.05	0.04	0.05	0.05
3000	0.45	0.48	0.58	0.65	0.68	0.05	0.05	0.04	0.05	0.05
3500	0.46	0.49	0.60	0.68	0.71	0.05	0.05	0.05	0.05	0.05
4000	0.48	0.52	0.63	0.73	0.76	0.05	0.05	0.05	0.05	0.05
4500	0.51	0.55	0.68	0.78	0.82	0.05	0.05	0.05	0.05	0.05
5000	0.56	0.59	0.73	0.84	0.88	0.05	0.05	0.05	0.05	0.05
5500	0.59	0.63	0.78	0.89	0.94	0.05	0.05	0.05	0.05	0.05
6000	0.64	0.68	0.85	0.97	1.02	0.05	0.05	0.05	0.05	0.05
6500	0.69	0.74	0.92	1.05	1.10	0.06	0.05	0.05	0.06	0.06
7000	0.78	0.84	1.02	1.18	1.23	0.06	0.06	0.05	0.06	0.06
7300	0.85	0.90	1.11	1.27	1.32	0.06	0.06	0.05	0.06	0.06
7500	0.91	0.96	1.17	1.33	1.40	0.06	0.06	0.06	0.06	0.06
7800	1.01	1.07	1.29	1.47	1.53	0.06	0.06	0.06	0.06	0.06
8000	1.08	1.15	1.38	1.56	1.63	0.06	0.06	0.06	0.06	0.06
8200	1.18	1.24	1.48	1.68	1.75	0.06	0.06	0.06	0.06	0.06
8400	1.29	1.35	1.60	1.80	1.88	0.06	0.06	0.06	0.06	0.06
8600	1.42	1.49	1.74	1.95	2.03	0.06	0.06	0.06	0.06	0.06
8800	1.56	1.64	1.89	2.11	2.19	0.06	0.07	0.06	0.06	0.07
9000	1.73	1.80	2.07	2.29	2.37	0.06	0.07	0.06	0.06	0.07
9200	1.91	1.98	2.27	2.49	2.58	0.06	0.06	0.06	0.06	0.07
9400	2.10	2.18	2.48	2.72	2.79	0.07	0.07	0.06	0.07	0.07
9600	2.31	2.39	2.71	2.95	3.03	0.07	0.07	0.06	0.06	0.07
9800	2.54	2.63	2.96	3.22	3.30	0.07	0.07	0.07	0.07	0.07
10000	2.79	2.89	3.24	3.50	3.59	0.07	0.07	0.06	0.07	0.07
10200	3.07	3.17	3.52	3.81	3.89	0.07	0.07	0.06	0.07	0.07
10400	3.37	3.47	3.84	4.13	4.23	0.07	0.07	0.06	0.07	0.07
10600	3.70	3.79	4.17	4.48	4.58	0.07	0.07	0.06	0.07	0.07
10800	4.04	4.14	4.54	4.86	4.96	0.07	0.07	0.06	0.07	0.07
11000	4.42	4.53	4.92	5.26	5.37	0.07	0.07	0.06	0.06	0.07
12000	6.78	6.91	7.34	7.73	7.86	0.06	0.06	0.06	0.06	0.06
13000	9.92	10.03	10.46	10.88	11.02	0.05	0.05	0.05	0.05	0.05
14000	13.67	13.80	14.31	14.74	14.87	0.04	0.04	0.04	0.04	0.04
14300	14.97	15.12	15.64	16.07	16.23	0.03	0.04	0.03	0.03	0.03
15000	18.46	18.60	19.18	19.62	19.76	0.02	0.01	0.01	0.00	0.00
16000	24.49	24.60	24.85	25.02	25.03	-0.06	-0.07	-0.08	-0.08	-0.08
17000	26.89	26.87	26.40	26.02	25.89	-0.10	-0.10	-0.08	-0.07	-0.06
18000	24.17	24.15	24.04	23.87	23.82	0.01	-0.01	-0.01	0.00	0.00
19000	22.45	22.51	22.53	22.50	22.55	0.02	0.02	0.01	0.02	0.01
20000	21.57	21.66	21.63	21.74	21.79	0.01	0.02	0.02	0.01	0.02
21000	20.89	20.97	21.17	21.22	21.24	0.03	0.02	0.00	0.01	0.01
22000	19.90	19.99	20.10	20.14	20.12	0.03	0.02	0.02	0.03	0.02
23000	19.04	19.10	19.25	19.31	19.28	0.04	0.03	0.03	0.03	0.03
24000	18.35	18.39	18.53	18.65	18.67	0.03	0.03	0.03	0.03	0.04
25000	17.70	17.77	18.04	18.19	18.25	0.04	0.04	0.03	0.03	0.04
26000	17.09	17.21	17.59	17.86	17.96	0.04	0.05	0.04	0.04	0.04
27000	16.74	16.81	17.32	17.70	17.81	0.06	0.05	0.05	0.03	0.05
28000	16.63	16.76	17.23	17.59	17.72	0.04	0.04	0.05	0.04	0.05
29000	16.85	17.03	17.42	17.82	17.97	0.05	0.05	0.05	0.05	0.05
30000	17.29	17.46	18.02	18.34	18.39	0.05	0.04	0.04	0.04	0.04
31000	18.07	18.25	18.85	19.05	19.11	0.04	0.04	0.02	0.04	0.03
32000	19.14	19.32	19.60	19.92	20.02	0.03	0.03	0.03	0.04	0.04
33000	20.21	20.26	20.41	20.99	21.12	0.03	0.03	0.02	0.03	0.03
34000	21.16	21.26	21.30	21.62	21.89	-0.02	-0.01	0.00	0.01	0.00
35000	20.82	20.93	21.10	21.52	21.69	0.03	0.04	0.04	0.01	0.02
36000	20.85	20.81	20.94	21.13	21.00	0.00	0.01	0.03	0.00	0.03
37000	19.12	19.10	19.17	19.28	19.22	0.02	0.03	0.00	0.02	0.02
38000	17.01	17.03	16.89	16.73	16.69	0.02	0.03	0.02	0.04	0.05
39000	13.16	13.18	13.37	13.29	13.25	0.08	0.08	0.09	0.09	0.10
40000	10.44	10.55	11.03	11.43	11.63	0.10	0.15	0.10	0.10	0.12

Typical Performance Data


FREQ.	INPUT RETURN LOSS					OUTPUT RETURN LOSS				
(MHz)	(dB)					(dB)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
10	32.04	32.18	34.66	34.28	34.44	37.29	38.03	39.87	40.40	43.91
50	36.77	37.38	39.50	43.25	44.30	36.43	36.67	39.70	42.32	43.60
100	34.97	35.32	37.93	39.48	40.50	35.79	36.45	39.47	41.71	42.09
200	34.56	34.46	34.57	34.90	34.88	34.54	34.58	34.15	34.70	34.57
300	31.46	31.55	30.73	30.64	30.78	31.89	31.91	31.04	31.13	31.14
400	28.97	28.95	28.42	28.63	28.74	28.58	28.62	28.14	28.35	28.27
500	27.43	27.25	26.31	26.55	26.57	27.41	27.19	26.42	26.55	26.59
600	26.11	25.91	24.77	24.82	24.88	26.10	25.90	24.78	24.80	24.87
700	24.88	24.65	23.71	23.64	23.68	24.65	24.44	23.54	23.43	23.47
800	23.49	23.30	22.55	22.51	22.51	23.45	23.29	22.57	22.49	22.52
900	22.53	22.46	21.91	21.81	21.84	22.44	22.37	21.86	21.78	21.78
1000	21.53	21.45	21.12	20.94	20.95	21.47	21.39	21.09	20.92	20.92
1200	20.30	20.28	20.04	19.87	19.83	20.21	20.21	19.93	19.79	19.75
1400	19.60	19.58	19.25	19.06	19.04	19.59	19.56	19.28	19.09	19.08
1600	18.70	18.73	18.81	18.64	18.62	18.75	18.76	18.83	18.66	18.62
1800	18.23	18.29	18.55	18.42	18.37	18.21	18.26	18.55	18.42	18.41
2000	18.28	18.32	18.49	18.46	18.45	18.24	18.28	18.47	18.50	18.47
2500	18.76	18.80	19.09	19.22	19.26	18.75	18.79	19.06	19.27	19.30
3000	20.34	20.29	20.01	20.12	20.16	20.34	20.30	19.97	20.14	20.19
3500	20.76	20.76	20.96	20.85	20.87	20.81	20.86	20.96	20.85	20.82
4000	20.90	20.89	20.96	20.63	20.65	21.00	20.96	21.02	20.67	20.69
4500	20.21	20.17	20.23	19.51	19.44	20.24	20.21	20.26	19.57	19.50
5000	19.21	19.25	19.65	19.14	19.09	19.41	19.44	19.83	19.28	19.20
5500	19.19	19.26	19.73	19.81	19.75	19.33	19.43	19.82	19.89	19.87
6000	19.76	19.86	20.25	20.73	20.84	19.79	19.90	20.28	20.80	20.95
6500	21.08	21.16	21.47	22.13	22.34	21.09	21.20	21.53	22.19	22.42
7000	22.35	22.49	23.21	23.71	23.45	22.35	22.49	23.18	23.78	23.65
7300	23.40	23.48	23.77	24.05	23.68	23.31	23.37	23.77	24.13	23.91
7500	23.79	23.83	23.64	23.56	23.18	23.83	23.95	23.98	23.89	23.57
7800	22.96	22.96	22.80	22.20	21.70	23.13	23.20	23.14	22.44	21.98
8000	22.30	22.31	21.89	21.13	20.67	22.47	22.50	22.37	21.51	21.02
8200	20.86	20.88	20.71	19.91	19.47	21.10	21.17	21.34	20.46	20.04
8400	19.92	19.97	19.63	18.94	18.59	20.03	20.12	20.25	19.56	19.15
8600	18.26	18.37	18.34	17.92	17.63	18.55	18.67	19.06	18.60	18.25
8800	17.12	17.23	17.26	17.09	16.92	17.54	17.64	18.05	17.90	17.65
9000	16.20	16.28	16.21	16.26	16.22	16.79	16.88	17.07	17.16	17.08
9200	15.50	15.53	15.35	15.56	15.62	16.13	16.20	16.23	16.50	16.55
9400	14.90	14.92	14.69	14.96	15.08	15.67	15.69	15.59	15.90	16.03
9600	14.53	14.54	14.20	14.46	14.56	15.37	15.37	15.13	15.44	15.57
9800	14.12	14.11	13.79	14.01	14.13	15.14	15.13	14.82	15.10	15.27
10000	13.82	13.81	13.55	13.73	13.88	14.95	14.93	14.69	14.90	15.04
10200	13.61	13.60	13.39	13.53	13.65	14.94	14.92	14.68	14.86	15.03
10400	13.51	13.51	13.39	13.48	13.59	14.98	14.98	14.81	14.98	15.12
10600	13.39	13.39	13.43	13.42	13.48	15.12	15.08	14.98	15.09	15.19
10800	13.45	13.46	13.57	13.51	13.52	15.27	15.28	15.17	15.21	15.25
11000	13.33	13.37	13.65	13.56	13.53	15.37	15.36	15.35	15.30	15.28
12000	12.58	12.69	13.18	13.16	13.18	14.27	14.29	14.43	14.14	13.99
13000	11.58	11.71	12.60	12.89	13.06	12.23	12.36	13.09	13.24	13.22
14000	11.78	11.98	13.02	14.00	14.48	12.63	12.81	13.32	14.13	14.56
14300	12.05	12.24	13.30	14.27	14.69	12.93	13.09	13.58	14.58	15.06
15000	12.81	12.96	13.80	14.38	14.52	13.04	13.21	13.91	14.68	14.93
16000	12.94	13.05	13.19	13.37	13.30	12.25	12.41	13.41	13.54	13.47
17000	10.64	10.71	10.51	10.65	10.64	10.76	10.85	11.10	11.31	11.38
18000	8.03	8.09	7.98	8.12	8.16	8.80	8.82	8.70	8.90	8.98
19000	5.98	6.06	6.26	6.39	6.44	6.78	6.85	7.01	7.11	7.11
20000	4.96	5.05	5.39	5.65	5.74	5.64	5.74	6.14	6.29	6.27
21000	4.54	4.64	5.03	5.39	5.57	5.47	5.56	5.93	6.24	6.34
22000	4.76	4.87	5.43	5.82	6.04	5.99	6.07	6.25	6.80	7.05
23000	5.21	5.34	6.02	6.47	6.74	6.45	6.56	6.90	7.48	7.74
24000	5.95	6.08	6.89	7.48	7.79	6.82	6.97	7.67	8.12	8.28
25000	6.94	7.09	7.93	8.47	8.71	7.55	7.69	8.39	8.78	8.92
26000	8.64	8.73	9.32	9.56	9.58	8.94	9.01	9.28	9.65	9.81
27000	11.24	11.28	10.96	10.86	10.70	10.52	10.58	10.40	10.57	10.62
28000	13.24	13.20	11.94	11.88	11.71	10.51	10.64	11.23	10.93	10.66
29000	10.67	10.69	10.16	10.00	9.87	9.27	9.35	9.96	9.74	9.61
30000	7.51	7.54	7.53	7.58	7.61	8.29	8.28	7.97	8.42	8.69
31000	5.17	5.26	5.35	5.72	5.95	6.15	6.18	6.02	6.53	6.75
32000	3.46	3.56	3.96	4.39	4.62	4.34	4.43	4.79	5.04	5.07
33000	2.21	2.34	2.90	3.13	3.23	2.98	3.09	3.59	3.66	3.63
34000	1.58	1.68	2.22	2.38	2.45	2.56	2.65	3.02	3.17	3.23
35000	1.26	1.36	1.88	2.03	2.11	2.55	2.59	2.68	2.89	3.01
36000	1.26	1.36	1.83	2.17	2.37	2.50	2.59	2.67	3.06	3.25
37000	1.54	1.68	2.32	2.88	3.11	2.35	2.50	3.13	3.40	3.44
38000	2.35	2.55	3.63	4.15	4.34	3.04	3.23	4.26	4.62	4.73
39000	4.39	4.60	5.74	6.52	6.81	5.33	5.55	6.54	7.67	8.36
40000	7.88	8.11	7.79	8.33	8.37	7.29	7.53	8.39	8.67	8.51

Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE (Full band)
INPUT POWER = -25 dBm




INSERTION LOSS vs. TEMPERATURE (Pass band)
INPUT POWER = -25 dBm




INPUT RETURN LOSS vs. TEMPERATURE (Full band)
INPUT POWER = -25 dBm




INPUT RETURN LOSS vs. TEMPERATURE (Pass band)
INPUT POWER = -25 dBm




OUTPUT RETURN LOSS vs. TEMPERATURE (Full band)
INPUT POWER = -25 dBm




OUTPUT RETURN LOSS vs. TEMPERATURE (Pass band)
INPUT POWER = -25 dBm



GROUP DELAY vs. TEMPERATURE (Full band)
INPUT POWER = -25 dBm




GROUP DELAY vs. TEMPERATURE (Pass band)
INPUT POWER = -25 dBm




Case Style DQ

DQ1225

Outline Dimensions





Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3 Pl. ± .004


Notes:

1. Case material: Plastic.
2. Termination finish:
   - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
   - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified


This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION



REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M152656	NEW RELEASE	09/11/15	ITG	MY

SUGGESTED MOUNTING CONFIGURATION
FOR DQ1225 CASE STYLE, "12FL02" PIN CODE



NOTES:

1. TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .0066"±.0007". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	09/10/15
TOLERANCES ON:	CHECKED	GF	09/11/15
2 PL DECIMALS ±	APPROVED	MY	09/11/15
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits®
13 Neptune Avenue
Brooklyn NY 11235

PL, 12FL02, DQ1225, TB-844+


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-451	OR
FILE: 98PL451	SCALE: 16:1	SHEET: 1 OF 1	

Evaluation Board and Circuit

To be used with Mini-Circuits 50 Ohm 2.92 connectors B20-118-F1+.
Connectors are sold separately.



TB-844-732+



Schematic Diagram


Note:

PCB Material: RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.0066 inch.


Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Evaluation Board and Circuit



TB-844-732C+



Schematic Diagram

Notes:

1. 50 Ohm 2.92 mm Female connectors.
2. PCB Material: RO4350 or equivalent, Dielectric Constant=3.5, Thickness=.0066 inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV82

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020C
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.