

REPLACEMENT PART REFERENCE GUIDE, ZYSW-2-50DR

AN-80-018

ORIGINAL PART: ZYSW-2-50DR

REPLACEMENT PART: ZYSW-2-50DR+ (RoHS version)



Replacement Part has been judged by Mini-Circuits Engineering as a suitable replacement to Original Part^a

MECHANICAL DIMENSIONS


ORIGINAL PART: ZYSW-2-50DR

REPLACEMENT PART: ZYSW-2-50DR+

Case Style ZZ121 (No Change)

Outline Dimensions

ZZ121



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
ZZ121	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.00)	.38 (9.65)	.61 (15.49)	--	.800 (20.32)	.800 (20.32)	.76 (19.30)	.125 (3.18)	1.688 (42.88)	2.18 (55.37)

CASE#	P	Q	WT. GRAMS
ZZ121	.75 (19.05)	.07 (1.78)	85.0

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .03; 3 Pl. ± .015

Notes:
a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.

CONCLUSION:

1) **FORM-FIT-FUNCTIONAL ANALYSIS_a:**

The Replacement part is Form, Fit compatible.

Following is a summary of changes/improvements in the Specification:

For typical performance and Graphs: See paragraphs 2 and 3

Parameter	Frequency (MHz)		Current Design			New Design		
	Min.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.
Insertion Loss (dB)	0.1	500		0.90	1.50		0.80	1.50
	500	2000		1.30	1.70		1.30	1.70
	2000	5000		2.10	-		1.90	-
Isolation (dB) IN-OUT	0.1	500	38.00	44.00		38.00	50.00	
	500	2000	28.00	38.00		28.00	40.00	
	2000	5000	-	20.00		-	18.00	
VSWR (:1) IN PORT	0.1	3000		1.40	2.00		1.45	
	3000	5000		-	2.50		1.65	
VSWR (:1) OUT PORT (ON)	0.1	3000		1.40	2.00		1.30	
	3000	5000			2.50		1.45	
Compression 1 dB	10	500	15.00	20.00		>	20	
	500	2000	19.00	23.00		>	24	
	2000	5000	18.00	21.00		>	23	
Max. Input Power (dBm)	-	-			24			31*
Switching time [ns], 50% of Control to 90% RF(Turn-on) and 10% RF(Turn-off)	-	-		20	40		20	
Rise/Fall time [ns] (10%-90%)	-	-		6	12		6	

* Frequency = 500-5000 MHz.

Notes:
a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.


2) TYPICAL PERFORMANCE COMPARISON AT ROOM TEMPERATURE:

MODEL: ZYSW-2-50DR (RF Parameters)


RF Parameters	Frequency		Current Design @ 1 Unit			New Design @ 5 Units		
	Low	High	Min.	Ave.	Max.	Min.	Ave.	Max.
Insertion Loss S-1(ON) (dB)	10	500	0.46	0.58	0.64	0.66	0.73	0.81
	500	2000	0.64	0.72	0.88	0.81	0.99	1.20
	2000	5000	0.88	1.23	1.63	1.14	1.37	1.63
Insertion Loss S-2(ON) (dB)	10	500	0.47	0.58	0.63	0.66	0.73	0.81
	500	2000	0.63	0.70	0.85	0.80	0.98	1.18
	2000	5000	0.85	1.20	1.60	1.15	1.35	1.66
Isolation S-2 (1-ON) (dB)	10	500	57.86	65.98	97.90	49.82	64.17	117.78
	500	2000	43.31	51.73	58.02	37.20	42.43	49.98
	2000	5000	36.87	39.43	43.31	16.76	28.14	37.42
Isolation S-1 (2-ON) (dB)	10	500	57.39	65.59	96.53	49.68	63.95	102.35
	500	2000	43.06	51.30	57.41	37.18	42.37	49.86
	2000	5000	35.97	38.19	43.08	17.16	28.67	37.47
Return Loss SUM Port [1(ON)] (dB)	10	3000	16.47	24.68	27.03	11.35	19.52	46.40
	3000	5000	16.47	23.82	31.90	11.35	13.67	25.14
Return Loss SUM Port [2(ON)] (dB)	10	3000	17.45	25.08	27.14	11.34	19.61	46.66
	3000	5000	17.45	27.59	47.42	11.34	13.88	24.17
Return Loss Port 1(ON) (dB)	10	3000	15.49	27.32	37.90	14.29	21.92	41.71
	3000	5000	14.70	21.68	29.90	14.51	16.80	29.27
Return Loss Port 2(ON) (dB)	10	3000	15.78	26.68	34.86	14.18	21.97	42.15
	3000	5000	15.12	21.95	33.95	14.30	17.14	29.62

Notes:
a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.

3) TYPICAL PERFORMANCE GRAPHS AT ROOM TEMPERATURE:



Notes:
a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.



4) SWITCHING TIME CHARACTERISTICS AND VIDEO LEAKAGE

MODEL: ZYSW-2-50DR+ (Redesigned Model)

Supply Voltage (V)		5, -5	5, -5	5, -5	5, -5	5, -5
Control voltage (V)		5,0	5,0	5,0	5,0	5,0
Measurement Port	Parameter	Unit 1	Unit 2	Unit 3	Unit 4	Unit 5
Port 1	On time (ns)	16.88	17.12	17.09	16.94	16.88
	Off time (ns)	17.97	18.12	18.16	17.66	18.03
Port 2	On time (ns)	20.06	20.25	21.16	20.31	21.03
	Off time (ns)	14.31	14.03	15.00	13.69	13.75
Port 1	Rise time (ns)	4.22	4.38	4.41	4.53	4.22
	Fall time (ns)	5.44	5.25	5.56	4.66	4.69
Port 2	Rise time (ns)	3.97	4.06	4.97	4.16	4.78
	Fall time (ns)	4.75	4.50	5.59	4.31	4.44
Port 1	On Video Leakage (mV p-p)	11.20	14.60	13.90	13.10	14.70
	Off Video Leakage (mV p-p)	27.30	31.70	29.40	30.20	32.90
Port 2	On Video Leakage (mV p-p)	13.10	13.80	12.50	13.30	11.50
	Off Video Leakage (mV p-p)	26.20	33.60	29.30	29.60	27.40

Notes:
a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.

IMPORTANT NOTICE

© 2015 Mini-Circuits

This document is provided as an accommodation to Mini-Circuits customers in connection with Mini-Circuits parts only. In that regard, this document is for informational and guideline purposes only. Mini-Circuits assumes no responsibility for errors or omissions in this document or for any information contained herein.

Mini-Circuits may change this document or the Mini-Circuits parts referenced herein (collectively, the "Materials") from time to time, without notice. Mini-Circuits makes no commitment to update or correct any of the Materials, and Mini-Circuits shall have no responsibility whatsoever on account of any updates or corrections to the Materials or Mini-Circuits' failure to do so. Mini-Circuits customers are solely responsible for the products, systems, and applications in which Mini-Circuits parts are incorporated or used. In that regard, customers are responsible for consulting with their own engineers and other appropriate professionals who are familiar with the specific products and systems into which Mini-Circuits' parts are to be incorporated or used so that the proper selection, installation/integration, use and safeguards are made. Accordingly, Mini-Circuits assumes no liability therefore.

In addition, your use of this document and the information contained herein is subject to Mini-Circuits' standard terms of use, which are available at Mini-Circuits' website at www.minicircuits.com/homepage/terms_of_use.html.

Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation: (i) by Mini-Circuits of such third-party's products, services, processes, or other information; or (ii) by any such third-party of Mini-Circuits or its products, services, processes, or other information.

Notes:

a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.