



Mini-Circuits

COAXIAL

# Precision Fixed Attenuator **BW-30N250W+**

50Ω 250W 30dB DC to 8000 MHz N-Male to N-Female

## THE BIG DEAL

- Wideband Operation, DC to 8000 MHz
- High Power Handling, 250W
- Excellent VSWR, 1.11 Typ.
- Excellent Flatness,  $\pm 0.4$  dB Typ.
- Uni-directional power rating.

## APPLICATIONS

- Test and Measurement Equipment
- LTE & 5G MIMO Infrastructure
- Satellite Communications
- Radar, EW, and ECM Defense Systems



Generic photo used for illustration purposes only

Model No.	BW-30N250W+
Case Style	GH3249
Connectors	N-Male to N-Female

### +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## PRODUCT OVERVIEW

Mini-Circuits' BW-30N250W+ is a 30 dB coaxial precision fixed unidirectional attenuator providing high power handling of up to 250W over the DC to 8 GHz frequency range. This model supports many of high-power applications requiring precise attenuation over a broad frequency range including high-power measurement, instrumentation, and more. It provides excellent VSWR (1.11 typ.), outstanding attenuation flatness ( $\pm 0.4$  dB) and excellent thermal stability from -55 to 125 °C. It features rugged construction with N-male to N-female connectors and heat dissipation fins for efficient cooling.

## KEY FEATURES

Features	Advantages
Wideband Operation, DC to 8000 MHz	Wide frequency range makes the BW-30N250W+ suitable for a wide variety of applications.
High power handling to 250W	Supports high-power test lab and system applications by protecting sensitive test equipment that is often damaged when exposed to high RF input power.
Excellent VSWR, 1.11:1 typ.	Well-matched for 50Ω systems; reduces effects of phase variation
Excellent flatness, $\pm 0.4$ dB	Provides consistent attenuation performance across the entire frequency band.
Rugged construction	Excellent durability for a long lifetime of use
Wide operating temperature range, -55 to 125 °C	Designed with heat dissipation fins for efficient cooling, the BW-30N250W+ provides reliable performance over extreme operating conditions. Note: See max power derating at high temperature.





COAXIAL

Precision Fixed Attenuator **BW-30N250W+**

Mini-Circuits

50Ω 250W 30dB DC to 8000 MHz N-Male to N-Female

## ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Units
Frequency Range	-	DC	-	8000	MHz
Attenuation	DC-2000	29	29.8	31	dB
	2000-4000	29	29.9	31	
	4000-6000	28.5	29.8	31.5	
	6000-8000	27.5	29.4	32.5	
Attenuation Flatness ( $\pm$ )	DC-8000	-	0.4	-	dB
VSWR	DC-2000	-	1.05	1.20	:1
	2000-4000	-	1.11	1.35	
	4000-6000	-	1.18	1.40	
	6000-8000	-	1.10	1.50	
Input Power (N- Male Input) <sup>1</sup>	DC-8000	-	-	250	W
Input Power (N- Female Output)	DC-8000	-	-	15	W

1. Max. input power at 25°C ambient, derate to 25W at 125°C.

## ABSOLUTE MAXIMUM RATINGS


Parameter	Ratings
Operating Case Temperature	-55 °C to +125 °C
Storage Temperature	-55 °C to +125 °C
Input Power (N-Male Input)	250 Watt
Input Power (N-Female Output)	15 Watt
Input Peak Power <sup>2</sup>	1000 Watt.

1. Permanent damage may occur if any of these limits are exceeded.

2. Peak power <5  $\mu$ SEC. PW, /<0.1% duty cycle.

▲ This model is uni-directional relative to the specific power rating i.e the power rating at the N-Male port is not equal to the power rating for signals input to the N-Female port.

## FUNCTIONAL DIAGRAM





## COAXIAL

# Precision Fixed Attenuator **BW-30N250W+**

Mini-Circuits

50  $\Omega$  250W 30dB DC to 8000 MHz N-Male to N-Female

### COAXIAL CONNECTIONS

Input	N-Male
Output	N-Female

### CONNECTOR SPECIFICATIONS


Description	Connector 1	Connector 2
Type	N-Male	N-Female
Orientation	Straight	
Mounting Type	Standard	
Impedance	50 $\Omega$	
Coupling Nuts	Stainless Steel, Silver Plated	
Center Contacts	BeCu, Silver Plated	

### MECHANICAL SPECIFICATIONS

Housing	Aluminum Alloy, Chemical Conversion Coat
Heat Sinks	Aluminum Alloy, Black Anodize Finish (0.5°C/Watt) <sup>1</sup>
Internal Resistive Elements	Beryllium Oxide Or Aluminum Nitride Ceramic With Thick Film And/Or Thin Film Resistor

1. Heat sink thermal rise (calculated)

### OUTLINE DRAWING



Weight (MAX.): 3820 grams

Dimensions are in inches (mm). Tolerances: 2 PL  $\pm 0.05$  [1.27]; 3 PL  $\pm 0.030$  [77]







COAXIAL

# Precision Fixed Attenuator **BW-30N250W+**

Mini-Circuits

50Ω 250W 30dB DC to 8000 MHz N-Male to N-Female

## TYPICAL PERFORMANCE CURVES



### NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)





# Fixed Attenuator

# BW-30N250W+

## Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)	
		N-Male	N-Female
10	29.68	1.01	1.02
100	29.73	1.02	1.02
500	29.80	1.04	1.04
1000	29.85	1.03	1.06
1200	29.87	1.03	1.07
1400	29.88	1.05	1.07
1600	29.90	1.06	1.08
1800	29.90	1.06	1.08
2000	29.92	1.06	1.08
2200	29.93	1.05	1.08
2400	29.93	1.06	1.09
2600	29.94	1.06	1.09
2800	29.93	1.04	1.09
3000	29.93	1.08	1.10
3200	29.93	1.08	1.11
3400	29.93	1.08	1.13
3600	29.93	1.14	1.14
3800	29.93	1.19	1.15
4000	29.91	1.15	1.17
4200	29.91	1.19	1.19
4400	29.90	1.21	1.20
4600	29.85	1.13	1.21
4800	29.83	1.14	1.21
5000	29.81	1.16	1.20
5200	29.78	1.13	1.19
5400	29.73	1.10	1.17
5600	29.70	1.08	1.15
5800	29.66	1.05	1.13
6000	29.64	1.08	1.11
6200	29.62	1.12	1.08
6400	29.57	1.09	1.07
6600	29.52	1.05	1.07
6800	29.47	1.06	1.08
7000	29.43	1.06	1.09
7200	29.39	1.06	1.11
7400	29.35	1.05	1.13
7600	29.30	1.05	1.13
7800	29.24	1.07	1.14
8000	29.20	1.11	1.13

## Typical Performance Curves




# Case Style

## Outline Dimensions

**GH**

**GH3249**



Weight (MAX.): 3820 grams

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .05$  [1.27]; 3 Pl.  $\pm .030$  [.77]

### Notes:

1. Case material: Aluminum alloy
2. Case Finish: Chemical conversion coat
3. Heat sinks material: Aluminum alloy
4. Heat sinks Finish: Black anodize

**Mini-Circuits®**

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 125°C, 5 cycles	MIL-STD-202, Method 107
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I
Connector Durability	500 mating/unmating cycles	MIL-PRF-39012E, PARAGRAPH 4.6.12