


Case Style

D

D08
D09

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
D08	1.000	1.025	.390 (9.91)	.430 (10.92)	.500 (12.70)	.525 (13.34)	.025 (.64)	.300 (7.62)	.200 (5.08)	.09 (2.29)	.13 (3.30)	.150 (3.81)
D09			.240 (6.10)	.280 (7.11)								

CASE#	N	P	WT.GRAMS
D08	.20 (5.08)	.14 (3.56)	8.5
D09			7.5

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.

 **Mini-Circuits**[®]

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified