


Outline Dimensions



* OVERALL CONNECTOR OR CABLE & BOOT DIM
[CONNECTOR SHAPE MAY VARY]

GM1526 SERIES
E-Z LOCK SMA MALE (CONN-1)
SMA MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	T		WEIGHT GRAMS
	FEET	METERS					INCHES	MM	
GM1526-.33	.33	.10	.43 (10.92)	- -	.36 (9.14)	.312 (7.92)	+.50/-0	+12.7/-0	17
GM1526-.67	.67	.20					+.50/-0	+12.7/-0	22
GM1526-1.0	1.00	.30					+.50/-0	+12.7/-0	26
GM1526-1.5	1.50	.46					+.50/-0	+12.7/-0	33
GM1526-1.64	1.64	.50					+.50/-0	+12.7/-0	35
GM1526-2	2.00	.61					+.50/-0	+12.7/-0	40
GM1526-3	3.00	.91					+.72/-0	+18.3/-0	53
GM1526-3.28	3.28	1.00					+.79/-0	+20.0/-0	57
GM1526-4	4.00	1.22					+.96/-0	+24.4/-0	67
GM1526-5	5.00	1.52					+1.20/-0	+30.5/-0	81
GM1526-6	6.00	1.83					+1.44/-0	+36.6/-0	94
GM1526-6.56	6.56	2.00					+1.57/-0	+40.0/-0	102
GM1526-18	18.00	5.49					+4.32/-0	+109.7/-0	257

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. Flexible Coaxial Cable.