

Coaxial High Pass Filter

BHP-900+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	72.21	0.04	200.0	0.700
100.0	89.68	0.04	300.0	0.510
200.0	76.93	0.06	400.0	0.700
300.0	65.78	0.08	500.0	0.810
400.0	56.60	0.12	555.0	0.840
500.0	46.37	0.18	560.0	0.850
560.0	39.31	0.25	600.0	0.960
600.0	34.17	0.27	650.0	1.100
650.0	27.47	0.37	690.0	1.330
690.0	21.80	0.44	695.0	1.360
700.0	20.35	0.48	700.0	1.360
705.0	19.64	0.44	705.0	1.410
710.0	18.91	0.47	710.0	1.460
760.0	11.49	0.92	760.0	2.070
765.0	10.76	1.02	765.0	2.150
770.0	10.03	1.12	770.0	2.250
775.0	9.31	1.25	775.0	2.340
805.0	5.35	2.60	805.0	2.980
810.0	4.78	2.97	810.0	3.080
815.0	4.25	3.41	815.0	3.170
820.0	3.76	3.91	820.0	3.240
825.0	3.31	4.49	825.0	3.300
830.0	2.90	5.14	830.0	3.330
835.0	2.54	5.89	835.0	3.350
840.0	2.23	6.73	840.0	3.340
845.0	1.96	7.67	845.0	3.310
850.0	1.72	8.71	850.0	3.260
855.0	1.53	9.88	855.0	3.190
860.0	1.36	11.17	860.0	3.110
865.0	1.23	12.62	865.0	3.030
870.0	1.11	14.24	870.0	2.940
875.0	1.02	16.08	875.0	2.840
880.0	0.95	18.18	880.0	2.750
885.0	0.89	20.65	885.0	2.650
900.0	0.77	29.93	900.0	2.400
950.0	0.66	18.67	950.0	1.810
1000.0	0.60	17.72	1000.0	1.440
1050.0	0.54	19.19	1050.0	1.330
1100.0	0.50	21.19	1100.0	1.190
1150.0	0.47	22.82	1150.0	1.080
1200.0	0.45	23.54	1200.0	0.990
1250.0	0.45	23.39	1250.0	0.910
1300.0	0.44	22.60	1300.0	0.850
1350.0	0.43	21.70	1350.0	0.790
1400.0	0.43	20.69	1400.0	0.750
1450.0	0.43	19.80	1450.0	0.700
1500.0	0.44	19.04	1500.0	0.670
1550.0	0.45	18.36	1550.0	0.640
1600.0	0.46	17.89	1600.0	0.620
2000.0	0.50	17.31	2000.0	0.480
2500.0	0.49	19.55	2500.0	0.410
3000.0	0.56	18.45	3000.0	0.380

REV. X1
BHP-900+
070628
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

