



### Outline Dimensions



### PCB Land Pattern



SUGGESTED LAYOUT,  
TOLERANCE TO BE WITHIN  $\pm 0.02$

DENOTES METALLIZATION  
 DENOTES SOLDER RESIST

CASE #	A	B	C	D	E	F	G	H	J	K	L	M
BL1543-1	.93 (23.62)	1.42 (36.07)	.25 (6.35)	.063 (1.60)	.100 (2.54)	.160 (4.06)	.060 (1.52)	.040 (1.02)	--	.070 (1.78)	.140 (3.56)	.970 (24.64)

CASE #	N	P	Q	R	S	T	U	V	W	WT. GRAM
BL1543-1	1.165 (29.59)	.100 (2.54)	.065 (1.65)	.980 (24.89)	.620 (15.75)	1.000 (25.40)	.640 (16.26)	.065 (1.65)	.083 (2.10)	6.5

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3Pl.  $\pm .005$

#### Notes:

- Case material: Copper-Nickel alloy.
- Base material: Printed wiring laminate.
- Termination finish: 3-5µinch (.08-.13 microns) Gold over 120-240µinch (3.05-6.10 microns) Nickel plate.  
All models, (+) suffix.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified