


Outline Dimensions

GU1840



CASE #	A	B	C	D	E	F	G	H	J	K	L	WT.GRAMS
GU1840	.166 (4.22)	.150 (3.81)	.155 (3.94)	.100 (2.54)	.037 (.94)	.025 (.64)	.012 (.30)	.060 (1.52)	.184 (4.67)	.030 (.76)	.004 (0.10)	.10

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .01; 3 Pl. ± .005

Notes:

1. Open style, Ceramic Base.
2. Termination finish: Palladium Silver.
3. Must be isolated from external conductors on mounting surface. Suggested solder mask area is .025 x .025. At Mini-Circuits option via may be removed.
4. Top-Hat total thickness: .013 inches MAX.
5. Orientation Dot on Top Hat corresponds to Pin #1.



P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS