


## Outline Dimensions

JG1228



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	S	WT, GRAM
JG1228	.910" (23.11)	.910" (23.11)	.252" (6.40)	.125" (3.18)	.165" (4.19)	.078" (1.98)	.060" (1.52)	.100" (2.54)	.058" (1.47)	.950" (24.13)	.115" (2.92)	.950" (24.13)	.115" (2.92)	.078" (1.98)	.060" (1.52)	8.5

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

### Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:  
For RoHS Case Styles: 2-5  $\mu$  inch (.05-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate.  
For RoHS-5 Case Styles: Tin-Lead plate.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661