

Coaxial Low Pass Filter

BLP-1200+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.00	38.30	10.0	0.900
195.0	0.20	15.70	100.0	1.000
380.0	0.40	14.00	195.0	1.000
565.0	0.20	19.00	285.0	0.800
750.0	0.30	25.30	380.0	0.900
930.0	0.50	20.10	470.0	1.000
1000.0	0.60	18.10	565.0	1.100
1180.0	4.30	5.30	655.0	1.100
1200.0	5.70	3.40	750.0	1.100
1300.0	17.70	0.70	840.0	1.200
1420.0	32.20	0.50	930.0	1.400
1500.0	43.80	0.40	1000.0	1.600
1550.0	53.20	0.30	1150.0	2.800
1600.0	58.30	0.30	1180.0	2.400
1620.0	57.90	0.30	1200.0	2.500
1690.0	58.00	0.30	1300.0	1.200
1720.0	55.60	0.20	1400.0	0.500
2000.0	58.70	0.20	1420.0	0.600
2050.0	61.60	0.10	1440.0	1.100
2070.0	62.20	0.10	1500.0	0.400
2100.0	63.00	0.10	1550.0	0.800
2110.0	62.90	0.10	1600.0	1.300
2120.0	62.00	0.10	1620.0	1.100
2130.0	64.70	0.10	1690.0	1.600
2140.0	66.10	0.10	1700.0	1.000
2150.0	64.30	0.10	1720.0	0.300
2160.0	65.10	0.10	1945.0	1.000
2200.0	66.00	0.10	2000.0	1.700
2300.0	70.50	0.10	2050.0	2.100
2500.0	66.00	0.10	2070.0	1.400

REV. X1
BLP-1200+
060724
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

