

Coaxial Low Pass Filter

BLP-21.4+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.10	31.70	1.0	36.160
2.0	0.12	26.40	2.0	36.110
5.0	0.21	24.00	5.0	36.800
10.0	0.29	23.30	10.0	38.690
15.0	0.45	16.10	15.0	42.250
20.0	0.45	27.70	20.0	55.730
22.0	0.60	21.60	22.0	69.400
23.5	1.46	9.60	23.0	81.700
24.5	3.45	4.40	23.5	88.290
25.0	4.95	3.00	24.0	92.340
27.0	12.37	0.70	24.5	91.460
29.0	19.53	0.30	25.0	85.660
30.0	22.77	0.30	26.0	66.760
31.0	25.77	0.20	27.0	48.880
32.0	28.62	0.20	28.0	36.300
33.0	31.31	0.20	29.0	28.750
35.0	36.30	0.10	30.0	24.490
38.0	42.86	0.10	31.0	19.400
39.0	45.08	0.10	32.0	17.880
40.0	46.77	0.10	33.0	13.730
41.0	48.73	0.10	34.0	13.700
86.5	76.16	0.10	35.0	14.630
105.0	77.54	0.10	36.0	8.860
124.0	75.42	0.10	38.0	7.640
143.0	75.51	0.00	39.0	7.390
162.0	74.57	0.10	40.0	9.970
171.5	75.79	0.10	41.0	2.670
181.0	81.15	0.10	86.5	2.560
190.5	76.97	0.10	96.0	2.440
200.0	72.23	0.10	105.0	2.280

REV. X1
BLP-21.4+
070603
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

