

Coaxial Low Pass Filter

BLP-450+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.00	42.40	10.0	2.000
80.0	0.10	33.60	80.0	2.100
147.5	0.10	28.30	147.5	2.200
217.5	0.20	21.00	217.5	2.300
285.0	0.30	21.40	285.0	2.600
355.0	0.50	16.30	355.0	3.300
400.0	0.60	18.00	400.0	4.300
420.0	1.00	12.80	410.0	4.800
440.0	2.80	5.20	420.0	5.300
545.0	26.50	0.40	430.0	5.900
555.0	28.60	0.30	440.0	6.000
565.0	30.60	0.30	545.0	1.500
570.0	31.50	0.30	550.0	1.300
575.0	32.50	0.30	555.0	1.500
580.0	33.50	0.30	560.0	1.400
590.0	35.40	0.30	565.0	1.100
620.0	40.90	0.20	570.0	0.900
680.0	51.20	0.20	575.0	1.200
700.0	54.80	0.10	580.0	1.100
720.1	57.90	0.10	590.0	1.500
750.0	63.00	0.20	600.0	1.700
975.0	69.50	0.10	620.0	0.900
1112.5	78.50	0.10	640.0	1.200
1250.0	68.90	0.10	680.0	0.600
1387.5	69.80	0.10	700.0	0.600
1525.0	70.50	0.10	720.0	0.600
1592.5	68.10	0.10	750.0	0.600
1662.5	71.20	0.10	975.0	0.600
1730.0	72.20	0.10	1042.5	0.500

REV. X1
BLP-450+
060724
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

