

Test Cable, SMA-Male/N-Male

CBL-2M-SMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
0.3	0.02	53.28	50.84
0.7	0.02	51.07	49.06
1.0	0.02	49.67	48.04
3.0	0.04	45.68	45.59
5.0	0.05	43.87	43.45
7.0	0.06	42.96	42.32
9.0	0.07	42.22	41.36
10.0	0.07	41.75	41.35
30.0	0.13	42.48	44.23
50.0	0.16	51.82	44.88
70.0	0.19	42.24	45.03
90.0	0.22	43.15	41.95
100.0	0.24	42.97	41.10
200.0	0.34	44.16	41.75
300.0	0.42	47.94	40.78
400.0	0.49	43.98	39.66
500.0	0.55	41.91	37.85
600.0	0.61	42.01	36.79
700.0	0.66	38.77	36.12
800.0	0.71	38.69	35.81
900.0	0.76	37.48	36.05
1000.0	0.81	39.90	35.37
1500.0	1.00	32.51	34.47
2000.0	1.18	32.42	36.89
2500.0	1.33	36.02	37.41
3000.0	1.48	35.90	37.81
3500.0	1.61	38.25	36.62
4000.0	1.75	35.60	37.15
4500.0	1.88	32.70	33.18
5000.0	2.00	31.28	32.26
5500.0	2.13	30.55	30.53
6000.0	2.23	28.67	29.06
6500.0	2.37	28.87	27.70
7000.0	2.42	31.82	27.26
7500.0	2.56	30.25	25.78
8000.0	2.64	34.29	26.16
8500.0	2.72	27.98	24.80
9000.0	2.85	30.57	24.32
9500.0	3.00	27.62	23.74
10000.0	3.11	28.38	23.69
10500.0	3.21	25.57	23.44
11000.0	3.41	26.07	23.23
11500.0	3.56	25.02	25.37
12000.0	3.65	27.56	23.96
12500.0	3.70	24.05	24.78
13000.0	3.78	22.78	23.42
13500.0	3.83	27.99	23.44
14000.0	3.86	23.32	20.75
14500.0	3.97	35.66	21.96
15000.0	4.00	21.43	20.38
15500.0	4.17	30.91	21.82
16000.0	4.06	20.72	20.58
16500.0	4.20	29.14	23.10
17000.0	4.18	22.13	22.57
17500.0	4.35	28.95	26.55
18000.0	4.22	28.12	25.11