

# Coaxial High Pass Filter

# BHP-150+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	71.12	0.09	70.0	4.130
50.0	72.50	0.15	75.0	4.020
70.0	50.20	0.13	80.0	4.460
75.0	45.17	0.14	85.0	4.810
80.0	40.39	0.15	90.0	5.240
85.0	35.75	0.18	95.0	5.800
90.0	31.22	0.22	100.0	6.670
95.0	26.73	0.27	101.0	6.900
100.0	22.30	0.33	102.0	7.140
101.0	21.42	0.37	103.0	7.390
102.0	20.53	0.39	104.0	7.650
103.0	19.63	0.41	105.0	7.910
104.0	18.75	0.44	110.0	9.630
105.0	17.87	0.47	111.0	10.090
110.0	13.42	0.71	112.0	10.600
111.0	12.52	0.77	113.0	11.170
112.0	11.64	0.86	114.0	11.770
113.0	10.77	0.96	115.0	12.430
114.0	9.91	1.10	120.0	15.590
115.0	9.04	1.23	121.0	16.130
120.0	5.14	2.53	122.0	16.580
122.0	3.87	3.46	123.0	16.930
123.0	3.30	4.07	124.0	17.170
124.0	2.81	4.77	125.0	17.280
125.0	2.37	5.58	126.0	17.260
126.0	2.00	6.52	127.0	17.110
127.0	1.69	7.60	128.0	16.840
128.0	1.43	8.81	129.0	16.450
129.0	1.22	10.18	130.0	15.980
130.0	1.05	11.74	131.0	15.450
132.0	0.82	15.52	132.0	14.880
133.0	0.76	17.84	133.0	14.290
150.0	0.58	16.01	150.0	7.770
200.0	0.29	31.20	200.0	3.640
250.0	0.24	30.41	250.0	2.270
300.0	0.25	21.92	300.0	1.620
350.0	0.28	18.41	350.0	1.250
400.0	0.31	16.38	400.0	1.020
450.0	0.35	15.24	450.0	0.850
500.0	0.36	14.49	500.0	0.750
550.0	0.39	13.94	550.0	0.680
600.0	0.41	13.50	600.0	0.600
650.0	0.44	13.13	650.0	0.550
700.0	0.45	12.80	700.0	0.510
750.0	0.47	12.46	750.0	0.490
800.0	0.49	12.20	800.0	0.470
850.0	0.51	11.93	850.0	0.440
900.0	0.53	11.70	900.0	0.430
950.0	0.55	11.48	950.0	0.410
1000.0	0.57	11.26	1000.0	0.410
1500.0	0.78	9.75	1500.0	0.340
2000.0	0.89	9.30	2000.0	0.320

REV. X1  
 BHP-150+  
 070628  
 Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

