

# Coaxial High Pass Filter

# BHP-300+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	70.05	0.11	100.0	1.520
100.0	67.77	0.08	125.0	1.840
125.0	56.38	0.14	150.0	2.140
150.0	45.47	0.17	159.0	2.240
159.0	41.59	0.17	160.0	2.250
160.0	41.15	0.18	162.0	2.250
162.0	40.29	0.18	163.0	2.280
163.0	39.86	0.18	164.0	2.290
164.0	39.43	0.18	170.0	2.450
170.0	36.88	0.19	180.0	2.690
180.0	32.65	0.21	190.0	2.940
190.0	28.46	0.26	200.0	3.320
200.0	24.28	0.33	205.0	3.560
205.0	22.20	0.38	206.0	3.620
206.0	21.78	0.39	207.0	3.670
207.0	21.35	0.40	208.0	3.720
208.0	20.94	0.41	209.0	3.780
209.0	20.52	0.42	210.0	3.840
210.0	20.10	0.44	211.0	3.900
212.0	19.26	0.46	212.0	3.970
220.0	15.91	0.61	220.0	4.590
225.0	13.82	0.75	225.0	5.090
228.0	12.58	0.86	228.0	5.440
229.0	12.16	0.91	229.0	5.560
230.0	11.75	0.96	230.0	5.690
232.0	10.94	1.07	232.0	5.940
233.0	10.53	1.13	233.0	6.080
234.0	10.13	1.20	234.0	6.220
235.0	9.74	1.27	235.0	6.360
236.0	9.34	1.35	236.0	6.500
250.0	4.46	3.58	250.0	8.290
252.0	3.91	4.13	252.0	8.410
254.0	3.41	4.76	254.0	8.480
256.0	2.96	5.48	256.0	8.490
258.0	2.56	6.28	258.0	8.430
260.0	2.21	7.17	260.0	8.320
262.0	1.90	8.15	262.0	8.160
264.0	1.64	9.22	264.0	7.960
266.0	1.43	10.39	266.0	7.740
268.0	1.25	11.65	268.0	7.490
270.0	1.09	13.02	270.0	7.230
272.0	0.97	14.49	272.0	6.960
274.0	0.87	16.07	274.0	6.700
300.0	0.49	23.84	300.0	4.350
400.0	0.32	32.34	400.0	2.020
500.0	0.27	27.26	500.0	1.310
600.0	0.27	22.13	600.0	0.970
700.0	0.27	20.48	700.0	0.770
800.0	0.27	20.41	800.0	0.650
900.0	0.27	21.41	900.0	0.570
1000.0	0.26	23.11	1000.0	0.520
1500.0	0.29	39.65	1500.0	0.390
2000.0	0.35	34.07	2000.0	0.350
2500.0	0.41	31.42	2500.0	0.340
3000.0	0.50	22.01	3000.0	0.330

REV. X1  
BHP-300+  
070628  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

