

Coaxial Low Pass Filter

BLP-850-75+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.00	39.00	10.0	1.540
115.0	0.11	17.92	11.9	1.410
220.0	0.25	14.64	14.1	1.600
325.0	0.26	16.02	16.6	1.610
430.0	0.21	25.19	19.6	1.510
535.0	0.32	21.89	23.5	1.510
640.0	0.53	15.89	27.8	1.440
750.0	0.71	23.37	33.3	1.490
850.0	5.08	3.44	39.3	1.450
950.0	16.83	0.70	47.1	1.490
990.0	21.45	0.50	55.6	1.480
1030.0	26.20	0.42	66.6	1.490
1070.0	30.43	0.35	78.7	1.470
1110.0	34.44	0.31	94.3	1.480
1150.0	38.50	0.28	111.4	1.460
1190.0	42.33	0.27	133.4	1.470
1250.0	47.58	0.25	157.6	1.470
1310.0	53.01	0.26	188.8	1.470
1370.0	58.31	0.22	223.0	1.470
1430.0	65.45	0.23	267.1	1.500
1490.0	70.21	0.21	315.5	1.530
1550.0	72.57	0.20	378.0	1.600
1606.3	75.16	0.21	446.5	1.680
1662.5	69.79	0.19	534.8	1.780
1718.8	66.56	0.21	631.8	1.970
1775.0	64.92	0.20	750.0	2.680
1831.3	62.90	0.20	850.0	3.040
1887.5	61.09	0.20	1150.0	0.900
1943.8	59.41	0.21	1490.0	0.600
2000.0	58.48	0.24	1515.1	1.150

REV. X1
BLP-850-75+
070603
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

