

Typical Performance Data

FREQUENCY (MHz)	PHASE SHIFT		RETURN LOSS					
	(Deg.)		(dBr)					
	0°C	°50C	Vc=0.5V @ 0°C	Vc=10V @ 0°C	Vc=25V @ 0°C	Vc=0.5V @ +50°C	Vc=10V @ +50°C	Vc=25V @ +50°C
50.0	214.95	222.34	-11.01	-9.86	-9.70	-11.24	-9.92	-9.70
65.0	359.99	370.33	-10.66	-10.08	-9.82	-10.81	-10.08	-9.91
80.0	417.15	424.27	-10.76	-10.21	-10.04	-10.92	-10.21	-10.04
95.0	502.31	519.32	-11.63	-10.23	-10.13	-12.02	-10.31	-10.13
105.0	558.68	570.75	-10.74	-10.16	-10.16	-10.83	-10.33	-10.16
120.0	586.13	591.76	-10.13	-10.25	-10.07	-10.13	-10.39	-10.13
135.0	591.70	594.71	-10.06	-10.70	-10.04	-10.06	-10.83	-10.06
150.0	590.40	592.21	-10.04	-10.91	-9.97	-10.04	-11.05	-10.04
165.0	583.66	584.60	-9.98	-10.62	-10.09	-9.98	-10.77	-10.09
180.0	568.25	567.91	-9.97	-10.52	-10.12	-9.97	-10.64	-10.20
195.0	533.10	530.82	-10.00	-10.38	-10.38	-10.00	-10.50	-10.50
205.0	486.07	482.31	-9.98	-10.32	-10.83	-10.03	-10.36	-11.01
220.0	390.51	387.32	-10.01	-10.18	-11.14	-10.07	-10.25	-11.31
235.0	333.92	332.49	-10.03	-10.22	-10.57	-10.08	-10.34	-10.63
250.0	306.43	306.09	-10.06	-10.32	-10.22	-10.06	-10.43	-10.22