

Fixed Attenuator

FW-15+

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10.0	15.00	1.02
50.0	15.00	1.02
100.0	15.02	1.02
500.0	15.08	1.02
1000.0	15.12	1.02
1200.0	15.14	1.02
1400.0	15.16	1.02
1600.0	15.18	1.03
1800.0	15.20	1.03
2000.0	15.22	1.03
2200.0	15.24	1.03
2400.0	15.26	1.04
2600.0	15.28	1.04
2800.0	15.31	1.04
3000.0	15.33	1.04
3200.0	15.35	1.04
3400.0	15.38	1.04
3600.0	15.40	1.05
3800.0	15.43	1.05
4000.0	15.45	1.04
4200.0	15.47	1.04
4400.0	15.50	1.05
4600.0	15.53	1.05
4800.0	15.55	1.05
5000.0	15.58	1.05
5200.0	15.61	1.06
5500.0	15.65	1.06
6000.0	15.72	1.08
6500.0	15.79	1.11
7000.0	15.87	1.14
7500.0	15.94	1.17
8000.0	16.00	1.19
8500.0	16.08	1.21
9000.0	16.13	1.23
9500.0	16.18	1.25
10000.0	16.21	1.27
10500.0	16.23	1.28
11000.0	16.24	1.28
11500.0	16.24	1.28
12000.0	16.22	1.30
12500.0	16.22	1.32
13000.0	16.16	1.32
13500.0	16.12	1.30
14000.0	16.08	1.28
14500.0	15.99	1.23
15000.0	15.97	1.17



P.O. Box 350166, Brooklyn, New York 11235-0003 • Fax (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR
FW-15+
5/1/2014
Page 1 of 1