

Fixed Attenuator

FW-20+

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10.0	19.98	1.03
50.0	20.03	1.03
100.0	20.04	1.03
500.0	20.09	1.03
1000.0	20.14	1.03
1200.0	20.17	1.04
1400.0	20.19	1.04
1600.0	20.22	1.04
1800.0	20.24	1.04
2000.0	20.27	1.05
2200.0	20.29	1.05
2400.0	20.33	1.05
2600.0	20.36	1.05
2800.0	20.39	1.06
3000.0	20.43	1.06
3200.0	20.46	1.06
3400.0	20.50	1.06
3600.0	20.54	1.06
3800.0	20.58	1.06
4000.0	20.62	1.06
4200.0	20.67	1.06
4400.0	20.71	1.06
4600.0	20.76	1.06
4800.0	20.80	1.06
5000.0	20.85	1.06
5200.0	20.90	1.06
5500.0	20.97	1.06
6000.0	21.09	1.07
6500.0	21.20	1.08
7000.0	21.32	1.10
7500.0	21.43	1.14
8000.0	21.54	1.17
8500.0	21.69	1.21
9000.0	21.76	1.26
9500.0	21.79	1.30
10000.0	21.89	1.33
10500.0	21.85	1.35
11000.0	21.81	1.35
11500.0	21.79	1.34
12000.0	21.74	1.33
12500.0	21.68	1.32
13000.0	21.58	1.31
13500.0	21.49	1.28
14000.0	21.41	1.27
14500.0	21.29	1.25
15000.0	21.24	1.22



P.O. Box 350166, Brooklyn, New York 11235-0003 • Fax (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR
FW-20+
5/1/2014
Page 1 of 1