

Typical Performance Data

| FREQUENCY (MHz) | ATTENUATION (dB) | VSWR (:1) |
|--------------------|---------------------|--------------|
| 10.0 | 3.02 | 1.00 |
| 50.0 | 3.03 | 1.01 |
| 100.0 | 3.04 | 1.01 |
| 500.0 | 3.10 | 1.01 |
| 1000.0 | 3.14 | 1.01 |
| 1200.0 | 3.15 | 1.01 |
| 1400.0 | 3.16 | 1.01 |
| 1600.0 | 3.17 | 1.01 |
| 1800.0 | 3.18 | 1.01 |
| 2000.0 | 3.20 | 1.01 |
| 2200.0 | 3.20 | 1.01 |
| 2400.0 | 3.21 | 1.00 |
| 2600.0 | 3.23 | 1.01 |
| 2800.0 | 3.24 | 1.02 |
| 3000.0 | 3.25 | 1.03 |
| 3200.0 | 3.25 | 1.04 |
| 3400.0 | 3.27 | 1.05 |
| 3600.0 | 3.28 | 1.06 |
| 3800.0 | 3.29 | 1.07 |
| 4000.0 | 3.30 | 1.09 |
| 4200.0 | 3.31 | 1.10 |
| 4400.0 | 3.32 | 1.11 |
| 4600.0 | 3.33 | 1.12 |
| 4800.0 | 3.34 | 1.13 |
| 5000.0 | 3.35 | 1.13 |
| 5200.0 | 3.37 | 1.14 |
| 5500.0 | 3.38 | 1.14 |
| 6000.0 | 3.40 | 1.14 |
| 6500.0 | 3.41 | 1.12 |
| 7000.0 | 3.44 | 1.10 |
| 7500.0 | 3.46 | 1.09 |
| 8000.0 | 3.49 | 1.09 |
| 8500.0 | 3.59 | 1.12 |
| 9000.0 | 3.53 | 1.16 |
| 9500.0 | 3.55 | 1.18 |
| 10000.0 | 3.56 | 1.18 |
| 10500.0 | 3.57 | 1.20 |
| 11000.0 | 3.58 | 1.20 |
| 11500.0 | 3.59 | 1.22 |
| 12000.0 | 3.60 | 1.23 |
| 12500.0 | 3.62 | 1.23 |
| 13000.0 | 3.61 | 1.22 |
| 13500.0 | 3.61 | 1.20 |
| 14000.0 | 3.62 | 1.17 |
| 14500.0 | 3.58 | 1.13 |
| 15000.0 | 3.62 | 1.11 |