

Ceramic High Pass Filter

HFCN-2000+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	115.15	99.34	98.50	0.02	0.04	0.06	0.02	0.04	0.05
50	85.18	69.34	68.75	0.08	0.10	0.11	0.09	0.12	0.14
100	87.71	74.05	85.09	0.12	0.12	0.14	0.12	0.14	0.17
700	64.69	64.94	66.07	0.24	0.31	0.39	0.25	0.32	0.38
980	57.44	57.92	57.72	0.30	0.39	0.50	0.28	0.38	0.46
1155	64.73	65.09	62.43	0.31	0.44	0.55	0.32	0.44	0.52
1255	49.60	48.31	47.16	0.35	0.49	0.62	0.37	0.50	0.59
1300	44.30	43.12	42.39	0.35	0.51	0.64	0.37	0.52	0.62
1345	39.63	38.75	37.93	0.37	0.53	0.68	0.41	0.56	0.67
1465	29.42	28.71	28.01	0.45	0.64	0.81	0.46	0.66	0.77
1530	24.58	23.93	23.25	0.51	0.71	0.92	0.56	0.75	0.91
1600	19.74	19.09	18.44	0.66	0.90	1.14	0.68	0.91	1.10
1675	14.88	14.26	13.65	0.94	1.24	1.53	0.93	1.22	1.47
1760	9.90	9.39	8.91	1.58	1.99	2.40	1.53	1.94	2.30
1870	5.00	4.82	4.65	3.49	4.11	4.70	3.40	4.01	4.53
1950	2.95	2.97	2.97	5.82	6.49	7.13	5.65	6.26	6.83
2000	2.21	2.31	2.38	7.46	8.04	8.64	7.26	7.78	8.29
2150	1.18	1.36	1.49	11.22	11.53	11.91	11.00	11.13	11.40
2260	0.95	1.12	1.26	12.36	12.65	13.02	12.16	12.29	12.47
2300	0.88	1.05	1.19	12.57	12.87	13.28	12.34	12.54	12.72
2400	0.79	0.95	1.08	12.92	13.35	13.85	12.79	13.12	13.39
2405	0.79	0.95	1.06	12.95	13.38	13.88	12.84	13.19	13.48
2410	0.78	0.95	1.05	12.95	13.41	13.90	12.86	13.21	13.50
2800	0.50	0.64	0.77	16.52	17.05	17.44	15.94	16.58	17.00
3500	0.36	0.53	0.67	25.49	24.10	23.58	23.17	22.60	22.44
4000	0.30	0.53	0.67	20.92	20.44	20.62	20.48	20.16	20.30
4500	0.35	0.58	0.72	23.57	24.12	25.06	23.42	24.61	24.86
5100	0.43	0.63	0.81	23.89	22.96	21.50	26.37	24.22	23.40
5550	0.59	0.84	1.01	13.65	14.39	14.76	14.04	14.51	14.43
5600	0.73	0.86	1.13	13.19	13.70	14.30	13.70	13.83	13.93
5800	0.80	1.06	1.23	11.52	11.65	12.12	11.73	11.75	11.72
6000	1.07	1.39	1.56	9.72	9.73	9.68	9.84	9.69	9.32
6150	1.08	1.44	1.70	9.13	8.70	8.88	9.01	8.61	8.51
6250	1.22	1.65	1.88	8.51	8.15	8.10	8.44	8.06	7.82
7000	2.64	2.96	3.31	4.75	4.77	4.60	4.59	4.68	4.62
7500	3.65	3.92	4.25	3.36	3.60	3.69	3.28	3.51	3.67
8000	4.74	4.99	5.26	2.70	2.84	3.20	2.68	2.75	3.06
9000	6.14	6.69	7.18	2.03	2.15	2.36	1.83	1.87	1.91
10000	21.91	19.92	18.73	2.29	2.28	2.34	0.53	0.85	0.99
11000	27.59	23.39	20.32	0.78	1.21	1.69	0.52	0.92	1.27
12000	5.87	5.65	5.52	2.63	3.50	4.42	2.49	3.01	3.66
13000	2.88	3.21	3.85	6.37	7.69	9.45	4.90	5.76	6.05

REV. X1
HFCN-2000+
080723
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

