

# Ceramic High Pass Filter

# HFCN-2700AD+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
50	53.91	0.01
240	40.00	0.01
1000	31.58	0.11
1500	40.29	0.19
1650	60.06	0.25
2000	34.05	0.44
2250	35.88	0.64
2270	32.83	0.64
2300	28.96	0.67
2350	23.70	0.78
2500	12.30	1.45
2670	4.09	5.28
2700	3.27	6.70
2730	2.60	8.39
2780	1.87	11.81
2820	1.52	14.80
3000	1.04	15.59
3100	0.98	14.12
3130	0.98	13.93
3150	0.96	13.85
3180	0.95	13.75
3200	0.94	13.74
3400	0.82	14.61
3600	0.72	16.64
3800	0.66	19.33
4000	0.63	22.74
4400	0.60	35.10
4800	0.61	25.87
5500	0.62	18.87
6000	0.66	16.72
7000	0.68	15.45
7500	0.69	15.37
8000	0.91	15.64
8050	0.88	16.06
8100	0.85	16.29
8150	0.80	16.39
8200	0.76	16.24
9000	0.87	13.70
10000	2.13	7.39
11000	18.01	1.54

REV. X1  
HFCN-2700AD+  
060827  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

