

Ceramic High Pass Filter

HFCN-2700

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	67.38	66.69	73.01	0.06	0.10	0.10	0.10	0.12	0.15
100	77.26	77.42	77.35	0.10	0.13	0.15	0.10	0.12	0.16
500	71.13	69.03	70.70	0.19	0.25	0.31	0.17	0.24	0.29
800	64.75	62.64	68.41	0.25	0.35	0.38	0.24	0.31	0.37
1200	61.85	61.62	62.17	0.27	0.38	0.46	0.26	0.34	0.41
1335	68.45	68.68	66.70	0.28	0.40	0.49	0.28	0.39	0.48
1395	61.48	59.86	58.84	0.27	0.39	0.49	0.29	0.41	0.51
1485	50.24	49.91	49.04	0.28	0.42	0.53	0.31	0.42	0.52
1500	49.03	48.61	47.69	0.29	0.43	0.54	0.30	0.43	0.51
1620	40.51	39.93	39.44	0.30	0.45	0.58	0.33	0.45	0.55
1700	35.60	35.06	34.66	0.31	0.49	0.62	0.33	0.48	0.57
1790	30.63	30.16	29.74	0.37	0.56	0.66	0.35	0.50	0.64
1800	30.08	29.62	29.21	0.40	0.56	0.67	0.37	0.53	0.63
1995	20.66	20.26	19.87	0.56	0.72	0.86	0.52	0.70	0.83
2115	15.49	15.17	14.81	0.77	0.95	1.10	0.69	0.89	1.04
2250	10.35	10.11	9.83	1.24	1.48	1.69	1.18	1.40	1.63
2430	5.29	5.16	5.03	2.85	3.25	3.57	2.78	3.14	3.45
2500	3.88	3.85	3.77	3.87	4.31	4.71	3.79	4.20	4.56
2555	3.04	3.09	3.02	4.85	5.31	5.85	4.76	5.13	5.63
2650	2.05	2.11	2.16	6.67	7.25	7.81	6.49	7.02	7.44
2670	1.91	1.99	2.03	7.10	7.70	8.27	6.93	7.45	7.90
2700	1.69	1.79	1.85	7.75	8.34	8.95	7.58	8.10	8.56
2800	1.19	1.33	1.43	9.95	10.56	11.20	9.74	10.24	10.69
2900	0.90	1.04	1.16	12.25	12.81	13.47	11.91	12.38	12.80
2920	0.86	1.01	1.11	12.61	13.18	13.85	12.29	12.77	13.20
3000	0.75	0.90	1.01	14.51	15.04	15.65	13.90	14.40	14.76
3200	0.52	0.69	0.81	19.04	19.87	20.22	17.78	18.47	18.77
4000	0.42	0.59	0.73	21.17	20.08	19.95	20.37	19.53	19.32
4500	0.51	0.64	0.79	20.35	20.31	20.03	19.09	19.59	19.30
5000	0.42	0.61	0.74	26.92	27.97	28.16	25.25	27.40	27.82
5500	0.56	0.75	0.93	22.61	20.67	20.14	24.56	21.83	20.97
5600	0.64	0.84	0.98	19.86	18.32	17.97	21.00	19.21	18.38
5700	0.57	0.89	1.05	17.61	16.54	16.13	17.97	17.16	16.40
5800	0.72	0.95	1.13	14.93	14.83	14.41	15.21	15.13	14.38
6000	0.77	1.11	1.28	12.74	12.11	11.75	13.02	12.28	11.67
6500	1.58	1.85	2.20	7.40	7.52	7.65	7.40	7.52	7.53
7000	2.67	2.91	3.20	4.75	4.92	5.00	4.63	4.83	4.93
7500	3.98	4.23	4.58	3.62	3.60	3.60	3.43	3.53	3.61
8000	4.88	5.41	5.86	2.75	2.61	2.54	2.51	2.51	2.63
9000	7.85	8.05	8.46	1.54	1.76	1.85	1.63	1.70	1.78

REV. X1
HFCN-2700
070110
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

