

Ceramic High Pass Filter

HFCN-4400+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	61.77	60.92	59.27	0.01	0.00	0.00	0.00	0.00	0.00
100	55.24	54.81	54.61	0.02	0.02	0.01	0.01	0.00	0.01
200	49.10	48.86	48.61	0.02	0.01	0.01	0.00	0.02	0.02
500	41.26	41.25	41.26	0.04	0.00	0.02	0.02	0.00	0.02
1000	36.40	36.41	36.52	0.03	0.04	0.06	0.01	0.03	0.06
1500	35.18	35.36	35.52	0.01	0.09	0.12	0.03	0.09	0.12
2000	38.02	38.51	38.92	0.11	0.19	0.22	0.07	0.15	0.18
2500	58.42	53.20	50.03	0.15	0.24	0.27	0.16	0.23	0.27
3000	33.10	32.87	32.50	0.19	0.30	0.35	0.21	0.31	0.37
3500	31.29	32.21	33.08	0.24	0.40	0.51	0.37	0.51	0.61
3600	34.90	36.25	37.15	0.36	0.53	0.64	0.37	0.52	0.65
3800	30.90	28.02	25.66	0.42	0.61	0.79	0.49	0.68	0.85
3900	23.30	21.37	19.69	0.53	0.75	0.98	0.60	0.84	1.05
4000	17.76	16.26	14.88	0.66	0.93	1.25	0.78	1.08	1.37
4100	13.20	11.95	10.81	1.02	1.39	1.84	1.11	1.55	1.99
4200	9.16	8.13	7.26	1.57	2.16	2.84	1.85	2.53	3.23
4300	5.90	5.19	4.64	2.88	3.81	4.85	3.26	4.35	5.51
4400	3.43	3.10	2.86	5.21	6.57	8.02	6.07	7.80	9.63
4500	2.01	1.96	1.96	8.96	10.67	12.33	10.92	13.73	16.95
4600	1.36	1.48	1.60	13.36	14.49	15.31	20.06	25.92	28.89
4700	1.14	1.33	1.49	15.39	14.94	14.74	24.08	20.60	18.50
5000	1.05	1.25	1.43	12.25	12.10	12.04	12.94	12.67	12.53
5600	0.87	1.05	1.22	15.19	15.01	14.64	15.07	15.17	15.17
6000	0.79	0.95	1.09	18.83	20.09	19.15	18.51	20.35	20.66
7000	0.63	0.84	1.03	24.41	23.43	22.46	26.95	23.98	21.49
8000	0.66	0.81	0.95	15.82	18.89	21.36	15.22	18.07	20.63
9000	0.43	0.65	0.83	22.43	22.61	22.59	20.69	22.23	23.65
9900	0.33	0.63	0.82	20.63	20.40	19.97	20.85	21.69	22.86
10100	0.39	0.68	0.88	17.26	17.12	17.66	17.40	18.15	19.57
10500	0.54	0.86	1.10	13.24	13.04	13.06	13.92	13.63	14.04
10900	0.86	1.25	1.56	10.86	10.24	9.91	11.41	10.67	10.53
11900	2.26	3.16	3.72	7.02	6.26	6.08	9.06	8.41	7.26
13000	3.72	3.53	3.64	4.10	4.65	4.92	3.92	4.85	4.99
14000	3.80	3.13	2.68	3.74	5.41	7.72	3.77	5.60	7.79
15000	1.48	1.88	2.12	11.20	11.56	13.36	10.87	10.57	12.19
16000	3.51	4.81	5.94	8.86	8.64	7.34	13.01	8.25	7.48
17000	8.91	9.58	10.86	3.67	4.64	5.46	5.22	4.30	3.38
18000	13.13	13.18	13.81	4.58	3.92	4.41	2.22	3.24	3.08
19000	13.50	13.29	13.08	4.21	3.46	2.86	1.75	3.09	4.65
20000	5.63	6.30	6.37	4.88	5.50	5.88	5.25	5.74	7.29

REV. X1
HFCN-4400+
071010
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

