

# Ceramic High Pass Filter

# HFCN-6010+

## Typical Performance Data

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | RETURN<br>LOSS<br>(dB) |
|--------------------|---------------------------|------------------------|
| 50                 | 69.96                     | 0.02                   |
| 500                | 44.13                     | 0.02                   |
| 1000               | 38.47                     | 0.03                   |
| 2000               | 34.30                     | 0.09                   |
| 5190               | 31.50                     | 0.49                   |
| 5200               | 31.74                     | 0.50                   |
| 5500               | 23.93                     | 0.74                   |
| 5725               | 12.23                     | 1.41                   |
| 5870               | 6.45                      | 2.98                   |
| 6010               | 2.99                      | 7.52                   |
| 6050               | 2.43                      | 9.57                   |
| 6300               | 1.51                      | 15.46                  |
| 6350               | 1.47                      | 14.35                  |
| 8000               | 1.34                      | 11.82                  |
| 10000              | 1.84                      | 7.56                   |
| 13000              | 1.27                      | 11.29                  |
| 15000              | 3.23                      | 7.85                   |

REV. X1  
HFCN-6010+  
090625  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

