

## Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10.0	6.03	1.02
50.0	6.05	1.02
100.0	6.06	1.02
500.0	6.12	1.01
1000.0	6.15	1.01
1200.0	6.16	1.01
1400.0	6.18	1.01
1600.0	6.19	1.01
1800.0	6.20	1.01
2000.0	6.21	1.01
2200.0	6.23	1.02
2400.0	6.24	1.02
2600.0	6.25	1.02
2800.0	6.27	1.03
3000.0	6.28	1.03
3200.0	6.29	1.04
3400.0	6.31	1.04
3600.0	6.32	1.05
3800.0	6.33	1.06
4000.0	6.34	1.06
4200.0	6.36	1.06
4400.0	6.37	1.06
4600.0	6.38	1.07
4800.0	6.40	1.07
5000.0	6.41	1.07
5200.0	6.43	1.08
5500.0	6.44	1.08
6000.0	6.48	1.08
6500.0	6.51	1.08
7000.0	6.55	1.09
7500.0	6.58	1.11
8000.0	6.61	1.13
8500.0	6.65	1.16
9000.0	6.71	1.19
9500.0	6.80	1.23
10000.0	6.79	1.26
10500.0	6.79	1.26
11000.0	6.80	1.25
11500.0	6.81	1.24
12000.0	6.82	1.23
12500.0	6.84	1.23
13000.0	6.82	1.21
13500.0	6.82	1.19
14000.0	6.82	1.18
14500.0	6.79	1.17
15000.0	6.84	1.17