

## Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10.0	7.96	1.01
50.0	7.98	1.01
100.0	7.99	1.01
500.0	8.04	1.00
1000.0	8.07	1.00
1200.0	8.09	1.01
1400.0	8.10	1.01
1600.0	8.11	1.01
1800.0	8.13	1.01
2000.0	8.14	1.01
2200.0	8.15	1.02
2400.0	8.16	1.02
2600.0	8.18	1.02
2800.0	8.19	1.02
3000.0	8.20	1.03
3200.0	8.21	1.03
3400.0	8.23	1.03
3600.0	8.25	1.04
3800.0	8.26	1.04
4000.0	8.28	1.04
4200.0	8.29	1.04
4400.0	8.30	1.05
4600.0	8.31	1.05
4800.0	8.33	1.05
5000.0	8.34	1.05
5200.0	8.36	1.05
5500.0	8.38	1.05
6000.0	8.42	1.06
6500.0	8.45	1.07
7000.0	8.50	1.09
7500.0	8.53	1.11
8000.0	8.56	1.13
8500.0	8.61	1.15
9000.0	8.66	1.18
9500.0	8.70	1.21
10000.0	8.71	1.22
10500.0	8.72	1.22
11000.0	8.76	1.21
11500.0	8.76	1.21
12000.0	8.77	1.21
12500.0	8.78	1.23
13000.0	8.76	1.25
13500.0	8.76	1.26
14000.0	8.77	1.27
14500.0	8.74	1.28
15000.0	8.77	1.28