

Ceramic High Pass Filter

HFCN-1200+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	99.43	104.60	109.11	0.00	0.01	0.01	0.01	0.01	0.00
50	62.45	67.51	72.12	0.00	0.00	0.01	0.01	0.00	0.00
100	69.92	76.44	73.68	0.01	0.01	0.01	0.02	0.02	0.00
300	63.85	63.03	63.97	0.03	0.05	0.09	0.01	0.02	0.05
510	57.52	57.87	57.70	0.08	0.14	0.17	0.08	0.11	0.14
690	56.47	57.29	57.71	0.17	0.25	0.30	0.17	0.22	0.29
750	66.86	63.39	61.22	0.22	0.31	0.36	0.19	0.24	0.32
780	55.63	53.15	52.06	0.25	0.35	0.41	0.21	0.29	0.36
825	44.04	43.20	41.95	0.30	0.40	0.51	0.26	0.36	0.42
865	37.29	36.52	35.67	0.35	0.47	0.54	0.30	0.39	0.47
905	31.64	30.96	30.20	0.43	0.55	0.64	0.35	0.46	0.55
910	30.97	30.29	29.56	0.43	0.53	0.64	0.36	0.50	0.59
940	27.12	26.47	25.76	0.51	0.65	0.76	0.42	0.54	0.64
995	20.50	19.94	19.23	0.74	0.90	1.07	0.62	0.79	0.91
1040	15.36	14.83	14.19	1.02	1.29	1.55	0.81	1.02	1.24
1090	10.04	9.59	9.06	1.81	2.22	2.68	1.50	1.84	2.21
1150	4.89	4.68	4.47	4.36	5.21	6.11	3.69	4.33	4.99
1180	3.20	3.15	3.11	6.73	7.88	9.01	5.70	6.47	7.25
1190	2.77	2.79	2.78	7.71	8.94	10.12	6.49	7.29	8.08
1200	2.42	2.46	2.48	8.73	10.05	11.25	7.32	8.13	8.91
1210	2.13	2.20	2.24	9.83	11.17	12.40	8.20	9.00	9.76
1220	1.91	2.01	2.07	10.87	12.22	13.43	9.05	9.80	10.55
1280	1.18	1.33	1.44	15.18	15.75	16.38	13.03	13.39	13.97
1300	1.08	1.24	1.36	15.44	15.80	16.34	13.73	14.05	14.63
1320	0.98	1.13	1.26	15.41	15.70	16.18	14.15	14.48	15.10
1340	0.94	1.10	1.20	15.38	15.65	16.11	14.56	14.93	15.57
1380	0.83	0.98	1.07	15.49	15.82	16.23	15.27	15.77	16.47
1410	0.77	0.90	1.02	15.96	16.28	16.64	15.92	16.50	17.20
1590	0.51	0.64	0.75	18.75	18.70	18.51	19.64	19.97	20.17
2000	0.38	0.50	0.59	17.48	17.40	17.51	17.47	17.34	17.42
2500	0.27	0.39	0.47	22.03	23.05	24.31	22.09	22.43	22.47
3200	0.30	0.44	0.56	17.02	17.07	16.88	16.85	16.89	16.55
3500	0.45	0.58	0.71	13.14	13.20	13.18	13.27	13.18	13.04
4000	0.75	0.93	1.06	9.29	9.46	9.51	9.31	9.40	9.34
4300	1.09	1.28	1.41	7.85	7.86	7.86	7.85	7.80	7.69
4600	1.37	1.62	1.81	6.73	6.66	6.65	6.70	6.64	6.57
5000	1.77	2.10	2.32	5.78	5.59	5.53	5.71	5.54	5.47
5500	2.47	2.77	2.95	4.26	4.44	4.53	4.20	4.39	4.49
6000	3.36	3.55	3.75	3.33	3.70	3.81	3.30	3.65	3.74
6500	4.09	4.25	4.39	2.82	3.12	3.34	2.81	3.07	3.32
7000	4.58	4.86	5.13	2.52	2.64	2.74	2.43	2.60	2.77
7500	5.35	5.82	6.27	2.24	2.24	2.26	2.13	2.17	2.35
8030	9.05	10.50	7.89	2.42	4.64	7.74	1.59	2.16	3.23
9000	11.88	13.57	12.12	1.32	1.81	2.92	2.21	3.09	4.99

REV. X1
HFCN-1200+
080723
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

