

Ceramic High Pass Filter

HFCN-2275

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	112.02	98.51	108.24	0.01	0.04	0.03	0.00	0.04	0.05
50	78.91	65.35	75.22	0.07	0.10	0.09	0.07	0.11	0.13
100	71.58	75.47	83.51	0.09	0.12	0.14	0.10	0.11	0.14
800	61.34	67.33	61.50	0.25	0.33	0.39	0.25	0.33	0.38
1085	59.27	59.48	58.61	0.27	0.37	0.43	0.26	0.35	0.42
1315	49.95	49.24	49.14	0.30	0.42	0.52	0.30	0.41	0.50
1400	45.58	45.01	44.48	0.32	0.45	0.55	0.31	0.45	0.54
1500	39.93	39.49	38.76	0.34	0.48	0.61	0.35	0.48	0.58
1675	30.33	29.61	28.97	0.45	0.63	0.78	0.44	0.60	0.72
1770	25.03	24.31	23.64	0.53	0.74	0.92	0.50	0.67	0.84
1855	20.32	19.59	18.90	0.66	0.90	1.13	0.60	0.82	1.02
1945	15.40	14.72	14.06	0.93	1.22	1.51	0.84	1.10	1.36
2045	10.33	9.75	9.19	1.59	2.00	2.42	1.37	1.77	2.18
2170	5.29	5.03	4.74	3.56	4.22	4.91	3.24	3.88	4.52
2255	3.11	3.06	2.98	5.86	6.70	7.52	5.51	6.26	7.05
2275	2.76	2.75	2.71	6.50	7.36	8.21	6.17	6.93	7.71
2350	1.85	1.95	1.99	9.04	9.91	10.76	8.74	9.43	10.23
2450	1.24	1.39	1.51	12.13	12.91	13.66	11.92	12.51	13.10
2500	1.08	1.25	1.36	13.29	13.98	14.71	13.31	13.79	14.32
2580	0.90	1.08	1.19	14.87	15.39	16.11	14.87	15.34	15.73
2620	0.83	1.01	1.13	15.31	15.91	16.50	15.54	15.96	16.29
2640	0.81	0.99	1.10	15.59	16.12	16.70	15.84	16.27	16.57
2800	0.65	0.82	0.95	17.58	18.03	18.44	17.88	18.27	18.48
3500	0.39	0.55	0.67	32.40	31.00	31.67	29.59	28.04	28.53
4000	0.42	0.62	0.73	19.64	18.64	18.55	19.89	18.80	18.39
4500	0.46	0.66	0.80	17.65	17.53	17.19	17.74	17.96	17.56
5000	0.44	0.65	0.78	20.58	20.85	20.73	20.46	21.43	21.74
5700	0.53	0.75	0.89	26.61	23.10	23.20	27.28	23.48	23.09
6000	0.65	0.89	1.02	17.65	16.53	16.28	17.59	16.30	15.81
6100	0.65	0.91	1.11	16.21	15.36	14.99	16.11	15.11	14.44
6230	0.77	1.09	1.22	14.41	13.69	13.61	14.17	13.31	13.02
6500	0.99	1.25	1.45	10.83	10.90	10.79	10.68	10.63	10.38
7000	1.63	1.76	2.04	7.48	7.71	7.64	7.23	7.57	7.48
7500	2.35	2.52	2.87	5.56	5.63	5.54	5.33	5.56	5.61
8000	2.81	3.29	3.58	4.54	4.46	4.27	4.38	4.43	4.45
9000	4.34	4.61	4.95	2.83	2.99	3.14	2.88	3.11	3.11
10000	4.29	4.48	4.92	3.77	5.21	8.29	3.35	4.24	5.01
10400	12.99	19.36	21.49	3.44	2.40	2.18	2.16	1.82	1.70
11000	22.11	25.63	28.02	0.99	1.17	1.38	0.78	1.18	1.50
11500	16.14	13.69	12.15	1.02	1.64	2.20	1.01	1.54	2.14
12000	6.53	5.89	5.45	2.32	3.42	4.61	2.48	3.23	4.03

REV. X1
HFCN-2275
070110
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

