

Ceramic High Pass Filter

HFCN-880

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	73.96	82.28	74.30	0.01	0.02	0.01	0.02	0.02	0.00
50	63.45	71.77	63.78	0.01	0.02	0.01	0.01	0.01	0.00
100	63.19	61.97	59.77	0.00	0.00	0.02	0.01	0.04	0.01
200	57.40	56.85	57.15	0.05	0.08	0.09	0.01	0.05	0.04
395	58.01	58.72	59.33	0.14	0.20	0.22	0.13	0.18	0.20
425	64.34	66.61	66.03	0.16	0.23	0.27	0.15	0.22	0.24
460	58.17	56.27	55.13	0.19	0.27	0.30	0.16	0.23	0.28
500	46.62	45.84	45.02	0.22	0.31	0.39	0.20	0.28	0.33
520	42.63	41.83	41.36	0.29	0.37	0.44	0.24	0.36	0.41
590	31.19	30.63	30.16	0.41	0.55	0.62	0.41	0.51	0.60
640	24.19	23.68	23.24	0.54	0.72	0.81	0.51	0.67	0.77
665	20.92	20.44	19.97	0.68	0.88	1.00	0.65	0.79	0.91
750	10.59	10.22	9.82	1.65	2.01	2.37	1.51	1.84	2.14
805	5.39	5.21	5.00	3.66	4.29	5.02	3.43	4.00	4.64
840	3.23	3.20	3.14	6.01	6.88	7.81	5.70	6.47	7.30
880	1.91	1.97	2.05	9.60	10.64	11.63	9.16	10.09	10.96
900	1.51	1.62	1.73	11.42	12.50	13.41	11.01	11.97	12.80
950	1.04	1.17	1.33	15.27	16.29	16.70	15.11	16.07	16.60
960	0.97	1.12	1.25	15.84	16.83	17.12	15.73	16.67	17.13
970	0.94	1.06	1.21	16.38	17.31	17.49	16.27	17.17	17.56
990	0.84	0.98	1.13	17.20	17.99	18.02	17.28	18.12	18.31
1000	0.82	0.97	1.10	17.45	18.20	18.14	17.69	18.51	18.60
1060	0.70	0.83	0.96	18.39	18.82	18.46	18.62	19.17	18.89
1235	0.54	0.66	0.77	17.61	17.47	17.36	17.75	17.57	17.54
1500	0.41	0.49	0.58	18.70	18.84	19.45	18.73	18.93	19.70
1650	0.35	0.44	0.53	22.31	22.25	23.05	22.54	22.64	23.71
2000	0.28	0.36	0.48	26.70	25.94	25.11	27.42	27.11	26.89
2200	0.29	0.40	0.52	19.03	18.52	18.19	19.06	18.64	18.56
2400	0.40	0.52	0.63	14.94	14.63	14.35	14.89	14.64	14.52
2450	0.42	0.55	0.67	14.09	13.81	13.51	14.06	13.83	13.67
2500	0.47	0.60	0.70	13.25	13.02	12.74	13.19	12.99	12.81
2800	0.72	0.86	1.01	9.94	9.82	9.60	9.88	9.77	9.61
3200	1.29	1.42	1.56	6.96	6.98	7.01	7.00	6.97	6.93
4000	2.62	2.85	3.02	3.88	3.95	4.07	3.92	3.95	3.99
4740	4.21	4.54	4.82	2.56	2.60	2.67	2.49	2.55	2.60
5500	6.15	6.39	6.79	1.65	1.90	2.05	1.58	1.79	1.94
6000	7.99	8.11	8.39	1.23	1.51	1.68	1.20	1.41	1.57
6500	9.74	10.05	10.62	1.09	1.26	1.38	1.05	1.22	1.36
7030	16.82	20.06	19.23	0.95	1.34	1.79	0.96	1.49	2.27
7290	5.91	5.71	6.41	6.02	5.11	3.74	9.25	7.13	4.89
8000	9.17	9.77	10.57	1.17	1.28	1.25	1.09	1.23	1.35

REV. X1
HFCN-880
070930
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

