

# Ceramic Low Pass Filter

# LFCN-400

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	0.03	0.06	0.09	42.07	40.09	39.54	41.12	40.09	38.43
50	0.15	0.18	0.21	30.23	28.36	27.22	29.64	28.06	26.89
100	0.22	0.25	0.28	26.76	26.50	26.24	25.57	25.38	25.07
400	0.63	0.76	0.88	26.79	25.72	25.08	24.46	23.45	22.71
450	0.81	0.99	1.15	22.85	21.78	20.61	21.95	20.90	19.86
560	2.24	2.71	3.16	9.98	9.71	9.22	12.77	13.36	13.84
565	2.40	2.89	3.38	9.49	9.21	8.75	12.66	13.42	14.03
590	3.71	4.57	5.42	6.83	6.47	6.01	11.97	12.76	13.17
615	7.15	8.72	10.25	3.70	3.45	3.24	7.74	7.58	7.26
635	12.68	14.72	16.71	2.05	2.08	2.06	4.41	4.51	4.47
645	16.32	18.50	20.64	1.63	1.73	1.77	3.48	3.65	3.67
655	20.33	22.72	24.98	1.35	1.48	1.56	2.86	3.08	3.18
660	22.51	25.00	27.35	1.25	1.38	1.48	2.62	2.85	2.94
670	27.36	30.03	32.55	1.12	1.26	1.35	2.27	2.51	2.66
680	32.85	35.71	38.23	1.04	1.18	1.27	2.00	2.26	2.39
700	45.31	45.62	45.32	0.87	1.01	1.12	1.63	1.90	2.04
750	49.40	50.72	51.62	0.69	0.81	0.90	1.22	1.42	1.58
800	43.70	42.97	42.23	0.58	0.69	0.78	1.01	1.20	1.34
880	38.80	38.97	39.05	0.45	0.57	0.65	0.78	0.96	1.06
1000	41.73	42.26	42.69	0.35	0.43	0.52	0.54	0.69	0.78
1100	48.36	49.34	50.10	0.29	0.39	0.46	0.46	0.60	0.67
1150	54.06	55.25	56.46	0.24	0.34	0.42	0.38	0.51	0.58
1210	66.14	67.51	67.11	0.21	0.32	0.39	0.38	0.49	0.57
1550	55.72	55.94	56.95	0.13	0.23	0.32	0.19	0.29	0.31
1770	70.58	71.17	72.04	0.15	0.26	0.34	0.24	0.33	0.37
2000	56.84	56.67	55.81	0.18	0.27	0.35	0.20	0.29	0.33
2500	50.60	51.63	51.81	0.15	0.24	0.29	0.16	0.26	0.28
3000	49.89	50.38	50.55	0.20	0.30	0.34	0.15	0.23	0.27
3500	43.34	43.35	43.45	0.18	0.31	0.39	0.13	0.24	0.29
4000	36.33	37.72	36.35	0.26	0.37	0.50	0.13	0.27	0.39
4340	19.14	18.96	20.49	1.14	1.19	1.00	1.04	1.17	0.93
5000	25.66	26.49	26.63	0.40	0.53	0.64	0.24	0.38	0.51
5500	27.40	26.38	26.03	0.42	0.62	0.80	0.21	0.42	0.55
6000	24.50	25.14	24.76	0.45	0.67	0.90	0.31	0.49	0.64
7000	20.92	20.96	21.33	0.90	1.26	1.55	0.42	0.55	0.61
8000	18.68	18.98	19.33	0.73	0.88	0.94	0.34	0.50	0.59
9000	17.55	17.31	17.29	0.88	1.12	1.37	0.33	0.58	0.73
10000	15.98	16.15	16.03	0.91	1.23	1.57	0.62	1.01	1.36
11000	18.07	19.61	21.53	2.16	2.95	3.45	2.84	3.66	4.35
13000	25.79	23.96	22.37	2.03	2.72	3.35	1.89	2.28	2.45
15000	8.66	8.76	8.53	4.82	5.27	5.88	4.64	4.81	5.08

REV. X1  
LFCN-400  
070925  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

