

Ceramic Low Pass Filter

LFCN-530

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	0.02	0.05	0.07	47.11	46.06	45.60	47.00	46.06	45.40
50	0.12	0.16	0.18	33.82	32.31	31.64	33.20	31.72	31.06
100	0.17	0.22	0.24	32.97	31.93	31.57	31.11	30.04	29.57
200	0.25	0.32	0.35	32.50	34.75	37.04	27.52	27.62	27.74
300	0.33	0.41	0.47	33.65	39.11	51.62	26.29	26.33	26.27
400	0.43	0.54	0.62	33.23	35.64	37.40	26.90	26.79	26.60
500	0.58	0.73	0.84	28.58	28.88	28.88	26.68	26.53	26.24
515	0.61	0.77	0.89	27.16	27.21	27.01	25.83	25.60	25.23
530	0.65	0.81	0.94	25.67	25.53	25.20	24.74	24.44	24.02
545	0.69	0.87	1.00	24.13	23.86	23.45	23.60	23.24	22.79
570	0.78	0.97	1.12	21.67	21.25	20.78	21.64	21.23	20.78
670	1.57	1.95	2.27	13.04	12.49	12.01	16.55	16.79	16.98
700	2.33	2.89	3.38	9.68	9.12	8.65	13.76	13.97	14.05
725	3.81	4.69	5.46	6.26	5.85	5.52	9.15	9.10	8.97
755	7.84	9.23	10.41	3.03	2.95	2.89	4.60	4.70	4.73
780	13.42	15.14	16.58	1.74	1.85	1.92	2.76	2.99	3.13
795	17.61	19.49	21.09	1.38	1.52	1.62	2.21	2.47	2.63
815	24.24	26.41	28.26	1.12	1.28	1.40	1.80	2.06	2.23
820	26.15	28.41	30.32	1.07	1.24	1.36	1.73	1.99	2.16
850	40.89	41.61	41.38	0.91	1.07	1.19	1.46	1.71	1.87
945	43.79	44.98	45.98	0.66	0.81	0.91	1.15	1.38	1.53
960	47.58	49.04	49.97	0.64	0.78	0.89	1.13	1.35	1.50
1050	40.25	40.20	40.18	0.53	0.66	0.76	1.00	1.20	1.35
1165	36.81	37.20	37.50	0.44	0.56	0.66	0.86	1.04	1.18
1315	39.26	39.77	40.21	0.35	0.47	0.56	0.68	0.85	0.97
1570	49.21	49.82	50.39	0.27	0.38	0.48	0.47	0.61	0.71
1755	58.61	59.17	59.60	0.23	0.35	0.44	0.38	0.50	0.59
1925	63.57	63.50	63.03	0.20	0.32	0.41	0.31	0.43	0.50
2140	58.41	57.51	57.31	0.19	0.31	0.40	0.26	0.36	0.43
2500	52.23	51.92	52.20	0.20	0.32	0.40	0.18	0.29	0.35
2880	49.46	47.84	47.83	0.24	0.35	0.43	0.20	0.30	0.36
3000	44.44	47.94	47.84	0.24	0.34	0.42	0.21	0.29	0.35
3640	41.72	42.84	42.96	0.23	0.37	0.46	0.21	0.30	0.38
4780	29.67	29.13	27.98	0.50	0.71	0.93	0.32	0.49	0.66
4910	18.10	18.81	21.01	1.63	1.38	1.09	1.00	0.91	0.79
5840	23.86	26.47	26.66	0.66	0.73	0.86	1.08	0.88	0.84
6000	25.48	24.80	24.78	0.44	0.67	0.84	0.35	0.54	0.70
7800	20.42	20.46	20.60	0.48	0.76	0.95	0.33	0.56	0.72
10820	15.77	16.32	16.76	1.90	2.44	2.99	0.73	1.12	1.49
13280	24.50	28.15	28.24	1.70	2.04	2.47	1.90	1.85	2.02
16000	14.26	14.50	14.44	2.93	3.48	4.22	3.38	3.68	3.77

REV. X1
LFCN-530
070925
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

