

Metal Shield Low Pass Filter

LPF-EDU1664

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	0.07	40.89	1	6.99
15	0.14	34.63	2	7.07
65	0.33	24.25	4	7.14
125	0.85	32.83	5	7.09
135	1.20	19.28	20	7.13
142	2.14	10.40	25	7.16
144	3.03	7.07	30	7.20
150	8.78	1.99	35	7.26
156	16.58	0.90	40	7.34
162	24.14	0.64	45	7.40
170	33.57	0.52	50	7.49
175	39.28	0.48	55	7.60
180	44.84	0.45	60	7.75
190	55.87	0.39	65	7.91
195	60.70	0.38	70	8.08
370	67.14	0.15	75	8.28
540	72.98	0.12	80	8.51
580	80.57	0.11	90	9.10
620	77.08	0.11	100	9.82
950	73.86	0.13	110	10.82
1180	70.54	0.15	120	11.80
1370	73.52	0.17	122	12.85
1820	65.63	0.28	124	13.93
2000	67.36	0.30	125	14.17



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



REV. X1
LPF-EDU1664
URJ
120807
Page 1 of 1